

DELL 32 4K USB-C HUB MONITOR | P3222QE

## A better view from anywhere



### DETAIL DRIVEN

Capture every nuance on a brilliant 31.5" 4K monitor with IPS technology for consistent views no matter where you sit.



### OPTIMIZE YOUR WORKSPACE

Pivot, tilt, swivel and adjust the height of your monitor to your exact preference.



### COMFORT WITHOUT SACRIFICING COLOR

Optimize eye comfort with an always-on, built-in low blue light screen that optimizes eye comfort while delivering excellent color accuracy.



### TRUSTED RELIABILITY

Dell monitors — World's number 1 monitor company.\*  
Enjoy peace of mind with Dell Premium Panel Exchange, 3 year Advanced Exchange Service<sup>1</sup> and optional ProSupport.<sup>2</sup>

# Maximize productivity



## DETAIL DRIVEN

**Detail driven:** Capture every nuance on a brilliant 31.5-inch, 4K monitor with more than 8 million pixels and four times the resolution of standard Full HD.

**Designed with you in mind:** Navigate the menu and adjust screen settings with the easy-to-use joystick control. Snap on the optional Dell Slim Soundbar (SB521A) and elevate your listening experience.

**Sleek yet practical:** The stunning design and small base complement an improved cable management system that hides cords in the monitor riser.



## COMFORT WITHOUT SACRIFICING COLOR

**Comfort without sacrificing color:** Optimize eye comfort with ComfortView Plus<sup>3</sup> — an always-on, built-in screen that reduces potentially harmful blue light emissions while delivering color accuracy.

**Color consistency comes standard:** See consistent, vibrant colors across a wide viewing angle enabled by In-Plane Switching (IPS) technology. With 99% sRGB coverage, you get precise colors right out of the box.



## OPTIMIZE YOUR WORKSPACE

**Adjust to your comfort:** Tilt, swivel, pivot and adjust the height of your monitor for a comfortable set up all day long. Furthermore, choose from a variety of mounts and stands including VESA for more flexibility.

**Clutter-free productivity hub:** Get more done with RJ45 wired ethernet connectivity and USB-C<sup>®</sup> providing up to 65W power delivery.

**Enhanced manageability:** MAC address pass-through<sup>4</sup>, PXE boot, and wake-on-LAN are conveniently built in.

**Jumpstart productivity:** Simply press the monitor power button and the power sync feature seamlessly starts your monitor and connected Dell PC, even when the laptop lid is closed. Compatible with select Dell PCs.



## TRUSTED RELIABILITY

### WORLD'S NUMBER 1 MONITOR COMPANY\*

**Peace of mind:** Dell Premium Panel Exchange allows a free panel replacement during the Limited Hardware Warranty<sup>5</sup> period even if only one bright pixel is found.

**Minimize downtime:** Your monitor comes with a 3-year Advanced Exchange Service<sup>1</sup> so that if a replacement becomes necessary, it will be shipped to you the next business day during your 3-year Limited Hardware Warranty.<sup>5</sup>

**Get a higher level of support:** Upgrade to 24x7, in-region technical phone support from qualified engineers with Dell ProSupport option.<sup>2</sup>

# Features & Technical Specifications

## Monitor

Diagonal Viewing Size	Dell 32 4K USB-C Hub Monitor – P3222QE
Active Display Area	800.01 mm (31.5 inches)
Width	697.31 mm (27.45 inches)
Height	392.23 mm (15.44 inches)
Maximum Preset Resolution	3840 x 2160 at 60 Hz
Aspect Ratio	16:9
Pixel Pitch	0.18159 mm x 0.18159 mm
Pixel Per Inch (PPI)	139.87
Brightness	350 cd/m <sup>2</sup> (typical)
Color Support	Color gamut: 99% sRGB Color depth: 1.07 billion colors
Contrast Ratio	1000:1 (typical)
Viewing Angle	178°/178°
Response Time	5 ms (Fast mode) 8 ms (Normal mode)
Panel Type	In-Plane Switching Technology
Display Screen Coating	Anti-glare treatment of the front polarizer (3H) hard coating
Backlight Technology	LED
ComfortView with Flicker-free screen	Yes, with ComfortView Plus
Dell Display Manager Compatibility	Yes, Easy Arrange and other key features
Remote Asset Management	Yes, via Dell Command   Monitor
GSA/TAA	Yes
Optional Soundbar	SB521A

## Connectivity

Connectors	1 x DisplayPort 1.4 (in) port 1 x HDMI 2.0 port 1 x USB Type-C® (USB 3.2 Gen1 (5Gbps) upstream port, USB Power Delivery up to 65W**) 4 x SuperSpeed USB 5Gbps (USB 3.2 Gen1 (5Gbps)) USB Standard-A downstream port 1 x RJ45 (1Gbps)
HDCP Support	HDMI (HDCP 1.4, HDCP 2.2), DP (HDCP 1.4, HDCP 2.2)

## Design Features

Adjustability	Height adjustable stand (150 mm), Tilt (-5° to 21°), Swivel (-30 to 30°), Pivot (-90 to 90°)
Security	Security lock slot (cable lock sold separately)
Flat Panel Mount Interface	VESA (100 mm x 100 mm)

## Power

AC input voltage/frequency/current	100-240 VAC / 50 or 60 Hz ± 3 Hz / 1.8 A (maximum)
Power Consumption (Operational)	0.2 W (Off Mode) <sup>6</sup> 0.2 W (Standby Mode) <sup>6</sup> 28.3 W (On Mode) <sup>6</sup> 145 W (Max) <sup>7</sup>
Power Consumption Stand by / Sleep	Less than 0.3W

## Dimensions (with stand)

Height	618.67 mm (24.36 inches)
Width	712.40 mm (28.05 inches)
Depth	233.17 mm (9.18 inches)

## Weight

Weight (panel only - for VESA mount/ no cables)	5.30 kg (11.68 lb)
Weight (monitor and cables with stand)	10.00 kg (22.04 lb)
Weight (with packaging)	13.40 kg (29.53 lb)

## Standard Service Plan

Premium Panel Exchange, 3 Years Advanced Exchange Service<sup>1</sup> & Limited Hardware Warranty<sup>5</sup>

## Optional Service Plan

Dell ProSupport<sup>2</sup>

## Environmental Compliance

ENERGY STAR® certified monitor, EPEAT® Gold registered where applicable<sup>3</sup>, TCO Edge Certified Display, RoHS Compliant, BFR/PVC Free monitor (excluding external cables), meets NFPA 99 leakage current requirements, Arsenic-free glass and Mercury-free for the panel only.

## What's in the box?

### Components

- Monitor with stand

### Cables

- Power cable
- DisplayPort to DisplayPort cable (1.8m)
- USB Type-C® cable (1m)
- USB Type-A to USB Type-C cable (1.8m)
- Cable tie


### Documentation

- Quick Setup Guide
- Safety, environmental, and regulatory information


# Adjustability and connectivity

DELL 32 4K USB-C HUB MONITOR | P3222QE

Easily adjust the panel to your preferred viewing position.



## Connectivity



- |                      |                                  |              |
|----------------------|----------------------------------|--------------|
| 1 Security lock slot | 4 DisplayPort (in)               | 7 RJ45 port  |
| 2 AC Power port      | 5 USB-C port                     | 8 Stand lock |
| 3 HDMI port          | 6 USB Type-A downstream port (4) |              |

## RECOMMENDED ACCESSORIES



DELL SINGLE MONITOR ARM | MSA20

Enjoy a virtually tool-free assembly and easy installation with this Dell Single Monitor Arm – MSA20. Dell Quick Release lets you snap on your Dell Monitor onto the arm simply without tools.



DELL MULTI-DEVICE WIRELESS KEYBOARD AND MOUSE COMBO | KM7120W

Seamlessly switch between 3 devices anytime with a click of the button and enhance your productivity with its 36-month battery life.



DELL SLIM SOUNDBAR | SB521A

World's slimmest and lightest soundbar<sup>9</sup> offers exceptional audio clarity and magnetically attaches to Dell monitors<sup>10</sup> offering a clean desk experience.

\* Dell monitors are #1 Worldwide for 7 consecutive years (2013, Q2 to 2020, Q4)! Source: IDC Worldwide Quarterly PC Monitor Tracker, Q4 2020.

\*\* Dell adheres to standard USB-C specifications and protocol and these monitors deliver up to 65W of power. Functionality with non Dell USB-C systems may vary.

1 Advanced Exchange: Dell will send you a replacement monitor the next business day in most cases, if deemed necessary after phone/online diagnosis. Shipping times may vary by location and for monitors 55" and above. Fee charged for failure to return defective unit. See [dell.com/servicecontracts/global](http://dell.com/servicecontracts/global).

2 Availability varies, please visit [www.dell.com/support](http://www.dell.com/support) for details.

3 TÜV Certified – Low Blue Light Hardware Solution and Flicker Free (ID 1111236810). For more details, visit [www.tuv.com](http://www.tuv.com).

4 MAC Address pass-through functionality is tested to work with most Dell PC systems. Functionality on non-Dell systems may vary.

5 For a copy of the Limited Hardware Warranty, write to Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see [dell.com/warranty](http://dell.com/warranty).

6 As defined in EU 2019/2021 and EU 2019/2013.

7 Maximum brightness and contrast setting with maximum power loading on all USB ports.

8 EPEAT Gold registered in the U.S. EPEAT registration varies by country. See [www.epeat.net](http://www.epeat.net) for registration status by country.

9 Based on Dell analysis of publicly available specs of comparative attachable monitor soundbars, July 2020.

10 Compatible with select Dell monitors only. Please refer to the Dell Slim Soundbar – SB521A compatibility list on [dell.com](http://dell.com).

[Dell.com/monitors](http://Dell.com/monitors)

Product availability varies by country. Please contact your Dell representative for more information.

© 2021 Dell Inc. or its subsidiaries. All Rights Reserved. Dell Technologies, Dell, EMC, Dell EMC and other trademarks are trademarks of Dell Inc. or its subsidiaries. Other trademarks may be trademarks of their respective owners. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum.

