



A height adjustable 32" IPS Panel Technology monitor featuring WQHD resolution

The ProLite XB3270QS-B5 is a 31.5" screen featuring an IPS panel and WQHD (2560x1440) resolution, delivering both excellent colour performance with wide viewing angles and noticeably sharper images, which is ideal for productivity solutions, demanding office and financial applications. The 150mm height-adjustable stand ensures you can adjust the screen position to your preferences, and the flicker-free panel with blue light reducer function reduces eye fatigue.





WQHD

With true WQHD 2560 x 1440p resolution your monitor is ready to display high definition images. This means you can accommodate more information on your screen, i.e. over 76% more in comparison to a 1920 x 1080 monitor.

IPS Technology

IPS displays are best known for wide viewing angles and natural, highly accurate colours. They are especially suited for colour-critical applications.

DISPLAY CHARACTERISTICS

Diagonal	31.5", 80cm
Panel	IPS Panel Technology LED, matte finish
Native resolution	2560 x 1440 @60Hz (3.7 megapixel WQHD)
Aspect ratio	16:9
Panel brightness	250 cd/m²
Static contrast	1200:1
Advanced contrast	80M:1
Response time (GTG)	4ms
Viewing zone	horizontal/vertical: 178°/178°, right/left: 89°/89°, up/down: 89°/89°
Colour support	1.07B 10bit (8bit + Hi-FRC) (sRGB:100%, NTSC: 72%)
Horizontal Sync	30 - 90kHz
Viewable area W x H	698.1 x 392.7mm, 27.5 x 15.5"
Pixel pitch	0.273mm
Colour	matte, black

02 INTERFACES / CONNECTORS / CONTROLS

Signal input	DVI x1 HDMI x1 DisplayPort x1
HDCP	yes
Headphone connector	yes

FEATURES

Blue light reducer	yes
Flicker free	yes
Extra	i-Style colour
OSD languages	EN, DE, FR, IT, RU, JP, CZ, NL, PL
Control buttons	Power, Menu, Scroll up/ Volume, Scroll down/ Eco, Input/ Exit
User controls	picture (picture format, brightness, contrast, black tuner, sharpness, overdrive, ACR, Eco, X-Res technology), colour (warm, normal, cool, user colour, i-Style colour, blue light reducer), input select, audio (volume, mute, audio input), language, OSD (H. position, V. position, background, time out), setup menu (HDMI RGB range, logo, LED, auto power off, memory recall, information)
Speakers	2 x 3W
Convenience	Kensington-lock™ prepared, DDC2B, Mac OSX



MECHANICAL

Display position adjustments	height, swivel, tilt
Height adjustment	150mm
Swivel stand	90°; 45° left; 45° right
Tilt angle	22° up; 3° down
VESA mounting	100 x 100mm
Cable management system	yes



ACCESSORIES INCLUDED

Cables	power, HDMI, DP
Other	quick start guide, safety guide

06 POWER MANAGEMENT

Power supply unit	internal	
Power supply	AC 100 - 240V, 50/60Hz	
Power usage	35W typical, 0.5W stand by	

07 SUSTAINABILITY

Regulations	CE, TÜV-Bauart, EAC, VCCI-B, PSE, RoHS support, ErP, WEEE, REACH, UKCA
Energy efficiency class (Regulation (EU)	F
2017/1369)	
REACH SVHC	above 0.1%: Lead

08 DIMENSIONS / WEIGHT

Product dimensions W x H x D	726 x 439.5 (579.5) x 245.5mm
Box dimensions W x H x D	810 x 176 x 510mm
Weight (without box)	8.6kg
Weight (with box)	11.6kg
EAN code	4948570121328

