

The United States Trade Agreements Act (TAA)-compliant Xerox® Printers and Multifunction Printers (MFPs)

Xerox offers a robust lineup of printers and MFPs tailored specifically for government use, in accordance with the US Trade Agreements Act (TAA), a mandatory requirement for many of today's contract procurements. Our comprehensive security approach includes measures to prevent unauthorized access, detect and protect against malicious attempts, and safeguard data and documents. This includes CAC/PIV solutions for NIPRNet and SIPRNet, as well as Common Criteria Certification for Xerox® VersaLink® and AltaLink® MFPs. In addition, we go above and beyond compliance requirements for the world's most widely recognized certifications related to environmental performance, such as ENERGY STAR® and EPEAT®. Below is a selection of TAA-compliant Xerox® Products:

Color Printers



	XEROX® C410 COLOR PRINTER	XEROX® VERSALINK® C620 COLOR PRINTER
TAA Part Number	C410/YDN	C620/YDN
Market Code	C410DNG	C620DNG
Print Speed (up to)	42 ppm color/black	52 ppm color/black
Duty Cycle (up to)*	125,000	150,000
Recommended Average Monthly Print Volume (up to)	10,000	20,000
Resolution (max)	1200 x 1200 dpi	1200 x 1200 dpi
Media Sizes	3 x 5 in. to 8.5 x 14 in.	3 x 5 in. to 8.5 x 14 in.
Two-sided Output	Standard	Standard
CAC/PIV¹	Enabled	Capable
Wi-Fi	Optional (Wireless Network Adapter Required – 097N02470)	Optional (Wireless Network Adapter Required – 097N02470)
AOM Authorization	Not required	Not required
Paper Capacity (std/max)	251/2,001	650/2,850

Black-and-White Printers



	XEROX® B410 PRINTER	XEROX® VERSALINK® B620 PRINTER
TAA Part Number	B410/YDN	B620/YDN
Market Code	B410DNG	B620DNG
Print Speed (up to)	50 ppm	65 ppm
Duty Cycle (up to)*	175,000	300,000
Recommended Average Monthly Print Volume (up to)	20,000	30,000
Resolution (max)	1200 x 1200 dpi	1200 x 1200 dpi
Media Sizes	3 x 5.8 in. to 8.5 x 14 in.	3 x 5 to 8.5 x 14 in.
Two-sided Output	Standard	Standard
CAC/PIV¹	Enabled	Capable
Wi-Fi	Optional (Wireless Network Adapter Required – 097N02470)	Optional (Wireless Network Adapter Required – 097N02444)
AOM Authorization	Not required	Not required
Paper Capacity (std/max)	650/2,300	650/3,850

Color Multifunction Printers



	XEROX® VERSALINK® C415 COLOR MULTIFUNCTION PRINTER	XEROX® VERSALINK® C625 COLOR MULTIFUNCTION PRINTER
TAA Part Number	C415/YDN	C625/YDN
Market Code	C415DNG	C625DNG
Print Speed (up to)	42 ppm color/black	52 ppm color/black
Duty Cycle (up to)*	125,000	150,000
Recommended Average Monthly Print Volume (up to)	10,000	20,000
Print Resolution (max)	1200 x 1200 dpi	1200 x 1200 dpi
Media Sizes	3 x 5 in. to 8.5 x 14 in.	3 x 5 in. to 8.5 x 14 in.
Two-sided Output	Standard	Standard
Document Feeder Type	100-Sheet Single-Pass DADF	100-Sheet Single-Pass DADF
CAC/PIV¹	Capable	Capable
Wi-Fi	Optional (Wireless Network Adapter Required – 97N02470)	Optional (Wireless Network Adapter Required – 097N02470)
AOM Authorization	Not required	Not required
Paper Capacity (std/max)	251/1,451	650/2,850

Black-and-White Multifunction Printers



	XEROX® VERSALINK® B415 MULTIFUNCTION PRINTER	XEROX® VERSALINK® B625 MULTIFUNCTION PRINTER
TAA Part Number	B415/YDN	B625/YDN
Market Code	B415DNG	B625DNG
Print Speed (up to)	50 ppm	65 ppm
Duty Cycle (up to)*	175,000	300,000
Recommended Average Monthly Print Volume (up to)	20,000	30,000
Print Resolution (max)	1200 x 1200 dpi	1200 x 1200 dpi
Scan Resolution (max)	600 x 600 dpi	600 x 600 dpi
Media Sizes	3 x 5.8 in. to 8.5 x 14 in.	3 x 5 to 8.5 x 14 in.
Two-sided Output	Standard	Standard
Document Feeder Type	100-Sheet Single-Pass DADF	200-Sheet Single-Pass DADF
CAC/PIV ¹	Capable	Capable
Wi-Fi	Optional (Wireless Network Adapter Required – 097N02470)	Optional (Wireless Network Adapter Required – 097N02444)
AOM Authorization	Not required	Not required
Paper Capacity (std/max)	650/2,300	650/3,850

Color Advanced Multifunction Printers



XEROX® VERSALINK® C7100 COLOR MULTIFUNCTION PRINTER SERIES			
	C7120	C7125	C7130
TAA Part Number	C7120/YS	C7125/YS	C7130/YS
Market Code	C7120SG	C7125SG	C7130SG
Print Speed (up to)	20 ppm color/black	25 ppm color/black	30 ppm color/black
Duty Cycle (up to)*	87,000	107,000	129,000
Recommended Average Monthly Print Volume (up to)	5,500	6,250	7,000
Print Resolution (max)	1200 x 2400 dpi		
Scan Resolution (max)	600 x 600 dpi		
Media Sizes	3.5 x 3.9 to 11.7 x 17 in.		
Two-sided Output	Standard		
Document Feeder Type	130-Sheet Single-Pass DADF		
CAC/PIV ¹	Enabled		
Wi-Fi	Optional (Dual Band WiFi Kit Required – 497K23470)		
AOM Authorization	Required		
Paper Capacity (std/max)	1,140		



XEROX® ALTALINK® C8100 COLOR MULTIFUNCTION PRINTER SERIES					
	C8130	C8135	C8145	C8155	C8170
TAA Part Number	C8130/YT	C8135/YT	C8145/YH	C8155/YH	C8170/YH
Market Code	C8130TG	C8135TG	C8145HG	C8155HG	C8170HG
Print Speed (up to)	30 ppm color/black	35 ppm color/black	45 ppm color/black	55 ppm color/black	70 ppm color/black
Duty Cycle (up to)*	90,000	110,000	200,000	300,000	300,000
Recommended Average Monthly Print Volume (up to)	5,000-12,000	5,000-12,000	8,000-20,000	8,000-22,000	10,000-40,000
Print Resolution (max)	1200 x 2400 dpi				
Scan Resolution (max)	600 x 600 dpi				
Media Sizes	5.5 x 7.2 to 12 x 18 in. (Bypass Tray: 3.5 x 3.9 in. to 12.6 x 52 in.)				
Two-sided Output	Standard				
Document Feeder Type	130-Sheet Single-Pass DADF				250-Sheet Single-Pass DADF
CAC/PIV ¹	Capable				
Wi-Fi	Optional (Dual Band WiFi and Bluetooth Kit Required – 476K25190)				
AOM Authorization	Required				
Paper Capacity (std/max)	2,180/5,180		3,140/6,140		

*Maximum volume capacity expected in any one month. Not expected to be sustained on a regular basis.

Black-and-White Advanced Multifunction Printers



XEROX® VERSALINK® B7100 MULTIFUNCTION PRINTER SERIES			
	B7125	B7130	B7135
TAA Part Number	B7125/YS	B7130/YS	B7135/YS
Market Code	B7125SG	B7130SG	B7135SG
Print Speed (up to)	25 ppm	30 ppm	35 ppm
Duty Cycle (up to)*	107,000	129,000	153,000
Recommended Average Monthly Print Volume (up to)	13,000	15,000	17,000
Print Resolution (max)	1200 x 2400 dpi		
Scan Resolution (max)	600 x 600 dpi		
Media Sizes	3.5 x 3.87 to 11.7 x 17 in.		
Two-sided Output	Standard		
Document Feeder Type	110-Sheet DADF		
CAC/PIV ¹	Enabled		
Wi-Fi	Optional (Dual Band WiFi Kit Required – 497K23470)		
AOM Authorization	Required		
Paper Capacity (std/max)	1,140 /5,140		



XEROX® ALTALINK® B8100 MULTIFUNCTION PRINTER SERIES			
	B8145	B8155	B8170
TAA Part Number	B8145/YH	B8155/YH	B8170/YH
Market Code	B8145HG	B8155HG	B8170HG
Print Speed (up to)	45 ppm	55 ppm	72 ppm
Duty Cycle (up to)*	200,000	250,000	300,000
Recommended Average Monthly Print Volume (up to)	15,000-50,000	20,000-75,000	25,000-100,000
Print Resolution (max)	1200 x 2400 dpi		
Scan Resolution (max)	600 x 600 dpi		
Media Sizes	5.5 x 7.2 to 12 x 18 in. (Bypass Tray: 3.5 x 3.9 in. to 12.6 x 52 in.)		
Two-sided Output	Standard		
Document Feeder Type	130-Sheet Single-Pass DADF		250-Sheet Single-Pass DADF
CAC/PIV ¹	Capable		
Wi-Fi	Optional (Dual Band WiFi and Bluetooth Kit Required – 476K25190)		
AOM Authorization	Required		
Paper Capacity (std/max)	3,140/6,140		

*Maximum volume capacity expected in any one month. Not expected to be sustained on a regular basis.

Call 800-835-6100 for product information.

¹ Enabled indicates this feature is standard. Requires activation via Embedded Web Server.
Capable indicates this feature is optional. Requires activation via purchasable Feature Installation Key.