

LG ProBeam BU60PSM Laser Projector

Sharp 21:9 Images and Installation Flexibility

KEY FEATURES

Key Features

- Sharp 4K UHD with native 21:9 support
- Bright images with 6,000 lumens
- Mercury-free laser for virtually maintenance-free operation

Excellent for:

- Office collaboration rooms
- Hotel conference centers and meeting rooms



The LG ProBeam BU60PSM laser projector is an ideal solution for enterprise companies looking to create modern collaboration meeting rooms for their hybrid workforce. With full resolution 21:9 native aspect and up to 4K UHD resolution, the LG ProBeam BU60PSM is an ideal projector solution that makes it easy to use current remote meeting solutions and versatile enough to deliver high resolution images.

21:9 Aspect Ratio and Front Row Experience

The LG ProBeam BU60PSM brings 21:9 ultra-wide resolution to the business environment, which is ideal for users of Microsoft® Teams interested in the new Front Row layout experience. It can fill a hybrid collaboration room with a 285" 21:9 image.




Hybrid Meeting

Advanced Features

The LG ProBeam BU60PSM features a reliable laser light source which eliminates a projector lamp. It also has a lot of included built-in features like two 5W speakers, Wi-Fi and Bluetooth.

4K Ultra High-Def Resolution

The 6,000 lumen LG ProBeam BU60PSM can deliver a truly immersive experience with an incredible 8.3 million pixel 4K UHD resolution (3840 x 2160). Image details will show up sharp and clear.



Office Collaboration

Installation Flexibility

The LG ProBeam BU60PSM is designed for easy installation. With both horizontal and vertical lens shift as well as a 1.6x zoom and 12-point edge adjustment, it can be easily installed and tuned for a perfect fit. Plus with 2 HDMI ports and HDBaseT support the LG ProBeam BU60PSM provides connectivity flexibility.

LG ProBeam BU60PSM Laser Projector


PROJECTION SYSTEM	Resolution ¹	21:9 Ultra Wide (2560 x 1080)	INPUTS / OUTPUTS	Connection Terminals	HDMI 2.0 (x2), USB Type-A (x2), RJ45 (x2), HDBaseT, RS-232, Audio Out (3.5mm)
	Resolution Max ²	4K UHD (3840 x 2160)		USB Plug & Play	Movie, Music, Photo, Office file
	Brightness ³	6,000 ANSI lumens	AUDIO	Sound	10W (5W+5W)
	Throw Distance	Standard Throw		Wireless	WiFi & Bluetooth
	Light Source	Laser (up to 20,000 hours)	POWER	Power Consumption	440W
	Contrast Ratio	3,000,000:1		Standby Power Consumption	Less than 0.5W
	Throw Ratio	1.30 – 2.08	DIMENSIONS/ WEIGHT	Dimensions (W x D x H)	14.6 x 11.4 x 6.1 in 370.8 x 289.6 x 154.9 mm
	Zoom	1.6x		Weight	21.4 lbs 9.7 kg
	Keystone	12-Point Keystone Adjustment	FEATURES	User Interface Platform	webOS 4.5
	Screen Size	40" to 300"		Internet Browser	Yes
	Lens Shift	H: 20%, V: 50%	OTHER	Warranty	3 Year Limited/15,000 hours
	HDR	HDR10		Assembled In	Korea (ROK)
	Noise	29dB to 33dB			

¹ Default: EDID value. User selectable.

² The resolution is based on the number of discrete pixels projected on screen (4K : 8.3 million, Full HD : 2.1 million, HD : 0.9 million)

³ The Brightness (ANSI Lumen) is based on the perceived brightness of projected image

Dimension (unit: mm)



Connectivity

