



SPECIFICATIONS

USB ports	2 x USB 2.0 Type-A 1 x USB 2.0 Type-B Upstream 1 x USB 2.0 Type-C (PD 65W)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive Sync compatible
ACTIVATED RANGE	48~155Hz
Adobe RGB / DCI-P3 / sRGB	90% / 94% / 118%
Dimension (W x D x H)	945.22 x 289.63 x 530.29 mm / 945.22 x 83.32 x 416.12 mm (without stand)
Control	5-Way Navigator Joystick
Console Mode	2K Resolution PS5™ Optimization FHD @ 120Hz * All trademarks and the registered trademarks are the property of their respective owners.
Frameless Design	Yes

CONNECTIONS



1. 5-way Joystick Navigator
2. AC Power Jack
3. Headphone Out
4. HDMI™ (2.0b) x 2
5. DisplayPort (1.4a)
6. USD Type-C (DP alt)
7. USB 2.0 Type-B
8. USB 2.0 Type-A x 2

FEATURES

IPS PANEL

IPS

Wider viewing angles and the most realistic and accurate colors.

UWQHD

3440 x 1440

UWQHD (3440 x 1440)

Game titles will even look better, displaying more details due to the WQHD (3440 x 1440) resolution.

155 Hz

155Hz High RefreshRate

Experience smooth gaming with a blazing fast refresh rate, that gives you the upper hand in fast-moving games.

1ms

1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



KVM

Control multiple devices via one set of keyboard, mouse, and MSI gaming monitor.



Type-C 65W PD

Built-in a USB Type-C connection with 65W power delivery allows you to effortlessly connect to and charge your devices.