




SPECIFICATIONS

PANEL SIZE	27"
PANEL RESOLUTION	2560 x 1440 (WQHD)
REFRESH RATE	75Hz
RESPONSE TIME	1ms (MPRT) / 4ms (GTG)
PANEL TYPE	IPS
VIEWING ANGLE	178°(H) / 178°(V)
ASPECT RATIO	16:9
CONTRAST RATIO	1000:1
sRGB	102% (CIE 1976)
ACTIVE DISPLAY AREA (MM)	596.736(H) x 335.664(V)
PIXEL PITCH (H X V)	0.2331(H) x 0.2331(V)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	16.7M
COLOR BIT	8 bits
VIDEO PORTS	2x HDMI™ (1.4b) 1x DisplayPort (1.2a)
AUDIO PORTS	1x Headphone-out
KENSINGTON LOCK	Yes
SPEAKER	2x 2W
VESA MOUNTING	75 x 75 mm
POWER TYPE	External Adaptor (12V 3A)
POWER INPUT	100~240V, 50~60Hz
DYNAMIC REFRESH RATE TECHNOLOGY	AMD FreeSync™
ADJUSTMENT (TILT)	-5° ~ 20°
ADJUSTMENT (SWIVEL)	-30° ~ 30°
ADJUSTMENT (PIVOT)	-90° ~ 90°
ADJUSTMENT (HEIGHT)	0 ~ 100 mm
DIMENSION (W X H X D)	613.50 x 413.40 x 200.80 mm (24.15 x 16.28 x 7.91 inch)
CARTON DIMENSION (W X H X D)	841 x 448 x 131 mm (33.11 x 17.64 x 5.16 inch)
WEIGHT (NW / GW)	5.67 kg (12.5 lbs) / 7.6 kg (16.76 lbs)
CERTIFICATES	CB/CE Energy Star

FEATURES



27" WQHD 1440P

View your applications, spreadsheets and more with a perfect 27 inches screen with a breathtaking viewing experience that comes with WQHD resolution



IPS Grade Panel

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best while creating your own on-line video



Less Blue Light PRO

Use a hardware solution to reduce the light emission in the blue-violet region of the blue light spectrum (wavelength 415 to 455 nm).



Anti-Flicker technology


MSI Anti-Flicker technology provides a very comfortable viewing experience by reducing the amount of screen flicker.



Anti-Glare Display Design

An anti-glare display makes viewing the display more pleasant for users and reduces eyestrain for users

Anti-Glare




Adjustable Stand

Adjust the stand to the angle that is most suitable for you to keep yourself work comfortably.



75Hz High Refresh Rate

Experience smooth gaming with a blazing fast 75Hz refresh rate, that gives you the upperhand in fast moving games.



Display Kit Support

Providing the most convenient tool, the proper color & display mode to you while working with it everyday.



Built-In Speaker

Built-in speakers allow you to listen clearly without connecting external speakers.

VIDEO INPUT COMPATIBILITY

PC, Mac, PS5™, PS4™, Xbox,
Mobile, Notebook
* All trademarks and the registered
trademarks are the property of their
respective owners.

Note

HDMI™ : 2560 x 1440 (Up to 75Hz) □
DisplayPort: 2560 x 1440 (Up to
75Hz)
Adaptive-Sync support

CONNECTIONS



1. 2x HDMI™ (1.4b)
2. 1x DisplayPort (1.2a)
3. 1x Headphone-out
4. 1x DC-in
5. 1x Kensington Lock