



---

# Lexmark CX737adzse

All about performance and versatility

---



## Lexmark CX737adzse

The Lexmark CX737adzse color printer is versatile for both traditional and specialized media to meet a variety of business requirements. Designed for customers who require mid-to-large workgroup color devices, with monthly print volumes up to 20,000 pages. Unique technological approach offers exceptional print performance in off-standard printing such as greeting cards, pill pack labels, hazardous materials labeling and a whole range of narrow printing uses at speeds up to 52/50 ppm (letter/A4) \* and 25 ppm (narrow).

### Lexmark's new VariTherm technology

- ▶ Lexmark's new VariTherm™ technology senses media size and adjusts heating for the media width to offer exceptional print performance on media narrower than 8.5 x 11 inches or A4.
- ▶ Particularly suited to industries such as healthcare (medicine labels, chart cards, badge media), manufacturing (paint can labels, lumber and steel tags, bar codes), and retail (signage, bottle and box labels).

### Security features protect your data, your device and your network

- ▶ Security ecosystem is designed to overcome the most complex data challenges.
- ▶ Includes standard Trusted Platform Module\*\* that stores encryption keys on separate hardware from the data, along with authentication and system integrity checks.
- ▶ Cryptographic capabilities create a unique digital fingerprint.

### Easy to manage without burden on IT staff

- ▶ Our sophisticated, IoT-enabled printers are loaded with sensors that continuously monitor hundreds of data points.
- ▶ When you connect your device to Lexmark Cloud Services, you can optimize performance and uptime with additional features like predictive service and automatic supplies replenishment.

### Built-in workflow solutions work for your business

- ▶ Includes standard access to Scan Center, an easy-to-use app that simplifies routing to multiple destinations simultaneously.
- ▶ Shortcut Center is also included, allowing you to create

personalized shortcuts for frequent copy, fax and email tasks.

- ▶ Embedded solutions framework allows you to add apps that matter to your business; choose from our library or compose your own.



### Keep the productivity flowing

- ▶ Maximize productivity with single-pass two-sided scanning with ultrasonic multifeed detection for fast and reliable scanning.
- ▶ The Intelligent Storage Drive (ISD) provides solid state storage with activation-ready preloaded add-on solutions.
- ▶ A large, button-free touchscreen helps users intuitively complete every task, from the basic to the complex.

### Professional color for all your print jobs

- ▶ Enjoy vibrant color with standard advanced features like PANTONE® calibration and Lexmark Named Color Replacement for consistent branding and professional appearance.
- ▶ Models ship with 5000-page black/color cartridges\*\*\*
- ▶ Cartridges are also available with yields up to 28,000/16,200 black/color\*\*\*


This is a Class A device according to international electromagnetic emissions standards (i.e. FCC Rules, EN 55022/EN 55032, etc.). Class A products are intended for use in non-residential/non-domestic environments. Use of a Class A product in residential/domestic environments may cause interference to radio communications and require corrective measures.

\* Print speeds measured in accordance with ISO/IEC 24734 (ESAT). For more information see: [www.lexmark.com/ISOspeeds](http://www.lexmark.com/ISOspeeds).

\*\* The Trusted Platform Module (TPM) is not available in some countries.

\*\*\* Average continuous black or continuous composite color (CMY) declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19798. Actual yield will vary considerably based upon many factors. See [www.lexmark.com/yields](http://www.lexmark.com/yields) for more information.

# Lexmark CX737adzse



- 1 Multifunction product with 10-inch (25 cm) touch screen  
24.44 x 18.85 x 20.9 in.
- 2 550-Sheet tray with 100-sheet multipurpose feeder  
Dimensions included as part of base model
- 3 550-Sheet Tray  
4.7 x 18.23 x 19 in.  
119 x 463 x 483 mm
- 4 550-Sheet Tray  
4.7 x 18.23 x 19 in.  
119 x 463 x 483 mm
- 5 550-Sheet Tray  
4.7 x 18.23 x 19 in.  
119 x 463 x 483 mm

- 6 550-Sheet Tray  
4.7 x 18.23 x 19 in.  
119 x 463 x 483 mm
- 7 Adjustable Stand  
20.5 x 25.7 x 24.6 in.  
521 x 653 x 625 mm
- 8 Convenience Stapler LV  
3.23 x 4.29 x 4.77 in.

Standard  
 Optional

<b>P/N</b> 47C9700	<b>Hardware</b> Lexmark CX737adzse
<b>P/N</b> 71C0W00	<b>Supplies</b> Lexmark CS/CX730, 735, C/ XC4342, C4352 170K Waste Container
71C0Z10	Lexmark CS/CX730, 735, C/ XC4342, C/XC4352 Black 150K Imaging Unit
71C0Z50	Lexmark CS/CX730, 735, C/ XC4342, C/XC4352 Color (CMY) 150K Imaging Unit
71C10C0	Lexmark CS/CX730, 735 Cyan Return Program 5K Toner Cartridge
71C10K0	Lexmark CS/CX730, 735 Black Return Program 5K Toner Cartridge
71C10M0	Lexmark CS/CX730, 735 Magenta Return Program 5K Toner Cartridge
71C10Y0	Lexmark CS/CX730, 735 Yellow Return Program 5K Toner Cartridge
81C0X10	Lexmark CX735 Black 28K Toner Cartridge
81C0X20	Lexmark CX735 Cyan 16.2K Toner Cartridge
81C0X30	Lexmark CX735 Magenta 16.2K Toner Cartridge
81C0X40	Lexmark CX735 Yellow 16.2K Toner Cartridge
<b>P/N</b> 40C2100 47C4500	<b>Paper Handling</b> 550-Sheet Tray Convenience Stapler
<b>P/N</b> 27X0400 57X0070	<b>Memory Options</b> 500+ GB Hard Disk Removable Hard Disk Enclosure Kit
<b>P/N</b> 57X0225 57X0235	<b>Application Solutions</b> Desktop Contactless Reader Contactless Front Solutions Module (Primary)
57X0300 57X0301	Contact Authentication Device Contactless Authentication Device
82S1203 82S1204	IPDS License Bar Code License
<b>P/N</b> 1021294 27X0823	<b>Connectivity</b> USB Cable (2-meter) MarkNet N8370 Wireless for CS720, CS725, CX725
27X6410	Lexmark MarkNet N8372 802.11 a/b/g/n/ac Wireless Print Server
57X7020 SPD0001	English Keyboard Kit Surge Protective Device, 110-120V
<b>P/N</b> 40C2300	<b>Furniture</b> Adjustable Stand

Product Specifications		Lexmark CX737adzse
<b>Printing</b>		
Display	Lexmark e-Task 10-inch (25 cm) class color touch screen	
Print Speed	Up to: Black: 52 ppm <sup>1</sup> (Letter) / Color: 52 ppm <sup>1</sup> (Letter)	
Time to First Page	As fast as: Black: 6.6 seconds / Color: 6.6 seconds	
Print Resolution	Black: 1200 x 1200 dpi, 4800 CQ (2400 x 600 dpi) / Color: 4800 CQ (2400 x 600 dpi), 1200 x 1200 dpi	
Memory	Standard: 2048 MB / Maximum: 2048 MB	
Hard Disk	Intelligent Storage Drive included; Magnetic Hard Disk available	
Recommended Monthly Page Volume	2000 - 20000 pages <sup>2</sup>	
Maximum Monthly Duty Cycle	Up to: 150000 pages per month <sup>3</sup>	
<b>Copying</b>		
Copy Speed	Up to: Black: 52 cpm <sup>1</sup> (Letter) / Color: 52 cpm <sup>1</sup> (Letter)	
Time to First Copy	As fast as: Black: 6.7 seconds / Color: 6.8 seconds	
<b>Scanning</b>		
Scanner Type / ADF Scan	Flatbed scanner with ADF / DADF (single pass Duplex)	
A4/Ltr Duplex Scan Speed	Up to: Black: 98 / 104 sides per minute / Color: 98 / 104 sides per minute	
A4/Ltr Simplex Scan Speed	Up to: Black: 49 / 52 sides per minute / Color: 49 / 52 sides per minute	
ADF Paper Input Capacity	Up to: 100 pages 20 lb or 75 gsm bond	
<b>Faxing</b>		
Modem Speed	ITU T.30, V.34 Half-Duplex, 33.6 Kbps	
<b>Supplies<sup>4</sup></b>		
Laser Cartridge Yields	up to: 28,000 <sup>5</sup> -page Black Extra High Yield Cartridge / up to: 16,200 <sup>5</sup> -page Color (CMY) Extra High Yield Cartridges	
Imaging Unit Estimated Yield	Up to: 150000 pages, based on 3 average letter/A4-size pages per print job and ~ 5% coverage <sup>6</sup>	
Cartridge(s) Shipping with Product	5,000 <sup>5</sup> -page Black and Color (CMYK) Return Program Toner Cartridges <sup>5</sup>	
<b>Paper Handling</b>		
Included Paper Handling	100-Sheet Multipurpose Feeder, Integrated Duplex, 300-Sheet Output Bin, 550-Sheet Input	
Optional Paper Handling	550-Sheet Tray	
Paper Input Capacity	Up to: Standard: 650 pages 20 lb or 75 gsm bond / Maximum: 2850 pages 20 lb or 75 gsm bond	
Paper Output Capacity	Up to: Standard: 300 pages 20 lb or 75 gsm bond / Maximum: 300 pages 20 lb or 75 gsm bond	
Media Types Supported	Vinyl Labels, Banner Paper, Paper Labels, Card Stock, Plain Paper, Envelopes, Refer to the Paper & Specialty Media Guide	
Media Sizes Supported	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Letter, B5 Envelope, Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope	
<b>General Information<sup>7</sup></b>		
Standard Ports	Gigabit Ethernet (10/100/1000), Front USB 2.0 Specification Hi-Speed Certified port (Type A), Rear Hi-Speed USB Port Compatible with USB 2.0 Specification (Type A), USB 2.0 Specification Hi-Speed Certified (Type B), One Internal Card Slot	
Optional Network Ports	Internal MarkNet N8370 802.11b/g/n/a Wireless, NFC	
Noise Level	Operating: 53 dBA (Print) / 56 dBA (Copy) / 51 dBA (Scan)	
Specified Operating Environment	Humidity: 8 to 80% Relative Humidity / Temperature: 10 to 32°C (50 to 90°F) / Altitude: 0 - 2896 Meters (9,500 Feet)	
Limited Warranty	See Statement of Limited Warranty: 1-Year Onsite Service, Next Business Day	
Size / Weight	H x W x D: 24.44 x 18.85 x 20.9 in. / 87.08 lb.	
ENERGY STAR Typical Electricity Consumption	TEC: 0.69 kilowatt-hours per week	

All information is subject to change without notice. Lexmark is not liable for any errors or omissions.

<sup>1</sup> Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: [www.lexmark.com/ISOspeeds](http://www.lexmark.com/ISOspeeds).

<sup>2</sup> "Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. <sup>3</sup> "Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. <sup>4</sup> Product functions only with replacement cartridges designed for use in a specific geographical region. See [www.lexmark.com/regions](http://www.lexmark.com/regions) for more details. <sup>5</sup> Average continuous black or continuous composite CMY declared cartridge yield up to this number of standard pages in accordance with ISO/IEC 19798. <sup>6</sup> Actual Yield may vary based on other factors such as device speed, paper size and feed orientation, toner coverage, tray source, percentage of black-only printing and average print job complexity. <sup>7</sup> Printers are sold subject to certain license/agreement conditions. See [www.lexmark.com/printerlicense](http://www.lexmark.com/printerlicense) for details.

This is a Class A device according to international electromagnetic emissions standards (i.e. FCC Rules, EN 55022/EN 55032, etc.). Class A products are intended for use in non-residential/non-domestic environments. Use of a Class A product in residential/domestic environments may cause interference to radio communications and require corrective measures.

© 2023 Lexmark. All rights reserved.

Lexmark, the Lexmark logo, Unison and VariTherm are trademarks of Lexmark International, Inc., registered in the United States and/or other countries.

PANTONE® is the property of Pantone LLC. All other trademarks are the property of their respective owners. Apple and AirPrint are trademarks of Apple Inc., registered in the U.S. and other countries and regions. MOPRIA®, the Mopria® Logo, and the Mopria Alliance™ word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited.

