


Designed to offer an exceptional user experience with superior performance and cutting-edge features for next-level productivity




reddot winner 2023




12th Gen Intel
Processors


DDR4
Memory


PCIe 4.0x4
M.2 SSD


2.5G LAN


Wi-Fi 6E
802.11ax


Kensington
Lock


4K


4 Displays


HDMI CEC

Performance for any workplace

- Powered by 12th Generation Intel® Core™ / Celeron® processors
- Maximum 32GB DDR4 memory support
- Supports PCIe Gen4 x4 M.2 SSD
- Up to Intel® Iris® Xe graphics

Built for efficiency

- Built-in Qi certified 15W wireless charger ¹
- Ultra-capable Wi-Fi 6E wireless network and 2.5G wired network
- Thunderbolt 4 for fast and versatile connectivity

Simplified IT management


- Always up-to-date operating system
- Centralized cloud management via Google Admin Console
- Secure by design with multilayered defense
- Support Chrome Enterprise & zero-touch enrollment

ASUS Chromebox 5



Model		ASUS Chromebox 5 (Core-i)	ASUS Chromebox 5 (Celeron)
OS		Chrome Enterprise or ChromeOS	
CPU		12th Generation Intel® Core™ i7-1260P/ i5-1240P/ i3-1220P/ Celeron® 7305	
Chipset		Integrated	
Graphics		Integrated - Intel® Iris® Xe Graphics (i7/ i5) Integrated - Intel® UHD Graphics (i3/ Celeron)	
Memory		2 x DDR4 SO-DIMM slots for DDR4 3200 MHz, 2 x 16GB (Max)	1 x DDR4 SO-DIMM slots for DDR4 3200 MHz, 1 x 16GB (Max)
Storage		1 x M.2 2280 PCIe Gen4 x4 slot for 128GB - 512GB NVMe SSD	
Wireless Network		M.2 2230 Intel® Wi-Fi 6E AX211 (802.11ax), 2x2, and Bluetooth® 5	
LAN		Realtek® LAN, 10/100/1000/2500 Mbps	
Interface	Front I/O	2 x USB 3.2 Gen2 (10 Gbps, with BC1.2) 1 x Audio Jack(Line out/ Mic in/ Headphone out) 1 x Micro SD card reader	
	Side I/O	*All data transfer speed is according to original spec, actual performance may vary depending on objective environmental changes. 1 x Kensington Lock 1 x Recovery button	
	Rear I/O	2 x USB 3.2 Gen1 (5 Gbps) 1 x Thunderbolt™ 4 USB-C (40Gbps, supports USB 4.0/DP1.4/PD in) 2 x HDMI 2.1 Port 1 x DisplayPort 1.4 1 x RJ45 2.5G LAN 1 x DC-in	
Wireless Charging		Qi wireless fast charging up to 15W (Optional)	
Power Supply		20Vdc, 7.5A, 150W	19Vdc, 3.42A 65W
Physical	Dimension	166.5 x 165.8 x 45.9 mm (1.27L)	
	Weight	0.8 kg	
Max Resolution	HDMI	3840 x 2160 @ 60Hz	
	DP	3840 x 2160 @ 60Hz	
	Thunderbolt	3840 x 2160 @ 60Hz	
Temperature	Operating	0°C~50°C	
	Storage	-40°C~85°C	
Humidity		0%~95% Relative Humidity	
Acoustic	Idle mode	<25 dBA	
	Full loading	<45 dBA * Test results will vary slightly depending on the HDD/SSD SKU selected by customer	
Certificates		BSMI / CB / CE / FCC / UL / Energy Star / C-Tick / WiFi / RF / VCCI	

Overview:



Accessories list:



- Power Cord
- AC Adapter
- Quick Start Guide & Warranty Card
- VESA Mount Kit (Optional)
- Wired Keyboard & Mouse (Optional)