



8MP (4K) IP Bullet Camera with Advanced Analytics, NDAA Compliant

O8B9M

2.8-12mm motorized lens, white housing



Features

- Captures up to 8MP @ 30fps
- Up to 4x optical zoom
- Built-in standard PoE (IEEE 802.3af)
- True Day/Night operation (IR cut filter)
- IR range: up to 229' (depending on scene reflection)
- True WDR operation
- Micro SD card slot up to 256GB (card not included)
- Conformant with ONVIF G/S/T
- Line crossing, region intrusion, and video blurring detection
- Face/People/Vehicle/Scene Change Detection*
- Two-way audio support
- IP67 Weather Resistance
- Junction box included (works with NPT/BSP specifications)
- 5 year warranty
- NDAA Compliant**
- Conformant with ONVIF Profile G/S/T



Included Junction Box

Camera Specifications

Image Sensor	Progressive scan 1/2.8" CMOS, 8MP
Maximum Resolution	3840 x 2160 (8MP)
Minimum Illumination	0.015lux @ F1.4, AGC ON; 0 lux with IR
Field of View (H)	(H): 96° ~ 32°; (V): 64° ~ 18.4°; (D): 103.8° ~ 36.5°
Image Settings	Region of interest, Saturation, Brightness, Chroma, Contrast, Wide Dynamic, Defog, Sharpen, Noise Reduction, Corridor Mode (Image rotation)
Day/Night	Smart IR with cut filter
Compensation	True WDR / BLC / HLC
Electronic Shutter Speed	1 sec. ~ 1/100000 sec.
DNR	3D DNR
Angle Adjustment	Pan 0° - 360°, Tilt 0° - 90°, Rotation 0° - 360°

Video Specifications

Main Stream Resolution	8MP/6MP/5MP/4MP/2K/3MP/1080P/720P (1~30fps)
Sub Stream Resolution	720P/D1/480 x 240 (1~30fps)
Third Stream	D1/CIF/480x240 (1~30fps)
Compression	H.265, H.264
Bitrate Control	VBR, CBR (64Kbps ~ 12Mbps)
Multiple Streaming	3 streams

Network Specifications

Protocols	UDP, DHCP, NTP, RTSP, PPPoE, DDNS, SMTP, FTP, 802.1x, UPnP, HTTP, HTTPS, QoS
DDNS support	Speco DDNS (free of charge)
Security	User ID & Password protection, IP/Mac address filtering, digest authentication
User Access	Max. 10 simultaneous users (Actual number of users may vary depending on bandwidth)

Interfaces

Network	RJ45 jack
Power	DC jack
Microphone Input	3.5mm
Audio Output	3.5mm
Card Slot	MicroSD, up to 256GB (not included)
Video Out	CVBS output (BNC x 1)
Alarm	1 CH alarm input; 1 CH alarm output
Reset	Yes

Audio Specifications

Audio Compression	G.711A / G.711U
-------------------	-----------------

Client Specifications

Web Browser Support	Chrome, Edge, Safari, Internet Explorer
PC Application	SecureGuard® VMS, SecureGuard® CMS
Mobile	SecureGuard® Client, Speco Blue (iPhone® and Android™)

System Specifications

PoE	Standard (IEEE 802.3af)
Perimeter Protection	Line crossing, region entrance/exiting/intrusion (people/vehicle/motorcycle/bicycle) detection
Target Counting	Line crossing people/motor vehicle/motorcycle/bicycle
Exception Detection	Scene change video blur and video color cast detection
Face Detection	Face detection and face capture
Alarm Triggers	Motion, Sensor Alarm, Analytics, SD card error
Image Settings	Watermark, IP address filtering, video mask, password protection

Operating & Unit Specifications


Power	PoE, 12VDC (power supply not included)
Power Consumption	<12W
Operating Temperature	-40°F ~ 140°F (-40°C ~ 60°C)
Operating Humidity	Less than 95 % (non-condensing)
Unit Dimensions	3.93" (W) x 11.0" (D) x 3.5" (H); (100.3mm x 279.5mm x 88.9mm)
Unit Weight	2.2 lbs. (1.0kg)
Certifications	FCC, RoHS

*with compatible Speco recorder

**Products are in compliance with NDAA Section 889 Part B Guidelines



Cameras Interfaces



Optional Accessories



ONVIF is a trademark of Onvif, Inc. Chrome and Firefox use Java which requires an initial internet connection. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Amazon's trademark is used under license from Amazon.com, Inc. or its affiliates. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 1/17/23

Apps available from the following:



ONVIF® 800-645-5516 • Fax: 631-957-9142 or 631-957-3880 • specotech.com

speco technologies®