



SAKER PLUS SERIES

The **Saker Plus Series** is a commercial grade electric projection screen suitable for big rooms. It consists of an aluminum heavy duty housing that permits a suspended ceiling installation using a pair of eye-bolts on each end of the case. Its list of complimentary features include Infra-red and Radio Frequency remote controls, a wireless 12 volt projector trigger and a detachable wall box controller.

The MaxWhite® front projection material is GREENGUARD® Gold Certified. It has a wide viewing angle and a 1.1 gain reflectivity.



Screen Material

- MaxWhite® 1.1 Gain matte white front projection material - Performs best in a light controlled environment
- Wide diffusion uniformity allows viewers to see a clear picture from any angle
- Not compatible with Ultra/Short-throw Projectors
- Standard black masking borders absorb projector overshoot and enhance picture contrast
- Black backing eliminates light penetration for superior color reproduction
- Available in the following diagonal sizes:
 - 200", 235" and 265" in 16:9 format
 - 235" and 265" in 4:3 aspect ratio

Design & Control System

- Heavy-duty aluminum moisture resistant white case
- Ring-bolts included on case for suspended ceiling installation
- Plug & Play design with built-in low voltage control system
- Includes handheld Infrared (IR) and Radio Frequency (RF) remote controls, and a wall box controller for manual on-wall operation.
- User-friendly programmable vertical drop position (RC1 Version)
- Wall box controller is detachable for a clean look
- Built-in selectable channels allow one RF remote programming to control multiple screens (RC1 Version Only)
- 12v trigger feature allows the screen's UP/DOWN operation to synchronize with the projector's power cycle
- 5-year limited manufacturer's warranty