



SPECIFICATIONS


Panel Size	23.8" (60cm)
Active Display Area (mm)	527.04(H) x 296.46(V)
Curvature	Flat
Panel Type	IPS
Panel Resolution	1920 x 1080 (FHD)
Pixel Pitch (H x V)	0.2745(H)x0.2745(V)
Aspect Ratio	16:9
Brightness (nits)	250
Contrast Ratio	1100:1
DCR	100000000:1
Signal Frequency	30~100 KHz(H) / 48~170 Hz(V)
Refresh Rate	170Hz
Response time	1ms (MPRT)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive sync
HDR Support	N/A
Video ports	2x HDMI™ (Supports FHD@144Hz as specified in HDMI™ 1.4b) 1x DP (Supports FHD@170Hz as specified in DisplayPort 1.2a with overclocking)
USB ports	N/A
Audio ports	1x Earphone out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	86.52% / 81.64% / 102.58%
Surface Treatment	Anti-glare
Display Colors	16.7M
Power Type	External Adaptor 20V 2.25A
Power Input	100~240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	-45° ~ 45°
Adjustment (Pivot)	-90° ~ 90°
Adjustment (Height)	0 ~ 130 mm
Kensington Lock	Yes
Control	5-way OSD navigation joystick
ACTIVATED RANGE	48 to 170Hz
Color Bit	8 Bits
Power consumption	On-mode: 18 (KWh/1000h) / Off-mode: 0.3 (KWh/1000h)

FEATURES

- eSports Gaming**
 MSI eSports gaming monitor will enhance your competitive gameplay to ensure you are always at your best levels.
- IPS PANEL**
 Wider viewing angles and the most realistic and accurate colors.
- 170Hz High Refresh Rate**
 Experience smooth gaming with 170Hz refresh rate, that gives you the upperhand in fast moving games.
- 1ms Fast Response Time**
 Eliminate screen tearing and choppy frame rates with 1ms response time.
- Wide Color Gamut**
 Game colors and details will look more realistic and refined, to push game immersion to its limits.
- Night Vision**
 See every detail clearly in the dark, helping you find and attack enemies before they notice.
- Console Mode - FHD only**
 Best solution for console users: FHD@120Hz
- Adjustable Stand**
 Maximize your productivity and comfort with the adjustable stand.

Dimension (W x D x H)	540.2 x 233.7 x 399.2 mm 540.2 x 57.1 x 328.2 mm (Without stand)
Console Mode	Support FHD@120Hz
Frameless Design	Yes
PIP / PBP Function	N/A
VESA Mounting	100 x 100 mm
Weight (NW / GW)	3.5kg / 5.1kg without Stand: 2.5kg
Note	Display Port: 1920 x 1080 (Up to 170Hz By DP Over Clocking) HDMI™: 1920 x 1080 (Up to 144Hz) Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

CONNECTIONS



1. 5-way joystick navigator
2. DC jack
3. 2 x HDMI™ (1.4b)
4. 1 x Display Port (1.2a)
5. Headphone out
6. Kensington lock