



TS-855eU-8G

CPU	Intel® Atom® C5125 8-core processor, 2.8GHz
CPU Architecture	64-bit x86
Floating Point Unit	Yes
Encryption Engine	Yes (AES-NI)
System Memory	8 GB non-ECC SODIMM DDR4 (1 x 8 GB)
Maximum Memory	64 GB (2 x 32 GB)
Memory Slot	2 x SODIMM DDR4 Support ECC memory For dual-DIMM configuration, you must use a pair of identical DDR4 modules.
Flash Memory	5GB (Dual boot OS protection)
Drive Bay	8 x 3.5-inch SATA 6Gb/s, 3Gb/s The system is shipped without HDD. For the HDD compatibility list, please visit https://www.qnap.com/compatibility/
Drive Compatibility	3.5-inch SATA hard disk drives 2.5-inch SATA hard disk drives 2.5-inch SATA solid state drives
Hot-swappable	Yes
M.2 Slot	2 x M.2 2280 (PCIe Gen 3 x 4) Compatible with NVMe SSD PCIe Gen 3 and above. Please refer to https://www.qnap.com/compatibility/ for compatibility.
SSD Cache Acceleration Support	Yes
SR-IOV	Yes
2.5 Gigabit Ethernet Port (2.5G/1G/100M)	2 (2.5G/1G/100M/10M)
5 Gigabit Ethernet Port (5G/2.5G/1G/100M)	Optional via a network adapter

10 Gigabit Ethernet Port	Optional via a network adapter
25 Gigabit Ethernet Port	Optional via a network adapter
Wake on LAN (WOL)	Yes Only the 2.5GbE port
Jumbo Frame	Yes
PCIe Slot	2 x PCIe Gen3 (x4) Slot 1: PCIe Gen 3 (x4) Slot 2: PCIe Gen 3 (x4) Card dimensions for PCIe slot 1 : 97 x 68.9x 18.76 mm / 3.82 x 2.71 x 0.74 inches. Card dimensions for PCIe slot 2 : 210 x 68.9 x 18.76 mm / 8.27 x 2.71 x 0.74 inches.
USB 3.2 Gen 1 port	4
HDMI™ Output	Optional via a PCIe graphics card
Form Factor	2U Short Depth Rackmount
LED Indicators	HDD 1-8, Status, LAN, USB, Power
Buttons	Power, Reset
Dimensions (HxWxD)	3.49 × 17.01 × 11.71 inch
Weight (Net)	17.86 lbs
Weight (Gross)	21.16 lbs
Operating Temperature	0 - 40 °C (32°F - 104°F)
Storage Temperature	-20 - 70°C (-4°F - 158°F)
Relative Humidity	5-95% RH non-condensing, wet bulb: 27°C (80.6°F)
Power Supply Unit	250W PSU, 100 - 240V
Power Consumption: HDD Sleep Mode	49.799 W
Power Consumption: Operating Mode, Typical	79.113 W Tested fully populated with WD10EFRX hard drives.
Fan	3 x 60mm, 12VDC
System Warning	Buzzer
Standard Warranty	3
Max. Number of Concurrent Connections (CIFS) - with Max. Memory	2500

Note: Use only QNAP memory modules to maintain system performance and stability. For NAS devices with more than one memory slot, use QNAP modules with identical specifications.

Warning: Using unsupported modules may degrade performance, cause errors, or prevent the operating system from starting. QNAP reserves the right to replace partial parts or accessories if the original is no longer available from its manufacturer/supplier. Any replacement would be fully tested and verified to meet strict compatibility and stability guidelines and will deliver identical performance to the original.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Product images are for illustrative purposes only and may differ from the actual product. Due to differences in monitors, colors of products may also appear different to those shown on the site.

Designs and specifications are subject to change without notice.