



Poly Blackwire 8225 Microsoft Teams Certified USB-C Headset (772K5AA)



Overview

Stay distraction-free on calls

Is background noise affecting your productivity? Reduce noise and increase focus with the Poly Blackwire 8225 headset with a noise-canceling microphone enhanced with Acoustic Fence technology and advanced hybrid active noise canceling (ANC).

Sound like a winner

With the Blackwire 8225, your voice is the only thing heard, not the chaos around you. Its noise-canceling microphone with Acoustic Fence technology puts you in a quiet office, even if you're in a noisy kitchen.

Long-lasting comfort

The Blackwire 8225 is crafted from premium materials with a lightweight design. You will get a comfortable, customized fit using adjustment markers and 180° pivoting speakers. You'll fall in love with the aesthetic design and robust look and feel.

Stay focused

It's no secret that tuning out background noise makes you more productive. Hybrid active noise canceling (ANC) makes it easy to escape the noise around you. And three ANC settings mean you can fine-tune your level of quiet where you work.

Features

Advanced hybrid ANC

Optimize audio comfort and quality with advanced hybrid active noise canceling (ANC) by choosing between three settings.

Acoustic Fence technology

Reduce disruptions from close talkers and environmental noise with the flexible, noise canceling microphone enhanced with Acoustic Fence technology.

Connectivity options

Allows greater flexibility of use by offering choices: USB-A or USB Type-C®.

Lightweight design

Padded headband and soft leatherette ear cushions provide all day comfort.

Inline control

Easy-to-use inline call control with call answer / end, mute, volume up / down buttons and a three-setting ANC switch.

Certified for Microsoft Teams

Full Microsoft Teams certification takes your Microsoft Teams experience to the next level with a button for instant access to the app and more.

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Audio	Noise and echo reduction; Dynamic EQ optimized; Noise cancellation (NC)
Boom mic length (ft)	0.44 ft
Boom mic length (mm)	135 mm
Boom mic rotation	280°
Button user controls	Call answer/end; Mute; Volume +/-; Microsoft Teams; ANC: off, low, high
Cable length	63 cm (inline module to headset); 149 cm (USB to inline module); 219 cm (total USB to headset)
Cable length (imperial)	2.07 ft (inline module to headset); 4.89 ft (USB to inline module); 7.19 ft (total USB to headset)
Cartons per layer	10
Cartons per pallet	80
Color	Black
Compatibility	Compatible with PCs and desk phones with available USB Type-A port
Compatible Operating Systems	Windows 10; macOS
Connection type	USB Type-C®
Connection type	Wired USB Type-C®
Connects to	PC
Country of origin	Made in China or Mexico
Ear cushions	Artificial leather (surface material)
Headphone type	On-ear (binaural)
Impedance	32 ohm
Indicator light	On call
Management Software	Poly Lens; Poly Lens app (desktop)
Manufacturer Warranty	Poly standard two-year limited warranty
Microphone bandwidth	100 Hz to 10 kHz
Microphone type	Omnidirectional
Minimum System Requirements	USB Type-C® port
Minimum dimensions (W x D x H)	15.5 x 3.2 x 17.8 cm
Minimum dimensions (W x D x H)	6.1 x 1.25 x 7.1 in
Multiple order quantity	10
Package dimensions (W x D x H)	183 x 209 x 55 mm
Package dimensions (W x D x H)	7.2 x 8.22 x 2.16 in
Package weight	0.72 lb

Package weight	330 g
Pallet (layers)	8
Pallet dimensions	40 x 48 x 76.37 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 194 cm
Pallet weight	671.68 lb
Pallet weight	304.67 kg
Products per pallet	800
Products per pallet layer	100
Sensitivity (microphone)	10 dB SLR
Sensitivity (speaker)	6 dB RLR
Signal-to-noise ratio	>30 dB
Speaker size	32 mm
Special features	UC certified; Two LED indicators on speaker in call status
UC compatibility	Microsoft
UNSPSC code	43191638
Weight	0.41 lb (with cable); 0.32 lb (without cable)
Weight	0.185 kg (with cable); 0.144 kg (without cable)
What's in the box	User guide; Poly Blackwire 8225

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Services

Poly Services

★ : Recommended

Poly Support Services

3 year Poly+ Blackwire Service	PBLKWIRE312 ★
3 year Partner Poly+ Blackwire Service	PBLKWIRE362

Audio

★ : Recommended

Audio Accessories

Poly 2.5mm to QD Cable (0.45M)	85Q30AA
Poly 2.5mm to QD Cable (3M)	85Q32AA
Poly 2.5mm to QD Cable with Hookswitch (0.18M)	85Q35AA
Poly 2.5mm to QD Gold Cable (0.45M)	85S11AA
Poly 3.5mm to QD Cable (0.15M)	85Q37AA
Poly 3.5mm to QD Cable (3M)	85Q40AA
Poly 3.5mm to QD Cable for IP Touch (3M)	85Q43AA
Poly 4 Pin QD to 6 Pin QD Cable	85Q45AA
Poly 4 Pin QD to 6 Pin QD Cable (0.13M)	85Q47AA
Poly A10-11 QD to QD Adapter	85S27AA
Poly A10-12 Adapter (S1 Plug)	85S26AA
Poly A10-16 Adapter	85T17AA
Poly A10-16 Adapter (Bagged)	85T18AA
Poly AL10 Inline Audio Limiter	85S25AA
Poly Blackwire 3200 Leatherette Ear Cushions (2 Pieces)	85S24AA
Poly Blackwire 3200 USB-A Inline Controls	85R03AA
Poly Blackwire 3200 USB-C Inline Controls	85R04AA
Poly Blackwire 3300 Case	85R06AA
Poly Blackwire 3310/3320 Foam Ear Cushions (2 Pieces)	85S23AA
Poly Blackwire 3315/3325 Leatherette Ear Cushions (2 Pieces)	85S22AA
Poly Blackwire 435 Clothing Clip (1 Piece)	85S21AA
Poly Blackwire 5000 Leatherette Ear Cushions (2 Pieces)	85S19AA
Poly Blackwire 5200 USB-A Inline Controls	85Q62AA
Poly Blackwire 5200 USB-C Inline Controls	85Q64AA
Poly Blackwire 5200 Y Training Cable	85S08AA
Poly Blackwire 600/700 Leatherette Ear Cushions (2 Pieces)	85S18AA
Poly Blackwire 7225 Case	85Q69AA
Poly Blackwire 7225 Espresso Leatherette Ear Cushions (2 Pieces)	85S17AA
Poly Blackwire 7225 Sand Leatherette Ear Cushions (2 Pieces)	85S16AA
Poly Blackwire 8225 Leatherette Ear Cushions (2 Pieces)	783Q9AA

Poly Blackwire C310/320 Foam Ear Cushions (2 Pieces)	85S15AA
Poly CA22CD-DC Dual Channel Remote with Battery	85Q91AA
Poly CA22CD-SC Single Channel Remote with Battery	85Q92AA
Poly DA75 USB to QD Black Adapter TAA	786C6AA
Poly DA90 USB to QD Adapter	85T19AA
Poly HIC-1 Cable	85R30AA
Poly HIC-10 Cable	783S2AA
Poly HIS Cable TAA	783S3AA
Poly M15D Adapter	85Q54AA
Poly M22 Adapter	85T20AA
Poly M22 Adapter (Bilingual)	85Q15AA
Poly M22 High Gain Adapter	85Q17AA
Poly M22 High Gain Adapter (Bilingual)	85Q19AA
Poly M22 Narrowband Adapter	85T21AA
Poly M22 to 2.5mm Cable (0.5M)	85R36AA
Poly M22 to QD Cable	85R38AA
Poly M22 to QD Lightweight Cable	85R40AA
Poly MDA100 RJ9 Cable	85R42AA
Poly MDA500 Cable	85R46AA
Poly MDA500 USB-C to USB-A Cable	85R48AA
Poly MDA500 USB-C to USB-C Cable	85R50AA
Poly MDA524 USB-C	85Q24AA
Poly QD to QD Extension Cable (3M)	85R66AA
Poly QD to QD Lightweight Extension Cable with QD Lock	85R69AA
Poly U10 Lightweight Cable with QD Lock	85R85AA
Poly USB-A to USB-C Adapter	85Q48AA
Poly USB-C to USB-A Adapter	85Q49AA
Poly Y Training Cable	85S07AA
Poly Y Training Cable with QD Lock-Digital Headsets	85S09AA

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.