



DAYTONA

Stable, reliable POS terminal that's made to last

Great reliability in a robust form factor: DAYTONA is ideal for point-of-sale applications that require larger workload in multiple environments. The terminal is developed to support multiple types of software applications thanks to different CPU performance levels. DAYTONA establishes a new standard for touchscreen terminals, with top-notch RAM and SSD. Thanks to the easy-access SSD and RAM, service and upgrades are a breeze. This terminal is developed to be flexible, and can easily update to become your company's most loyal helper.



CHARACTERISTICS

1. Field upgradeable

Easily upgrade RAM and SSD **to increase system specifications**

2. USB-C on all 4 sides of the terminal for proprietary peripherals

Consolidate peripheral integrations **for attended and unattended applications**

3. Multiple operating systems

Compatible in both **Windows 10 IoT, Windows 11** (only i3 and i5 models), and **Linux**

4. Multiple CPU options

Celeron®, i3, and i5 configurations: keep consistent look and feel across your business environment

5. Cable management

Easily hide cables in the base **for a clean installation**

MARKETS

- Retail
- Hospitality
- Entertainment
- Gaming, Lottery and Betting

MODELS

- Windows® - J3455 8GB/128GB SSD - 4:3 (15")
 - Windows® - i3 8145UE 8GB/128GB SSD - 4:3 (15")
 - Windows® - i5 10210U 8GB/256GB SSD - 4:3 (15")
-

ACCESSORIES

- Second display 10.1"
 - Customer display LCM 2x20
 - MSR
-

TECHNICAL SHEET

	WINDOWS® - J3455	WINDOWS® - i3 8145UE	WINDOWS® - i5 10210U
Processor	Celeron® J3455, up to 2.3GHz	Core i3 8145UE, up to 3.90GHz	Core i5 10210U, up to 4.20GHz
TPM	N/A	TPM 2.0	TPM 2.0
Memory	8GB	8GB Up to 32GB	
Storage	2.5" SATA SSD, 128GB		2.5" SATA SSD, 256GB
I/O	USB: 3.0 x 4, 2.0 x 2, TypeC x 1 (TYPE C USB 2.0 HS only 5V/2A) Serial ports: RJ50 x 2 Display: HDMI x 1 up to 1920x1080 LAN: RJ45 x 1 Cash Drawer: RJ12 x 1	USB: 3.0 x 4, 2.0 x 2, TypeC x 1 (TYPE C USB 2.0 HS only 5V/2A) Serial ports: RJ50 x 1 Display: HDMI x 1 up to 1920x1080 LAN: RJ45 x 2 Cash Drawer: RJ12 x 1	
LCD	15" TFT		
Brightness	350 NITS		
Resolution	1024x768		
Touch screen	PCAP True Flat		
Speaker	1 x 3W		
Wireless	1 x WLAN 802.11 a/b/g/n/ac + Bluetooth® 4.2 (Optional)		
OS	Windows® 10 IOT	Windows® 10 IOT / Windows® 11	
Electrical specifications	Device: 60 W/12 V DC Jack Adapter Power supply: from 100 Vac to 240 Vac		
Dimensions	362 mm (L) x 210 mm (W) x 330 mm (H)		
Weight	4.9 Kg		

MODELS



934MS011500L33

PCPOS DAYTONA 15" NO OS SSD
128GB J3455 8GB



934MS011700L33

PCPOS DAYTONA 15" NO OS SSD
128GB i3-8145UE 8GB



934MS012200L33

PCPOS DAYTONA 15" WIN SSD
128GB J3455 8GB



934MS012400L33

PCPOS DAYTONA 15" WIN SSD
128GB i3-8145UE 8GB

Via Berettine, 2 - 43010 Fontevivo PR - VAT: IT02498250345 - TEL: +39 0521 680111 - FAX: +39 0521 610701 - UNIQUE CODE: 8RQN7AZ

The technical data on this website are not binding and may be changed without advanced notice.

Last update: 05 January 2024