

Epson Perfection® V19 II

Color Photo and Document Flatbed Scanner

Scanners

High-Resolution Scanning



Affordable, easy-to-use high-resolution photo scanner.

Amazing image clarity and detail — 4800 dpi optical resolution¹, ideal for photo enlargements

Epson ScanSmart® software included² — easily scan photos, artwork, illustrations, books, documents and more

One-touch scanning³ — scan in fewer steps with easy-to-use buttons³

Restore color to faded photos — with one click, Easy Photo Fix® technology makes it simple

Scan books and photo albums — high-rise, removable lid

Generate searchable PDFs³ — convert scanned documents to searchable PDF files

Create editable Microsoft® Office documents³ — scan to Word, Excel® and PowerPoint®⁴ files with Optical Character Recognition (OCR)³

Compact and lightweight — USB powered for portability; 3.1 lb

Convenient — scan letter-sized documents in as fast as 10 seconds⁵

Save space — built-in kickstand for vertical placement and storage



*Source: The NPD Group, Inc., Retail Tracking Service, U.S. & Canada, Scanners, Aug. 2021 – Jul. 2022.



Epson Perfection® V19 II Color Photo and Document Flatbed Scanner

Specifications

Type
Flatbed Color Image Scanner

Optical Sensor
CIS (Contact Image Sensor)

Optical Resolution¹
4800 dpi

Hardware Resolution
4800 x 4800 dpi

Effective Pixels
40,800 x 56,160 pixels (4800 dpi)

Color Bit Depth
48-bits per pixel (internal); 24-bits per pixel (external)

Grayscale Bit Depth
16-bits per pixel (internal); 8-bits per pixel (external)

Maximum Scan Area
Flatbed: 8.5" x 11.7"

Light Source
3-color RGB LEDs

Scanning Speed (Letter-Size, Color)
Color 300 dpi: approximately 10 seconds (via USB 2.0)
Color 600 dpi: approximately 30 seconds (via USB 2.0)

Features

Buttons
PDF, Send, Copy and Start

Image Restoration
Epson® Easy Photo Fix technology

Upright Scanning
Built-in stand for upright scanning and storage

Scanner Lid
Removable scanner lid for oversized and thick media

Software Included

Epson ScanSmart²

System Requirements

Microsoft Windows® 11, Windows 10, Windows 8.1, Windows 8, Windows 7
Mac® OS X® 10.11.x – macOS® 13.x

General

Reliability
MCBF: 10,000 cycles

Scanner Interface
Hi-Speed USB 2.0

Operating Temperature
50 °F to 95 °F (10 °C to 35 °C)

Operating Humidity
20% – 80% (no condensation)

Power Supply
USB Interface Bus Power (Micro-B connector)
Rating: 5 V, 500 mA

Power Consumption
Operating: 2.5 W
Ready: 1.1 W
Off: 0.0125 W (when PC is suspended)

Dimensions (W x D x H)
9.9" x 14.4" x 1.5"

Weight
3.1 lb

Warranty
1-year limited warranty in the U.S. and Canada

Eco Features

RoHS compliant
End-of-life options available⁶
Epson America, Inc. is a SmartWay® Transport Partner⁷

What's Included

Epson Perfection V19 II scanner, USB cable, *Start Here* setup poster

Ordering Information

Epson Perfection V19 II	B11B267201
-------------------------	------------

¹ Optical resolution is the maximum scan resolution of the image sensor, using the definition of ISO 14473. | ² Internet connection required for software download. | ³ With Epson ScanSmart software installed on the connected Windows PC or Mac. Internet connection required. | ⁴ Save to PowerPoint feature available for Windows only. | ⁵ Based on letter-sized scans at 300 dpi in Black-and-White, Grayscale or Color Mode. | ⁶ For convenient and reasonable recycling options, visit www.epson.com/recycle | ⁷ SmartWay is an innovative partnership of the U.S. Environmental Protection Agency that reduces greenhouse gases and other air pollutants and improves fuel efficiency.



Epson America, Inc.
3131 Katella Ave., Los Alamitos, CA 90720

Epson Canada Limited
185 Renfrew Drive, Markham, Ontario L3R 6G3

www.epson.com
www.epson.ca

EPSON, Easy Photo Fix, Epson ScanSmart and Perfection are registered trademarks and the EPSON logo is a registered logomark of Seiko Epson Corporation. Mac, macOS and OS X are trademarks of Apple Inc., registered in the U.S. and other countries. Excel, Microsoft, PowerPoint and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and other countries. All other product and brand names are trademarks and/or registered trademarks of their respective companies. Epson disclaims any and all rights in these marks. Copyright 2023 Epson America, Inc. CPD-63032 3/23

Contact: