

ThinkStation P3 Ultra

Business professionals can level up their work experience and performance with this 3.9-liter mini-tower powered by up to 13th Gen Intel Core i9 Processor. Enhance productivity with optional Wi-Fi 6E that enables faster connection speeds even in densely congested areas while with dual Thunderbolt 4 port, connect displays and share files at high speed. A slew of security features includes a discrete TPM 2.0 chipset, Kensington security slot, and BIOS security that keeps data well-protected.



Configured with up to 4TB of high-speed storage via 2x M.2 SSD modules and up to 128GB DDR5 memory, this device offers extreme portable power and enables users to multitask on compute-intensive workflows.

To view and compare detailed spreadsheets, professionals can connect to up to eight independent displays via an onboard Display Port, Thunderbolt, and discrete graphics.

EPEAT Gold, ENERGY STAR 8.0, TCO Certified 9.0, and ROHS compliant certification makes it an energy-efficient device.

Professional machines for advanced users

ThinkStation P3 Series workstations provide affordable power-computing with a choice of processor technologies, expansion bays and support for multiple storage drives.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



On-site Service

If a problem can't be fixed remotely, we will visit your location
 Normally next business day service
 Agreed appointment times

Accessories

Lenovo Go Wireless Numeric Keypad

21-key numeric keypad with industry-leading scissor switch keys
 Minimalist design with ultra slim profile at 13 mm with dedicated productivity keys (Calculator, Tab, Equal, Esc keys)
 Rechargeable , up to 3 months use in single charge (may vary based on usage)



PN: 4Y41C33791, GY41C33979

Lenovo Essential Wireless Keyboard & Mouse Combo

Simple design that is comfortable for all day use and tough enough to handle spills
 Convenient and easy to use wireless connection
 Quality typing experience with quiet key strokes and a full-size number pad



PN: 4X30M39458 - US English

ThinkStation P3 Ultra

Performance

Processor

Up to one 12th Gen Intel Core i5/i7/i9 processor or 13th Gen Intel Core i3/i5/i7/i9 processor, supports up to 24 cores, up to 5.8GHz

Operating System

Windows 11 Pro
 Windows 11 Home
 Windows 11 Home Single Language
 Windows 11 DG Windows 10 Pro 64
 Ubuntu Linux
 Red Hat Enterprise Linux (certified only)

Graphics

Supports up to one NVIDIA RTX A5500 Laptop GPU

Chipset

Intel W680 chipset

Memory ¹

Up to 128GB, 4 DDR5 SO-DIMM slots

¹The max memory is based on the test results with current Lenovo memory offerings. The system may support more memory as the technology develops.

Storage ²

Up to 1x 2.5" HDD + 2x M.2 SSD
 · 2.5" HDD up to 1TB
 · M.2 SSD up to 4TB each

²The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.

Design

Dimensions ³

87 x 223 x 202 mm (3.43 x 8.78 x 7.95 inches)

³The system dimensions may vary depending on configurations.

Weight ⁴

3.6 kg (7.94 lbs, maximum configuration)

⁴The system weight is approximate and may vary depending on configurations

Connectivity

Ethernet

Two onboard Ethernet, GbE and 2.5GbE
 Additional Ethernet options via PCIe adapter

WLAN + Bluetooth ⁵

Up to Intel Wi-Fi 6E AX211, Bluetooth 5.1, vPro

⁵Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

Security & Privacy

Discrete TPM 2.0
 Kensington Security Slot, 3 x 7 mm
 Chassis intrusion switch

Manageability

Intel vPro Enterprise with Intel AMT 16.0*

⁶Intel vPro offers a superset of DASH's defined capabilities.

Certifications

Green Certifications ^{7 8}

EPEAT Gold Registered
 ENERGY STAR 8.0
 TCO Certified 9.0
 RoHS compliant

⁷The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁸EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country.

Other Certifications

MIL-STD-810H