



PTZ330UV2

30X 4K AI PTZ Camera
















4K Resolution



30X Optical Zoom



HDMI, IP, USE 3G-SDI



Supports PoE+



8MP Picture



Al Funct



4Kp60

 Simultaneous output at 4Kp60 with HDMI/USB/IP



Seamless Content Capture with SmartShoot Al Functions

- Optimize your camera controls for automatic content capturing between preset areas
- Create a multi-camera feel across all your preset zones
- Save time and effort with a variety of shooting ranges



Advanced Motion Control

- Achieve precise camera movement during recording
- Pan/tilt rotation maneuvers as small as 0.1° per step and as fast as 200°
- Customizable speed controls allow you to optimize your recording



Prepare for Any Angle

- Up to 256 different preset locations through VISCA via RS232 and RS422 functionality
- Simplified IR remote and the ability to set 10 preprogrammed preset locations
- Easy manual control of the recording view with outstanding preset locations



Tally Light

Simplify multi-camera live video productions with an illuminated red light on the active camera.











Free Software for Users and **AV Managers**

Whether you need a simple tool to control your PTZ or TR camera, or manage over a hundred on your network, AVer has great options. CaptureShare and PTZ Management for desktop and AVer PTZ Control Panel for iPad have you covered. For new voice tracking features, look to PTZ Link. Visit our support page for easy download of our desktop software.

Compatible Software



















Product Specifications

PTZ310UV2

Camera	Image Sensor	1/2.8"4K Exmor CMOS
	Effective Picture Elements	8 Megapixels
	Output Resolutions	4K/60, 4K/59.94, 4K/50, 4K/30, 4K/29.97, 4K/25, 1080p/60, 1080p/59.94, 1080p/50, 1080p/30, 1080p/29.97, 1080p/25, 1080i/60, 1080i/59.94, 1080i/50, 720p/60, 720p/59.94, 720p/50
	Minimum Illumination	0.46 lux (IRE50, F1.6, 30fps)
	S/N Ratio	> 50dB
	Gain	Auto / Manual
	TV Lines	1400 (Center/Wide)
	Shutter Speed	1/1 to 1/32,000 sec
	Exposure Control	Auto, Manual, Priority AE(Shutter, IRIS), BLC, WDR
	White Balance	Auto, Manual, ATW, One Push
	Optical Zoom	30X
	Digital Zoom	1X
	Total Zoom	30X
	Viewing Angles	DFOV: 69.2° (Wide) to 2.8° (Tele), HFOV: 62.3° (Wide) to 2.5° (Tele), VFOV: 37.3° (Wide) to 1.4° (Tele)
	Focal Length	f = 4.5 mm (Wide) to 135 mm (Tele)
	Aperture (Iris)	F = 1.8 (Wide) to 4.7 (Tele)
	Minimum Working Distance	0.1 m (Wide), 1.2 m (Tele)
	Pan / Tilt Angles	Pan: ±170°, Tilt: +90° / -30°
	Pan / Tilt Speed (Manual)	Pan: 0.1° to 100° / sec, Tilt: 0.1° to 100° / sec
	Preset Speed	Pan: 200° / sec, Tilt: 200° / sec
	Preset Positions	10 (IR), 256 (RS-232, RS-422, IP)
	Camera Control - Interfaces	RS-232 (DIN8), RS-422 (RJ45), IP
	Camera Control - Protocols	VISCA (RS-232 / RS-422 / IP), PELCO-D & PELCO-P (RS-232 / RS-422), CGI (IP)
	Image Processing	Noise Reduction (2D / 3D), Flip, Mirror
	Power Frequencies	50 Hz. 60 Hz
Al Functions	Modes	SmartShoot
Audio	Audio - Channel	2ch Stereo
AuuiU	Audio - Codec	AAC-LC
nterface	Video Outputs	3G-SDI, HDMI, IP, USB
menace	Audio Outputs	3G-SDI, HDMI, IP, USB
	Audio Output	MIC in, Line in
General	Power Requirement	AC 100 - 240V to DC 12V/2A
	Power Consumption	19W
	PoE	PoE+
	Dimensions (W x H x D)	180.0 x 192.0 x 145.0 mm
	Net Weight	2.0 (±0.1) kg
	Application	Indoor
	Tally Light	Yes
	, · ·	Kensington Slot
	Security Security	Infrared
	Remote Control	Temperature: 0 °C to +40 °C; Humidity: 20% to 80%
	Operating Conditions	Temperature: -0 °C to +60 °C; Humidity: 20% to 95%
D Ctucominu	Storage Conditions	·
IP Streaming	Resolution	4K 60fps H.264, H.265, MJPEG
	Network Video Compress Formats Maximum Frame Rate	H.264, H.265, MUPEG 4K 60 fps
	Bit-Rate Control Modes	VBR, CBR (selectable)
	Range of Bit-Rate Setting	512 Kbps to 120 Mbps
	Network Interface	10/100/1000 Base-T
	Multi-Stream Capability	4: HDMI / RTSP / USB(4Kp60) & 3G-SDI(1080P60)
	Network Protocols	IPv4, TCP, UDP, ARP, ICMP, IGMP, HTTP, HTTPS, DHCP, RTP / RTCP, RTSP, RTMP, SRT, HLS, LLDP, VISCA over IP
	NDI® HX3 Capability	WA USBOOT B
USB	Connector	USB 3. 0 Type-B
	Video Formats	MJPEG, YUY2
	Maximum Video Resolution	2160p
	USB Video Class (UVC)	UVC 1.1
	USB Audio Class (UAC)	UAC 1.0
Web UI	Live Video Preview	Yes
	Camera PTZ Control	Pan, Tilt, Zoom, Focus, Preset Control
	Camera / Image Adjustment	Exposure, White Balance
	Network Configuration	DHCP, IP Address, Gateway, Subnet Mask, DNS

Software Tools	IP Search and Configuration Tool	Support Windows® 7 or later	
	PTZ Management	Support Windows® 7 or later	
	PTZ Control Panel	Supports iOS & iPadOS® 11 or later	
	PTZ Link	Supports Windows® 7 or later, macOS® 10.14 or later	
	OBS Plugin for PTZ Cameras	Supports Windows® 8 or later, macOS® High Sierra v10.13 or later	
	CaptureShare	Supports Windows® 7 or later, macOS® 10.14 or later	
Warranty	Camera	5 Years	
	Accessories	1 Year	
Package Contents	Camera, Drilling Paper, Ceiling Mount Bracket (x2), Quick Start Guide, Cable Fixing Plate, M2 x 4 mm Screw (x3), Power Adapter & Power Cord, 1/4"-20 L=6.5 mm Screw (x2), Remote Control, M3 x 6		
	mm Screw (x3), DIN 8 to D-Sub 9 Cable, RS-232 In/Out Y Cable, Cable Ties (x4)		
Optional Accessories	AVer CL01 PTZ Camera Controller, L-Typ	AVer CL01 PTZ Camera Controller, L-Type Ceiling Mount	
Ordering Info	Part Number	PTZ330UV2	

Hardware Specifications

