

## PERFORMANCE

### Processor

Intel® Core™ i7-1185G7 (4C / 8T, 3.0 / 4.8GHz, 12MB)

### Graphics

Integrated Intel Iris® Xe Graphics

### Chipset

Intel SoC Platform

### Memory

32GB Soldered LPDDR4x-4266

### Memory Slots

Memory soldered to systemboard, no slots, 8-channel

### Max Memory

32GB soldered memory, not upgradable

### Storage

512GB SSD M.2 2280 PCIe® x4 NVMe® Opal 2.0

### Storage Support

One drive, up to 2TB M.2 2280 SSD

### Storage Slot

One M.2 2280 PCIe 4.0 x4 slot

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3306 codec

### Speakers

Stereo speakers, 2W x2 woofers and 0.8W x2 tweeters, Dolby® Atmos®

### Camera

HD 720p + IR Hybrid with Privacy Shutter

### Microphone

4x, Array

### Battery

Integrated 57Wh

### Max Battery Life

MobileMark® 2014: 21.0 hr

MobileMark 2018: 16.1 hr

JEITA 2.0: 23.9 hr

### Power Adapter

65W USB-C® (2-pin)

## DESIGN

### Display

14" WQXGA (3840x2400) IPS 500nits Anti-reflection / Anti-smudge, 100% DCI-P3, DisplayHDR™ 400, Touch

### Touchscreen

OGS, 10-point Multi-touch

### Keyboard

Backlit, English

### Case Color

Storm Grey

### Case Material

Aluminium (Top), Aluminium (Bottom)

### Pen

Lenovo® Integrated Pen

### Dimensions (WxDxH)

314.4 x 223 x 14.99 mm (12.38 x 8.78 x 0.59 inches)

### Weight

Starting at 1.399 kg (3 lbs)

## SOFTWARE

### Operating System

Windows® 11 Pro, English

## CONNECTIVITY

### Ethernet

No Onboard Ethernet

### WLAN + Bluetooth®

Intel Wi-Fi® 6 AX201, 11ax 2x2 + BT5.1

### Standard Ports

- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 2x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4a)
- 1x HDMI® 2.0
- 1x Headphone / microphone combo jack (3.5mm)

### Docking

Various docking solutions supported via Thunderbolt / USB-C.

For more compatible docking solutions, please visit [Docking for ThinkPad® X1 Yoga® Gen 6](#)

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0 Enabled

### Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

### Physical Locks

Kensington® Nano Security Slot™

### Other Security

- Camera privacy shutter
- IR camera for Windows® Hello
- Human Presence Detection

## MANAGEABILITY

### System Management

Intel® vPro®

## SERVICE

### Base Warranty

3-year, Courier or Carry-in

## CERTIFICATIONS

### Green Certifications

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- TCO Certified
- RoHS compliant

### Other Certifications

- Intel Evo™ Platform
- TÜV Rheinland® Low Blue Light

### Mil-Spec Test

MIL-STD-810H military test passed

## MODEL

TopSeller : Yes

Announce Date : 2023-05-09

EAN / UPC / JAN : 197528068305

End of Support : 2027-10-02



intel

- Lenovo reserves the right to change specifications or other product information without notice.
- Battery life is an estimated maximum. Actual battery life may vary by hardware or system settings, active applications, battery conditioning, etc.
- California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo 65W USB-C AC Travel Adapter

40AW0065WW

STREAMLINE YOUR LIFE WITH A 65W USB-C AC TRAVEL ADAPTER. Changing the way you travel for business or pleasure, the Lenovo 65W USB-C AC Travel Adapter eliminates the need for multiple chargers. Power your USB-C devices...

## Recommended Services

BEST	3Y Premier Support Plus upgrade from 3Y Courier/Carry-in (5WS1L39178)
BETTER	3Y Premier Support Upgrade from 3Y Courier/Carry-in (5WS0T36160)
GOOD	3Y Onsite upgrade from 3Y Courier/Carry-in (5WS0E97271)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference