

WHRLN Series H.265 Hybrid NDAA Wall Mount DVR with Smart Analytics

H6WHRLN

6 Channel Wall Mount Hybrid Digital Video Recorder 4 Configurable Hybrid Channels (TVI or IP) plus 2 IP Channels

H16WHRLN

16 Channel Wall Mount Hybrid Digital Video Recorder 8 Configurable Hybrid Channels (TVI or IP) plus 8 IP Channels

H24WHRLN

24 Channel Wall Mount Hybrid Digital Video Recorder

8 Configurable Hybrid Channels (TVI or IP) plus 8 IP Channels plus 8 TVI Channels















5	
MP	











STO	RAGE
2 TB -	32 TB

2TB-I6TB: H6WHRLN 2TB-32TB: HI6WHRLN | H24WHLRN

H6WHRLN2TB	H6WHRLN12TB	H16WHRLN8TB	H16WHRLN32TB	H24WHRLN12TB
H6WHRLN4TB	H6WHRLN16TB	H16WHRLN12TB	H24WHRLN2TB	H24WHRLN16TB
H6WHRLN6TB	H16WHRLN2TB	H16WHRLN16TB	H24WHRLN4TB	H24WHRLN20TB
H6WHRLN8TB	H16WHRLN4TB	H16WHRLN20TB	H24WHRLN6TB	H24WHRLN24TB
H6WHRLN10TB	H16WHRLN6TB	H16WHRLN24TB	H24WHRLN8TB	H24WHRLN32TB







Use With

Cover

Key Features

EZ Wizards - For ease of use and setup

Camera: quickly discover and install all Speco IP cameras

Setup: for quick setup of general settings

Network: network setup and port forwarding

Record: quickly setup recording resolutions and recording type

Search: quickly search for events from thumbnails

Copy: quickly copy what you are playing onto a USB flash drive

- Supports up to 5MP (HD-TVI + IP) on all channels and 4K (IP) on 1channel (H6WHRLN)
- Supports up to 5MP (HD-TVI + IP) on all channels and 4K (IP) on 8 channels (H16WHRLN, H24WHRLN)
- H.265 compression Store up to 2x more than H.264!
- 1 SATA port for up to 16TB of storage (H6WHRLN)
- 2 SATA ports for up to 32TB of storage (H16WHRLN, H24WHRLN)
- 1 eSATA port for an additional 8TB of storage
- 4K HDMI out and VGA monitor output
- Object and line crossing detection and alerts*
- Smart Search Specify a region on the camera view and search on changes in that area*
- 2-way audio communication
- Alarm 4/8/16 inputs, 1/2/4 outputs
- Free US-based DDNS and P2P services
- Remote viewing via web browser, your Apple TV, Amazon Fire TV, or your mobile device
- Easy video exporting via USB
- 5 year limited warranty
- *with Speco Smart Analytic IP Cameras

Additional Features

- Supports different recording types: Continuous, Motion, Analytics, and Sensor
- Create bookmark pins on playback for easy reference
- Instant playback for individual channels directly from the live view screen
- Customizable channel view placement
- Remote monitoring, recording, playback, configuration, upgrades, and PTZ control via the internet
- Simultaneous HDMI & VGA video output
- Built-in S.M.A.R.T technology (Self-Monitoring, Analysis and Reporting Technology for HDD)
- Supports 2-way audio communication (speaker required)





- Auto Live Camera Pop-Up
- View A Camera
- Event Tag

Optional Accessories



9 Port Gigabit Network Switch

(8 ports PoE, 1 port Uplink)



6-Port Gigabit Network Switch

(4 ports PoE, 2 ports uplink)





26-port Gigabit Network Switch with 24-ports PoE and 2xSFP Uplink

Limited Warranty/Hard drives excluded. Check www.specotech.com for more details. iPhone is a trademark of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc. Amazon's trademark is used under license from Amazon.com, Inc. or its affiliates. The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 5/8/23















	Model		WHRLN		
	Channels	6	16	24	
	Compression	Standard H.265			
System	OS	Embeded Linux			
	Analog Only Input	BNC x4	BNC x8	BNC x16	
	Configurable Analog Inputs	4	8	8	
	IPC Only Input	2CH (up to 6CH)*	8CH (up to 16CH)*	8CH*	
Video	Network Access & Transfer Bandwidth	16/40Mbps	32/96Mbps	64/192Mbps	
	Network Access Format	8MP/5MP/4M			
	Output	HDMIx1: 4Kx2K/1920x1080/1280x1024 VGAx1: 1920x1080/1280/x1024/1024x768 BNCx1: CVBS (used as the main or spot output)			
	Input	RCAx4 RCAx8		8	
Audio	2-way Audio	Take up channel one audio input			
	Local Output	RCAx1			
	Record Stream	Dual stream recording			
	Resolution	4K/5MP/4MP/1080P/720P/WD1			
Record	Frame Rate	4K@6fps/7fps 5MP@12fps/15Fps (PAL/NTSC) 1080P/720P/WD1@25fps/30fps (PAL/NTSC)			
	Bit Rate	32~78Mbps			
	Mode	Manual, s	chedule, motion, sensor, intelligence		
IP Input	Resolution	8MP/5MP/4MP	/3MP/1080P/960P/720P@25fps/30fp	os	
	Simultaneous Playback	Max 4CH	Max 8CH	Max 16CH	
Playback	Search Mode	EZ Search, museum search, time search, event search, bookmark search, snapshot search Highlighted color to display camera records in a certain period of time, different colors refer to different record events			
ridyback	Smart Search				
	Function	Play, pause, FF, FB, etc.			
	Mode	Manual, se	ensor, motion, exception, intelligence		
Alarm	Input	4CH local alarm input; Support IPC alarm input	8CH local alarm input; Support IPC alarm input	16CH local alarm input; Support IPC alarm input	
, dam	Output	1CH local alarm input; Support IPC alarm input	2CH local alarm input; Support IPC alarm input	4CH local alarm input; Support IPC alarm input	
	Linkage	Record, snapshot, preset, e-mail, pop-up window, etc.			
	Interface	RJ45 10M/100Mbps x 1 RJ45 10M/100M/100Mbps x 1		/100Mbps x 1	
Network	Protocol	TCP/IP, PPPoE, DHCP, DNS, DDNS, UPnP, NTP, SMTP, HTTP, HTTPs, RTSP		s, RTSP	
	Web Client	Multiple online users monitoring			
Nobile Device	OS	Speco Blue iOS, Android, SecureGuard® Client			
Oth	er Viewing Platforms	- Ap	ople TV and Amazon Fire TV		
	HDD	SATAx1, max 16TB per HDD	SATAx2, max 16	TB per HDD	
Storage	eSATA	eSATAx1 max 8TB			
	Local	USB, USB mobile HDD			
Export	Network	Yes			
	USB	USB2.0x2			
Interface	Remote Control	Yes			
	Power Supply	DC12V/2A	DC12V/	′4A	
	Power Consumption	≤10W(without HDD)	≤15W(without HDD)	≤30W(without HDD)	
Dimensions	Dimensions(WxDxH)	11.5" × 3.5" × 15"	16" x 3.5"		
	Working Environment		°F to 122°F (-10°C to 50°C)		









