

Power Cord for Select Eaton Universal PDUs -
11500VA 240V Single-Phase, 360P6W Input, 60A,
10 ft. (3.05 m)

MODEL NUMBER: CBL362-10



PDU power cord with 8-pin universal plug connects your EVMAGU23X-3 G3 universal input PDU (UPDU) to a compatible AC outlet.

Features

Detachable Power Cord Supports Universal Input PDU

This detachable 11.5kVA power cord is designed for North American 240V single-phase use. Its 8-pin universal connector mates with the EVMAGU23X-3 G3 universal input PDU (UPDU) to meet your diverse rack-power needs. The 10-foot (3.05-meter) length with 360P6W input plug allows you convenient flexibility in placing the UPDU with respect to the AC outlet.

Specifications

OVERVIEW	
UPC Code	786689783907
Device Compatibility	PDU
Country/Region	Global
INPUT	
Input Phase	Single-Phase
Maximum Input Amps	60.0
Voltage Compatibility (VAC)	200-240
PHYSICAL	
Color	Black

Highlights

- Delivers 11.5kVA single-phase power to Eaton's EVMAGU23X-3 G3 UPDU
- 10 ft. length allows flexibility in placing PDU in relationship to AC outlet

System Requirements

Pairs with Eaton's EVMAGU23X-3 G3 universal input PDU (UPDU)

Package Includes

CBL362-10 Power Cord, 11500VA 240V Single-Phase, 10 ft. (3.05 m)



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States

Plug Color	Blue
Cable Jacket Color	Black
Connector Color	Black
Power Cord Jacket Type	SOOW
Cable Outer Diameter (OD)	25mm
Number of Conductors	3
Wire Gauge (AWG)	6
Wire Gauge (OD - mm ²)	6
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	5.00 x 17.00 x 17.00
Shipping Dimensions (hwd / cm)	12.70 x 43.18 x 43.18
Shipping Weight (lbs.)	22.00
Shipping Weight (kg)	9.98
Unit Dimensions (hwd / in.)	4.000 x 11.250 x 10.750
ENVIRONMENTAL	
Operating Temperature Range	32° to 140°F (0° to 60°C)
Storage Temperature Range	32° to 194°F (0° to 90°C)
Operating Temperature	32° to 140°F (0° to 60°C)
Operating Humidity Range	10% TO 90% RH, NON-CONDENSING
Storage Humidity Range	10% TO 90% RH, NON-CONDENSING
CONNECTIONS	
Side A - Connector 1	(1) 8-Pin Souriau UTG
Side B - Connector 1	(1) 360P6W
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cTUVus; cUL Listed

Product Compliance	CE (Europe); FCC (USA); RoHS; UKCA; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty