



SPECIFICATIONS

Panel Size	23.6" (60cm)
Active Display Area (mm)	521(H)x293(V)
Curvature	1500R
Panel Type	VA
Panel Resolution	1920x1080 (FHD)
Pixel Pitch (H x V)	0.272(H)x0.272(V)
Aspect Ratio	16:9
Brightness (nits)	250
Contrast Ratio	3000:1
DCR	100000000:1
Signal Frequency	52.8~90 KHz(H) / 48~75 Hz(V)
Refresh Rate	75Hz
Response time	1ms(MPRt)
DYNAMIC REFRESH RATE TECHNOLOGY	FreeSync
Video ports	1 x Display Port (1.2a) 1 x HDMI™ (1.4b)
Audio ports	1x Headphoneout
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	82% / 77% / 98%
Surface Treatment	Anti-glare
Display Colors	16.7M
Power Type	External Adaptor 12V 2.5A
Power Input	100~240V
Adjustment (Tilt)	-5°~ 20°
Adjustment (Swivel)	N/A
Adjustment (Pivot)	N/A
Adjustment (Height)	N/A
Kensington Lock	Yes
Control	5-way OSD navigation joystick
ACTIVATED RANGE	48 to 75Hz
Dimension (W x D x H)	539.8x 184.7 x 413.4 mm 539.8 x 74.2 x 321.8 mm(without stand)
Carton Dimension (W X D X H)	WW:600 x 140x 400 mm Outer:615 x 155 x 430 mm
Frameless Design	Yes
PIP / PBP Function	N/A

FEATURES

1500R



Enjoy the most immersive gameplay with 1500R curvature rate.

1ms Fast Response Time



Eliminate screen tearing and choppy frame rates with 1ms response time.

Night Vision



See every detail clearly in the dark, helping you find and attack enemies before they notice.

Wide Color Gamut



Game colors and details will look more realistic and refined, to push game immersion to its limits.

Frameless Design



With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.

VESA Mounting

100 x 100 mm

Weight (NW / GW)

3.01kg/ 4.5kg

Note

Display Port:1920 x 1080 (75Hz)
HDMI™: 1920 x 1080 (75Hz)
Adobe RGB, DCI-P3 and sRGB follow
CIE1976 Standard

CONNECTIONS



1. 5-way joystick navigator
2. 1 x Display Port (1.2a)
3. 2 x HDMI™(2.0b)
4. Headphone-out
5. DC-in
6. 1x Kensington Lock