



## SPECIFICATIONS

Panel Size	27" (69cm)
Active Display Area (mm)	596.736(H) x335.664(V)
Curvature	Flat
Panel Type	Rapid IPS
Panel Resolution	2560x1440 (WQHD)
Pixel Pitch (H x V)	0.2331(H)x0.2331(V)
Aspect Ratio	16:9
Brightness (nits)	400 (Typ.) 400 (HDR Peak)
Contrast Ratio	1000:1
DCR	100000000:1
Signal Frequency	76.08~380.4 KHz(H) / 48~240 Hz(V)
Refresh Rate	240Hz
Response time	1ms GtG
<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	Adaptive Sync
<b>HDR Support</b>	VESA DisplayHDR 400
<b>Video ports</b>	2x HDMI™ (Supports WQHD@144Hz as specified in HDMI™ 2.0b) 1x DisplayPort (Supports WQHD@240Hz as specified in DisplayPort 1.4a) 1x Type-C (DP Alt.)
<b>USB ports</b>	N/A
<b>Audio ports</b>	1x Headphone out
<b>Viewing Angle</b>	178° (H) / 178° (V)
<b>Adobe RGB / DCI-P3 / sRGB</b>	97% / 98% / 136%
<b>Surface Treatment</b>	Anti-glare
<b>Display Colors</b>	1.07B (8 bits + FRC)
<b>Power Type</b>	External Adaptor 19V 5.79A
<b>Power Input</b>	100~240V, 50/60Hz
<b>Adjustment (Tilt)</b>	-5° ~ 20°
<b>Adjustment (Swivel)</b>	-45° ~ 45°
<b>Adjustment (Pivot)</b>	-90° ~ 90°
<b>Adjustment (Height)</b>	0 ~ 130mm
<b>Kensington Lock</b>	Yes
<b>Control</b>	5-way OSD Navigation Joystick
<b>ACTIVATED RANGE</b>	48 to 240Hz
<b>Dimension (W x D x H)</b>	613.49 x 196.5 x 402.1 mm / 613.5 x 69.8 x 362.5 mm (without stand)

## FEATURES



### eSports Gaming

MSI eSports gaming monitor will enhance your competitive gameplay to ensure you are always at your best levels.



### Rapid IPS

Provides 1ms GTG fast response time, optimizes screen colors and brightness.



### WQHD (2560 x 1440)

Game titles will even look better, displaying more details due to the WQHD (2560 x 1440) resolution.



### 240Hz Extremely High Refresh Rate

Experience smooth gaming with a blazing fast 240Hz refresh rate, that gives you the upper hand in fast moving games.



### Fast Response Time - 1ms GtG

Eliminate screen tearing and choppy frame rates with 1ms GTG response time.



### Type-C 65W PD

Built-in a USB Type-C connection with 65W power delivery allows you to effortlessly connect to and charge your devices.



### Night Vision

See every detail clearly in the dark, helping you find and attack enemies before they notice.



### Adjustable Stand

Maximize your productivity and comfort with the adjustable stand.



### Wide Color Gamut

Game colors and details will look more realistic and refined, to push game immersion to its limits.



### VESA Certified DisplayHDR 400



Provide eye-catching detail through contrast and shadows adjustment.




### G-Sync Compatible

Prevent screen tearing or stuttering, producing ultra-smooth lag-free gameplay.

<b>Carton Dimension (W X D X H)</b>	WW carton: 815 x 145 x 502 mm / Outer: 830 x 158 x 526 mm
<b>Console Mode</b>	2K Resolution PS5™ Optimization FHD/WQHD @ 120Hz * All trademarks and the registered trademarks are the property of their respective owners.
<b>Frameless Design</b>	Yes
<b>PIP / PBP Function</b>	Yes
<b>VESA Mounting</b>	75 x 75 mm
<b>Weight (NW / GW)</b>	5.95 kg / 8.1 kg Without Stand: 3.92 kg
<b>Note</b>	Display Port: 2560 x 1440 (Up to 240Hz). Type-C: 2560 x 1440 (DP alt. w/ PD Charging 65W) HDMI™: 2560 x 1440 (Up to 144Hz) Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

## CONNECTIONS



1. 5-way joystick navigator
2. DC jack
3. Earphone out
4. 2x HDMI™ (2.0b)
5. 1x Display Port (1.4a)
6. Type-C (65W PD Charging)