



SPECIFICATIONS


Panel Size	27" (69cm)
Active Display Area (mm)	596.736(H)x335.664(V)
Curvature	Flat
Panel Type	Rapid IPS
Panel Resolution	2560x1440 (WQHD)
Pixel Pitch (H x V)	0.2331(H)x0.2331(V)
Aspect Ratio	16:9
Brightness (nits)	300 (Typ.)
Contrast Ratio	1000:1
DCR	100000000:1
Signal Frequency	78.2~268.8 KHz(H) / 48~165 Hz(V)
Refresh Rate	170Hz
Response time	1ms GtG
DYNAMIC REFRESH RATE TECHNOLOGY	G-SYNC Compatible
HDR Support	HDR Ready
Video ports	2x HDMI™ (Supports WQHD@144Hz as specified in HDMI™ 2.0b) 1x DisplayPort (Supports WQHD@170Hz as specified in DisplayPort 1.2a By DP overclocking)
USB ports	N/A
Audio ports	1x Headphone out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	91.18% / 92.83% / 120.22%
Surface Treatment	Anti-glare
Display Colors	1.07B (8 bits + FRC)
Power Type	External Adaptor 20V 2.25A
Power Input	100~240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	-45° ~ 45°
Adjustment (Pivot)	-90° ~ 90°
Adjustment (Height)	0 ~ 130mm
Kensington Lock	Yes
Control	5-way OSD navigation joystick
ACTIVATED RANGE	48 to 170Hz
Dimension (W x D x H)	613.04 x 233.68 x 405.11 mm / 613.04 x 58.89 x 368.84 mm (without stand)

FEATURES

- eSports Gaming**
 MSI eSports gaming monitor will enhance your competitive gameplay to ensure you are always at your best levels.
- Rapid IPS**
 Provides 1ms GTG fast response time, optimizes screen colors and brightness.
- WQHD (2560 x 1440)**
 Game titles will even look better, displaying more details due to the WQHD (2560 x 1440) resolution.
- 170Hz High Refresh Rate**
 Experience smooth gaming with 170Hz refresh rate, that gives you the upperhand in fast moving games.
- Fast Response Time - 1ms GtG**
 Eliminate screen tearing and choppy frame rates with 1ms GTG response time.
- Adjustable Stand**
 Maximize your productivity and comfort with the adjustable stand.
- Wide Color Gamut**
 Game colors and details will look more realistic and refined, to push game immersion to its limits.
- Night Vision**
 See every detail clearly in the dark, helping you find and attack enemies before they notice.
- G-Sync Compatible**
 Prevent screen tearing or stuttering, producing ultra-smooth lag-free gameplay.

Console Mode	2K Resolution PS5™ Optimization FHD/WQHD @ 120Hz * All trademarks and the registered trademarks are the property of their respective owners.
Frameless Design	Yes
VESA Mounting	100 x 100 mm
Weight (NW / GW)	6.7 kg / 8.6 kg Without Stand: 3.8 kg
Note	Display Port: 2560 x 1440 (Up to 170Hz by DP overclocking). HDMI™: 2560 x 1440 (Up to 144Hz) Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

CONNECTIONS



1. 5-way joystick navigator
2. DC jack
3. 1x Display Port (1.2a)
4. 2x HDMI™ (2.0b)
5. Earphone out
6. Kensington Lock