



L A P T O P S

GF63 Thin

GF63 THIN 11UCX-1424US

Specification

| | |
|------------------------------|---|
| Manufacturer Part # | GF63111424 |
| OS | Windows 11 Pro |
| CPU | Intel® Core™ i5-11400H |
| CPU Speed | 2.7 - 4.5GHz |
| Chipset | HM470 |
| Color | Black |
| Screen Size | 15.6" FHD, IPS-Level 144Hz 45% NTSC |
| Resolution | 1920x1080 16:9 |
| GPU | NVIDIA® GeForce RTX™ 2050 Laptop GPU |
| Video Memory | 4G GDDR6 |
| Keyboard | Red keyboard with Anti-Ghost key (99 Key) |
| Speaker | 2x Speakers 2W |
| Memory | 8GB (8G*1) DDR4 3200MHz |
| HDD Capacity | 512GB NVMe SSD |
| HDD Interface | NVMe |
| LAN | Gb LAN |
| WLAN | Intel Wi-Fi 6 AX201(2*2 ax) |
| Bluetooth | BT 5.1 |
| Card Reader | - |
| Webcam | 720p HD Webcam |
| USB | 3x USB 3.2 Gen1 |
| Type-C Port | 1x USB 3.2 Gen1 Type C |
| Video Port | HDMI 4K @ 30Hz |
| Audio Port | 1 Mic in/ 1 headphone out |
| AC Power Adaptor | 120W |
| Battery Pack | 3 cell , 51Whr Li-Polymer |
| Dimension | 14.13"x9.99"x0.85" |
| Weight | 4.10 lbs |
| Manufacturer Warranty | 1 year Limited warranty (Include 1 Year Global) |