



ExpertBook B9 OLED | B9403CVA

The world's lightest 14" OLED business laptop for C-suite executives ¹

The epitome of sustainable excellence

Designed with premium magnesium- lithium alloy, ASUS ExpertBook B9 OLED pushes the limits of lightness for ultimate portability and durability. With an environmentally-friendly design, brilliant OLED display and smart dual cooling fans, ExpertBook B9 OLED is the perfect partner for executives and business travelers, upping both your green credentials and professionalism – and setting a new benchmark for elite business laptops.



990g
Ultralight



16:10 3K OLED
display



Enterprise-
grade security



Sustainable
technology



Up to 13th Gen
CPU



US military
grade

The perfect balance of lightweight, durability and craftsmanship

- **Premium magnesium lithium alloy**
- **Ultralight weight with 990g**
- Robust durability proven by the latest **US military grade MIL-STD-810H standard**
- **All-day battery life** up to 11 hours for on-to-go executives
- Support **fast charging** up to 50% capacity in 36 minutes

Sustaining an incredible future, for your business and the planet

- **Minimize carbon emission** employing sustainable Thixomolding process to **reduce 29% E-waste and 75% production time**
- Made with up to 70% post-industrial recycled metal and FSC™-Mix certified packaging

Enterprise-grade security to keep your confidential data safe

- Multilayer security and remote management for enterprise with **Intel vPro Platform**
- **Biometric authentication** and identity verifications via IR camera, fingerprint sensor and NFC login

The best device for modern workplace

- Up to **Intel® Core™ i7-1365U vPro® Processor** with **Iris X^e graphic**
- **Stay cool after long-working hours.** Optimum cooling performance with dual fans, adjustable cooling, and auto dust removal
- Up to **64GB LPDDR5x** memory
- **16:10 WQXGA+ OLED display** for color fidelity and low blue light emission
- **AI-powered video conference** with AI noise cancelation and AiSense camera

Warranty and Support



3-Year global warranty
100% free of charge, with no hidden costs.



Pick Up & Return service²
Enjoy a door-to-door service including pick up, repair, and return.



MyASUS App
Contact customer service, view repair status, read product guides and more.

Contact Us

Commercial Support – Contact Us
Self-service:
Phone:
Email:

Commercial Sales – Volume Purchase
Inquiries
Email:
For more information:

SPECIFICATION



Model	B9403CVA
Operating system	Windows 11 Pro(ASUS recommends Windows 11 Pro) Windows 11 Home
CPU	Intel® Core™ i7-1365U vPro® Processor 1.8 GHz Intel® Core™ i5-1345U vPro® Processor 1.6 GHz Intel vPro® Essentials with Intel® Core™ i7-1355U Processor 1.8 GHz Intel vPro® Essentials with Intel® Core™ i5-1335U Processor 1.6 GHz Intel® Core™ i7-1355U Processor 1.8 GHz Intel® Core™ i5-1335U Processor 1.6 GHz
GPU	Intel® Iris Xe graphics
Memory	Up to 64GB LPDDR5x 7500 MHz Onboard: 8/16/32 GB LPDDR5 5200 MHz 64 GB LPDDR5x 7500 MHz
Storage	1 x M.2 SSD, up to 2TB PCIe® 4.0 SSD 512GB/1 TB M.2 PCIe®4.0 Value SSD 512GB/1 TB/2TB M.2 PCIe®4.0 Performance SSD
Display	14.0" 3K OLED (2880*1800), 16:10, wide view, glare, 400 nits, 100% sRGB, 100% DCI-P3
Stylus	Not available
I/O ports	1 x USB 3.2 Gen 2 Type-A 2 x Thunderbolt™ 4.0 Type-C 1 x HDMI 2.1(TMDS) 1 x 3.5 mm combo audio jack 1 x Nano Kensington® lock slot 1 x Micro HDMI transfer to RJ45
Video camera	1080p FHD IR camera, Webcam Shield
Wireless	Wireless on board Wi-Fi 6E (802.11ax) (Dual band) 2*2 + Bluetooth® 5.3 Wireless Card
Audio	2 x speaker 3 x multi-array microphone with intelligo beam forming ASUS two-way AI Noise-Canceling Technology Smart amp technology Dolby certified
Weight	63 Wh battery: starting at 990g
Dimensions (WxDxH)	31.1 x 21.5 x 1.578 cm
Battery	63 Wh, 3-cell, Li-polymer
Security	Nano Kensington® lock slot, fingerprint sensor, webcam shield, TPM 2.0 (optional), NFC login
Keyboard and touchpad	Full-size keyboard with 1.5 mm key travel; backlit; spill-resistant to 400cc* *Quantity used during testing, with duration of 3 minutes
NumberPad	Yes
Featured software	ASUS Control Center (sold separately), ASUS Business Manager, MyASUS
AC adapter	USB Type-C®, 65 W; Output: 20 V DC, 3.25 A; Input: 100~240 V AC 50/60 Hz universal
Energy efficiency compliance	Energy Star 8.0, FSC™-Mix certified Packing, WEEE, French Repairability Index

Disclaimer :

1. Weight may vary according to configuration.
2. ASUS Expert Series Service Package may differ from country to country. We recommend that you check with your local dealers for the specifications of the products available in your country.


Recommended Accessories



ASUS SimPro dock 2



ZenScreen MB165B



65W USB-C Ultra Mini Universal Adapter