Poly Blackwire 5210 Monaural USB-C Headset +3.5mm Plug +USB-C/A Adapter

Wear it well

The Blackwire 5200 Series fits your busy workday. Ergonomically designed for long lasting comfort. And with the easy-to-use connectivity you can work on a variety of devices throughout the day.



*Product image may differ from actual product

Get great sound

Tune out the inevitable workplace distractions with a headset full of features – soft, conforming ear cushions that provide passive noise canceling and a precisely tuned microphone masks nearby conversations.

Enjoy long lasting comfort

Your ears will thank you, especially after long conference calls. This headset is built to stay comfortable. Adjust it to fit the way you work. Need to move locations? The headset folds up for easy portability in the carrying case.

Connectivity options

Enhanced connectivity for your devices: USB-C cord with tethered USB-A adapter for PC and 3.5 mm for mobile or tablet connectivity.

Comfort and durability

Ultra-soft leatherette ear cushion(s) wrapped around pillow-soft memory foam provide long lasting comfort. A lightweight cushioned metal headband offers durability and a comfortable custom fit.

Wearing style

Monaural wearing style for those who prefer to leave one ear open.

Simple call management

Use the intuitive inline controls to answer/end calls, control volume, and mute to simplify call management. Conveniently placed indicator lights provide helpful but unobtrusive user call, mute, and volume status.

Datasheet



Poly Blackwire 5210 Monaural USB-C Headset +3.5mm Plug **+USB-C/A Adapter**

Specifications



Compatible with

Compatible operating systems: Windows 10; macOS

Connectivity and communications

Connection type: 3.5 mm audio; USB Type-A; Wired USB Type-C® Ear cushions: Artificial leather (surface material) Headphone type: On-ear (monoaural)

User interface features

Button user controls: Call answer/end; Mute; Volume +/-

Audio

Audio features:

Noise and echo reduction Dynamic EQ optimized

Microphone type: Omnidirectional

Microphone bandwidth: 100 Hz to 10 kHz

Speaker bandwidth: 20 Hz to 20 kHz

Speaker size: 32 mm Signal-to-noise ratio: >118 dB

Sensitivity (microphone): -38 dBV/Pa Sensitivity (speaker): 116 dB

Battery

Impedance: 32 ohm

Certifications

Certified collaboration software: Skype for Business; Microsoft Teams; Zoom; Cisco Jabber; Works With Chomebook Certified; Avaya

Special features: UC certified

Environmental

Acoustic protection technology: SoundGuard Digital^{1,2}

Applications supported

Management software:

Plantronics Hub (desktop)

Minimum system requirements

USB Type-A port: 3.5 mm audio: USB Type-C® port

Weight and dimensions

Product Primary Color: Black

Weight (imperial): 0.38 lb

Weight (metric): 165.2 a

Cable length (imperial): 3.81 ft (inline module to headset); 3.08 ft (USB to inline module); 7.12 ft (total USB

Cable length (metric): 116 cm (inline module to headset); 94 cm (USB to inline module); 217 cm (total USB

to headset)

Product number: 8X230AA

Warrantv

Poly standard two-year limited warranty

What is in the box

Ouick start auide

Warranty card

Carrying case Headset

USB Type-C® to USB Type-A adapter

Key Selling Points Footnotes

¹Visit https://www.poly.com/us/en/products/headsets/blackwire/blackwire-5200 for more detail.

Technical Specifications Footpotes

SoundGoard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA timeweighted average (TWA). Requires Poly Lens Desktop App to enable SoundGuard Digital features.



