



# Poly Voyager 4245-M Office Headset +USB-A to Micro USB Cable (7S3Y5AA)

## Overview

### Lightweight and comfortable

The Voyager 4245 Office wireless headset system enables your employees to experience high levels of wireless freedom, comfort, and audio quality. Connecting to desk phones, PCs, and mobile devices is seamless.

### Power up productivity

Everyone can move freely and collaborate in comfort all day. Multiple wearing options on a single device keep your teams happy—and make for easy ordering and stock control. Bluetooth® technology enables for seamless global wireless deployment.

### Unlimited talk time [1]

Never lose that critical connection with your customers due to a depleted battery. Voyager 4245 Office headset system has continuous battery life for unlimited talk time[1]. So, teams stay productive for all-around great customer experience.

# Features

## More collaboration

Office workers can collaborate more on the move with the extended wireless range of up to 91 m/298 ft.

## Convertible design

Office workers will enjoy the lightweight, monaural headset with three wearing styles: Over-the-head, behind-the-head, and over-the-ear.

## Eliminate battery anxiety

Conversations stay on track—when the battery runs low, it can be swapped while a call is in progress. And when it's time to swap the battery—visual and audible alerts indicate battery level.

## Acoustic hearing protection

SoundGuard DIGITAL uses sophisticated algorithms to provide additional acoustic protection, above and beyond the impulse and long-duration protection provided by SoundGuard while maintaining natural sounding speech.

## Easy management via Poly Lens

Take control of your deployment from anywhere via remote management with Poly Lens cloud-based device management software.

## Communications platforms.

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.<sup>[2]</sup>

---

[1] Unlimited talk time: use of spare charged battery required.

[2] Visit <https://www.poly.com/us/en/products/headsets/voyager/voyager-4245> for more detail.

## Specifications

<b>Weight</b>	28 g
<b>Weight</b>	0.06 lb
<b>Package dimensions (W x D x H)</b>	190 x 210 x 55 mm
<b>Package weight</b>	620 g
<b>Battery life</b>	Unlimited talk and standby time <sup>[2]</sup>
<b>UPC number</b>	(ABA) 197497168822; (ABB) 197497194265; (ABG) 197498519029; (AC3) 197497168839; (UUF) 197192930755
<b>Manufacturer Warranty</b>	Poly standard two-year limited warranty
<b>What's in the box</b>	Quick start guide; Warranty card; Wireless headset; USB charging cable; BT600 Bluetooth® USB adapter; Travel case

## Additional specifications

Acoustic protection technology	SoundGuard <sup>[1]</sup>
Battery type	Rechargeable Li-ion polymer
Bluetooth version	Bluetooth® Core 5.0
Button user controls	Call answer/end; Mute; Volume +/-
Cartons per layer	10
Cartons per pallet	60
Certified collaboration software	Microsoft Teams
Charge time	<3 hours
Color	Black
Compatibility	Compatible with PCs, desk phones and smartphones via Bluetooth®, USB Type-A or RJ-11 cable
Compatible Operating Systems	Windows 11; Windows 10; macOS; Android™; iOS
Connection type	Wireless: Bluetooth®; Wired: USB Type-A, RJ-11
ECCN	EAR99
Ear cushions	Artificial leather (surface material)
HTS code	8517620090
Headphone type	Convertible
Impedance	32 ohms
Indicator light	On call
Management Software	Poly Lens; Poly Lens app (desktop) <sup>[2]</sup>
Master carton dimension (imperial)	7.67 x 23.50 x 8.85 in
Master carton dimension (metric)	19.5 x 59.7 x 22.5 cm
Master carton weight (imperial)	7.74 lb
Master carton weight (metric)	3.51 kg
Microphone type	Noise cancelling
Multiple order quantity	5
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in
Package weight	1.36 lb
Pallet (layers)	6
Pallet dimensions	48 x 40 x 58.66 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 149 cm
Pallet weight	225.54 kg
Pallet weight	497.23 lb

<b>Products per pallet</b>	300
<b>Products per pallet layer</b>	50
<b>Speaker bandwidth</b>	20 Hz to 20 kHz (multimedia mode); 50 Hz to 7 kHz (wideband mode)
<b>Speaker size</b>	32 mm
<b>Supported bluetooth profiles</b>	A2DP; AVRCP; HFP; HSP
<b>UNSPSC code</b>	52161514
<b>Wireless range</b>	Up to 91 m in open area
<b>Wireless range (imperial)</b>	Up to 300 ft in open area

---

*[1] Protects against Acoustic Shock by limiting sounds to below 118 dBA.*

*[2] With hot-swappable battery.*

---

# Services

## Communication & Collaboration

★ : Recommended

### Poly Support Services

3 year Partner Poly+ Voyager Service	PVOYAG362
3 year Poly+ Voyager Service	PVOYAG312

## Disclaimer — Copyright

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Sep 01, 2025 7:50 AM UTC+0000