


Poly TC8 Touch Controller (875J0AA)

Overview



Easily control your meetings

Launch, join, and share in an instant. The Poly TC8 touch control panel provides easy access to Poly video conferencing solutions. The 8-inch high-resolution touch display makes control options clear and accessible.

Personalize your productivity

The intuitive interface makes it easy to personalize your experience for more productive meetings. And the home screen has an integrated calendar, so it's easy to find your meetings and connect with others.

Pair for success

Poly TC8 is compatible with Poly video solutions, including Poly Studio X video bars and Poly G7500 [1].

Features

Touch display

Intuitive controls are easy to find and use via clear, high-resolution 8-inch touch display.

Single cable

Tidy, professional-looking setup, thanks to sleek design and a single Power over Ethernet cable that carries both power and data.

Simple setup

Easy setup as its pre-paired out of the box when purchased as part of a full Poly video solution.

Integrated calendar

The integrated calendar makes it simple to find your meeting and connect.

Rich controls

Customizable, based on the way you work. Easily share content, adjust the camera, and change participant layouts.

[1] Poly Studio X and Poly G7500 sold separately.

Additional specifications

Aspect ratio	16:10
Certified collaboration software	Zoom; Microsoft Teams
Color	White
Display size (diagonal)	20.3 cm (8")
Horizontal viewing angle	75°
Interoperability	Support for native 3rd party applications includes: Zoom Rooms, 8x8, BlueJeans, GoToRoom, Tencent, RingCentral, DialPad and others (when paired to a Poly Video OS system); Integration with Extron (environmental controls)
Manufacturer Warranty	Poly standard one-year limited warranty
Minimum dimensions (W x D x H)	205 x 123 x 79 mm
Minimum dimensions (W x D x H)	8.07 x 4.84 x 3.11 in
Native resolution	WXGA (1280 x 800)
Non-operating temperature - Celsius	-20 to 60 °C
Non-operating temperature - fahrenheit	-4 to 158 °F
Operating altitude	3,048 m
Operating altitude	10,000 ft
Operating temperature range	32 to 104 °F
Operating temperature range	0 to 40 °C
Panel technology	IPS
Physical security	Standard Kensington lock slot
Ports	1 RJ-45
Power	Power over Ethernet (PoE), compatible with IEEE 802.3af class 3
UNSPSC code	45111902
UPC number	(ABA) 197497663501; (AC3) 197961911428
Vertical viewing angle	75°
Weight	1.79 lb
Weight	812 g
What's in the box	Poly TC8; RJ-45 cable; Warranty card; Quick start guide

Services

Poly Services

★ : Recommended

Poly Support Services

3 Year Poly+ TC8	P30760312 ★
1 Year Partner Poly+ Onsite TC8	P30760158
1 Year Partner Poly+ TC8	P30760160
1 Year Poly Elite Onsite 4hr TC8	E30760914
1 Year Poly Elite Onsite TC8	E30760114
1 Year Poly Elite TC8	E30760112
1 Year Poly+ Onsite Poly TC8	P30760114
1 Year Poly+ TC8	P30760112
1 Year extension of 5yr HW Replacement All Inclusive TC8 advanced part replace Poly DaaS	D30760AL1
1 Year extension of 5yr HW Replacement TC8 with advanced part replacement Poly DaaS	D30760DS1
3 Year Partner Poly+ Onsite TC8	P30760358
3 Year Partner Poly+ TC8	P30760362
3 Year Poly Elite TC8 For Walmart use only	E30760312
3 Year Poly+ Onsite TC8	P30760314
3 Year Upgrade from embedded Poly+ to Partner Poly+ Onsite TC8	P30760788
5 Year Next Business Day HW Replacement TC8 Poly DaaS Service	D30760DS5
Service Reactivation fee TC8 for product less than one year out of support coverage	R30760801
Service Reactivation fee TC8 for product more than one year out of support coverage	R30760802
Upgrade from embedded 1yr Poly+ to 1yr Poly EliteTC8	E30760912
Upgrade from embedded 1yr Poly+ to 1yr Poly+ Onsite TC8	P30760102
Upgrade from embedded 1yr Poly+ to 3yr Partner Poly+ TC8	P30760351
Upgrade from embedded 1yr Poly+ to 3yr Poly+ Onsite TC8	P30760309
Upgrade from embedded 1yr Poly+ to 3yr Poly+ TC8	P30760103
Upgrade from embedded 3yr Partner Poly+ to 3yr Partner Poly+ Onsite TC8 Available only at time of p	P30760555
Upgrade from embedded 3yr Partner Poly+ to 3yr Poly+ Onsite TC8 Available only at time of purchase	P30760444

Professional Services

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Nov 22, 2023 11:10 AM UTC+0000