

ThinkPad P15v Gen 3 (Intel) 21D8007HCA

Lenovo

PSREF
Product Specifications
Reference

PERFORMANCE

Processor

Intel® Core™ i5-12500H, 12C (4P + 8E) / 16T, P-core 2.5 / 4.5GHz, E-core 1.8 / 3.3GHz, 18MB

Graphics^[1]

Integrated Intel® Iris® Xe Graphics

Chipset

Intel® SoC Platform

Memory

2x 16GB SO-DIMM DDR5-4800 Non-ECC

Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Max Memory

Up to 64GB DDR5-4800

Storage

1TB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

Storage Support^[2]

Up to two drives, 2x M.2 SSD

- M.2 2280 SSD up to 4TB, 2TB each
- RAID 0/1 support

Storage Slot

Two M.2 2280 PCIe® 4.0 x4 slots

Card Reader

SD Reader

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby Audio™ Premium

Camera

HD 720p + IR with Privacy Shutter

Microphone

2x, Array

Battery

Integrated 68Wh

Power Adapter

135W Slim Tip (3-pin)

DESIGN

Display^[3]

15.6" UHD (3840x2160) IPS 600nits Anti-glare, 100% Adobe® RGB, DisplayHDR™ 400, Dolby Vision®

Color Calibration

Factory Color Calibration

Keyboard

Backlit, French

Case Color

Black

Case Material

PC-ABS (Top), PC-ABS (Bottom)

Dimensions (WxDxH)^[4]

366.5 x 250 x 22.7 mm (14.43 x 9.84 x 0.89 inches)

Weight^[5]

Starting at 2.096 kg (4.62 lbs)

SOFTWARE

Operating System

Windows® 11 Pro, French

CONNECTIVITY

Ethernet

100/1000M (RJ-45)

WLAN + Bluetooth^[6]

Intel® Wi-Fi® 6E AX211, 11ax 2x2 + BT5.1

WWAN

WWAN Upgradable to 4G

Standard Ports^[7]

- 2x USB 3.2 Gen 1 (one Always On)
- 1x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4)
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)
- 1x SD card reader
- 1x Power connector

Optional Ports (configured)

1x Nano-SIM Card Slot

Docking

Various docking solutions supported via Thunderbolt™, USB-C®, or USB-A.

For more compatible docking solutions, please visit [Docking for ThinkPad® P15v Gen 3 \(Intel®\)](#)

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0 Enabled

Fingerprint Reader

Touch Style, Match-on-Chip, on Palm Rest

Physical Locks

Kensington® Security Slot™, 3 x 7 mm

Other Security

- IR camera for Windows® Hello (facial recognition)
- Camera privacy shutter
- Bottom cover tamper detection

MANAGEABILITY

System Management^[8]

Non-vPro®

SERVICE

Base Warranty

3-year, Courier or Carry-in

Included Upgrade

3Y Sealed Battery Add On, 3Y Premier Support Upgrade from 3Y Courier/CCI

CERTIFICATIONS

Green Certifications^[9]

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- RoHS compliant
- TCO Certified 9.0

Mil-Spec Test

MIL-STD-810H military test passed

ISV Certifications

Please visit [ISV certifications for Lenovo® Workstations](#)

MODEL

TopSeller : Yes

Announce Date : 2023-06-13

EAN / UPC / JAN : 197528678962

End of Support : 2028-10-08



Product image is a sample, it may not match the real color of this model

Note:

^[1] Intel Iris Xe Graphics capability requires system to be.....

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to

<https://psref.lenovo.com/Detail/2003?M=21D8007HCA>

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkPad Hybrid USB-C with USB-A Dock (American Standard Plug Type B)

40AF0135US

- The ThinkPad Hybrid USB-C with USB-A dock is a productivity solution for any USB-C or USB-A laptop, including non-Lenovo laptops from Dell, HP, and Apple, providing power, display, and port expansion in any m...

Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Premier Support (5WS1M86981)
BETTER	3Y Premier Support Plus upgrade from 3Y Premier Support (5WS1L39490)
GOOD	4Y Premier Support upgrade from 3Y Premier Support (5WS1H31743)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference