

# **Specifications and Supplies**

HL-L9430CDN HL-L9470CDN

## ▲ Home > Table of Contents

# **Table of Contents**

Specifications	1
Supplies	7

## ▲ Home > Specifications

# **Specifications**

- >> General Specifications
- >> Print Media Specifications
- >> Printer Specifications
- >> Interface Specifications
- >> Direct Print Feature Specifications
- >> Supported Protocols and Security Features
- >> Computer Requirements Specifications

# **General Specifications**

Printer Type		• Laser			
Print Method		Electrophotographic Laser Printer			
Memory Capacity	Standard	• 1 GB			
Machine display		Liquid Crystal Display (LCD) 3.5 in. (87.6 mm) TFT Color touchscreen LCD <sup>1</sup>			
		• Touchscreen 2.85 x 2.70 in. (72.5 x 68.7 mm)			
Power Source		• 110 V to 120 V AC 50/60 Hz			
Power Consumption	Peak	Approximately 1,050 W			
(Average)	Printing <sup>2</sup>	Approximately 790 W at 77°F (25°C)			
	Printing (Quiet Mode) <sup>2</sup>	Approximately 430 W at 77°F (25°C)			
	Ready <sup>2</sup>	<ul> <li>Approximately 90 W at 77°F (25°C)</li> <li>Approximately 18.4 W</li> </ul>			
	Sleep <sup>2</sup>				
	Deep Sleep <sup>2</sup>	Approximately 1 W			
	Power Off <sup>3 4</sup>	Approximately 0.02 W			
Dimensions		Unit: in. (mm)			
(Typical outline view)		• *: 17.4 (442)			
		**: 15.9 (403)			
**		*** : 21.3 (541)			
*	<del></del>	- HI LO420CDN			
Weights (with supplie	<b>9</b> \$)	• HL-L9430CDN			
		63.4 lb (28.8 Kg)  • HL-L9470CDN			
		64.0 lb (29.0 Kg)			
		04.0 ib (29.0 Ng)			

Noise Level	Sound Pressure	Printing	<ul> <li>1-sided printing LpAm = 55 dB (A)</li> <li>2-sided printing LpAm = 56. 5dB (A)</li> <li>1-sided printing LpAm = 52 dB (A)</li> </ul>
		(Quiet Mode)	LpAm = 52 dB (A)  • 2-sided printing  LpAm = 53 dB (A)
		Ready	• LpAm = $17.2 \text{ dB(A)}^5$
	Sound Power	Printing <sup>6</sup>	Monochrome • LWAd = 6.87 B (A)
			• LWAd = 6.88 B (A)
		Printing	Monochrome
		(Quiet Mode)	
			LWAd = 6.37 B (A)
			2-sided printing
			LWAd = 6.68 B (A)
			Color
			1-sided printing
			LWAd = 6.37 B (A)
			• 2-sided printing
			LWAd = 6.68 B (A)
		Ready	• LWAd = 3.02B (A)
Temperature	Operating		• From 50°F to 90°F (10°C to 32°C)
	Storage		• From 32°F to 104°F (0°C to 40°C)
Humidity	Operating		20% to 80% (without condensation)
	Storage		10% to 90% (without condensation)

- <sup>1</sup> Measured diagonally.
- 2 Measured when the machine is connected to the USB interface.
- Measured according to IEC 62301 Edition 2.0.
- 4 Power consumption varies slightly depending on the usage environment.
- <sup>5</sup> If the fan motor is on: LpAm = 17.2 dB(A)
- <sup>6</sup> Measured in accordance with ISO 7779.

# **Print Media Specifications**

Paper Input	Paper Tray (Standard)	Paper Type	•	Plain Paper, Letterhead, Colored Paper, Thin Paper, Recycled Paper, Thick Paper, Thicker Paper
		Paper Size •		A4, Letter, B5 (JIS), B5 (ISO), A5, A5 (Long Edge), B6 (JIS), A6, Executive, Legal, Mexico Legal, India Legal, Folio, 16K (195x270 mm), A4 Short (270mm Paper)
		Paper Weight	•	16 to 61 lb (60 to 230 g/m <sup>2</sup> )
		Maximum Paper Capacity	•	Up to 520 sheets of 20 lb (80 g/m²) Plain Paper
	Multi-purpose tray (MP tray)	Paper Type	•	Plain Paper, Letterhead, Colored Paper, Thin Paper, Thick Paper, Thicker Paper, Recycled Paper, Bond, Label, Envelope, Env. Thin, Env.Thick, Glossy Paper

Danas Image	Multi muma cas tura (AAD	Damar C!	- Midth:			
Paper Input	Multi-purpose tray (MP tray)	Paper Size	• Width:			
	,		3 to 8.5 in. (76.2 to 215.9 mm)			
			• Length:			
			5 to 14 in. (127 to 355.6 mm)			
			• Envelope:			
			COM-10, DL, C5, Monarch			
		Paper Weight	• 16 to 61 lb (60 to 230 g/m <sup>2</sup> )			
		Maximum	• Up to 100 Sheets of 20 lb (80 g/m²) Plain Paper			
		Paper Capacity	Envelope: 15 envelopes			
	Paper Tray 2, 3, 4 (Optional) <sup>1</sup>	Paper Type	Plain Paper, Letterhead, Colored Paper, Thin Paper, Recycled Paper			
	Paper Size		A4, Letter, B5 (JIS), A5, Executive, Legal, Mexico Legal, India Legal, Folio, 16K (195x270 mm), A4 Short (270mm Paper)			
		Paper Weight	• 16 to 28 lb (60 to 105 g/m <sup>2</sup> )			
	Maximur		• LT-330CL			
		Paper Capacity	Up to 250 sheets of 20 lb (80 g/m²) Plain Paper			
			• LT-340CL			
			Up to 500 sheets of 20 lb (80 g/m²) Plain Paper			
Paper Output <sup>2</sup>	Face Down Output Tray		Up to 250 Sheets of 20 lb (80 g/m²) Plain Paper (face down delivery to the face down output paper tray)			
	Face Up Output Tray		One sheet (face up delivery to the face up output tray)			
	Mailbox		• 100 sheets x 4 bins of 20 lb (80 g/m²)			
	(Optional)		400 sheets x 2 bins of 20 lb (80 g/m <sup>2</sup> )			
2-sided	Automatic 2-sided Printing	Paper Type	Plain Paper, Letterhead, Colored Paper, Thin Paper, Thick Paper, Thicker Paper, Recycled Paper, Glossy Paper			
	Paper Size		Select the paper size you want to use by sliding the 2-sided lever:			
			A4, A4 Short (270mm Paper)			
			Letter, Legal, Mexico Legal, India Legal, Folio			
			1			

Maximum number of Lower Trays: Up to three LT-330CL Lower Trays, or two LT-340CL, or a combination of one LT-330CL and one LT-340CL.

# **Printer Specifications**

Automatic 2-sided Print • Yes				
Emulation		<ul> <li>PCL5e, PCL5c, PCL6 (PCL XL Class3.0), BR-Script3, PDF Version 1.7, XPS Version 1.0</li> </ul>		
Resolution		• 600 x 600 dpi, 2,400 dpi class (2400 x 600) quality		
Print Speed 1 2 1-sid	ded Print <sup>3</sup>	Monochrome		
		Up to 42 pages/minute (Letter size)		
		Up to 40 pages/minute (A4 size)		
		Color		
	-	Up to 42 pages/minute (Letter size)		

<sup>&</sup>lt;sup>2</sup> For labels, we recommend removing the printed sheets from the output paper tray immediately after they exit the machine to avoid the possibility of smudging.

Print Speed <sup>1 2</sup>	1-sided Print <sup>3</sup>	Up to 40 pages/minute (A4 size)		
2-sided Print		<ul> <li>Monochrome</li> <li>(HL-L9430CDN) Up to 29 sides/minute (Up to 14 sheets/minute) (Letter size) Up to 28 sides/minute (Up to 14 sheets/minute) (A4 size) </li> <li>(HL-L9470CDN) Up to 42 sides/minute (Up to 21 sheets/minute) (Letter size) </li> </ul>		
		Up to 40 sides/minute (Up to 20 sheets/minute) (A4 size)  Color  (HL-L9430CDN)  Up to 29 sides/minute (Up to 14 sheets/minute) (Letter size)  Up to 28 sides/minute (Up to 14 sheets/minute) (A4 size)  (HL-L9470CDN)  Up to 42 sides/minute (Up to 21 sheets/minute) (Letter size)  Up to 40 sides/minute (Up to 20 sheets/minute) (A4 size)		
First Print Time <sup>4 5 6 7</sup>		Monochrome Less than 10 seconds at 73.4°F (23°C) / 115 V		
		• Less than 10 seconds at 73.4°F (23°C) / 115 V		

- 1 The print speed may change depending on the type of document you print.
- <sup>2</sup> The print speed may be slower when the machine is connected by wireless LAN.
- Measured in accordance with ISO/IEC 24734.
- 4 Printing from Ready mode and standard tray.
- 5 Length of time from when the machine is started until paper output is complete (except when the machine is turned on or when an error is fixed).
- <sup>6</sup> May vary when calibration or registration is in progress.
- 7 This applies when printing on A4- or Letter-size paper from the standard tray. It could be longer however, depending on the paper size and the amount of print data.

## **Interface Specifications**

USB <sup>1 2</sup>	Hi-Speed USB 2.0
	Use a USB 2.0 interface cable that is no more than 6 feet (2 meters) long.
LAN	• 10Base-T/100Base-TX/1000Base-T <sup>3</sup>
Wireless LAN	IEEE 802.11a/b/g/n (Infrastructure Mode)
4	IEEE 802.11a/g/n (Wi-Fi Direct®)
NFC <sup>5</sup>	• Yes

- 1 Your machine has a USB 2.0 Hi-Speed interface. The machine can also be connected to a computer that has a USB 1.1 interface.
- <sup>2</sup> Third-party USB hub devices are not supported.
- <sup>3</sup> Use a Category 5e (or greater) network cable.
- <sup>4</sup> For certain models, the wireless network connection can be used only when the optional Wireless Module is installed.
- 5 When you connect an external IC card reader, use a HID class driver supported device.

## **Direct Print Feature Specifications**

Compatibility	•	PDF version1.7, JPEG, Exif+JPEG, PRN (created by the machine's own printer driver), TIFF (scanned by Brother models), XPS version 1.0
Interface	•	USB direct interface : Front x 1, Rear x 1

## **Supported Protocols and Security Features**

#### **Ethernet**

10Base-T/100Base-TX/1000Base-T

#### Wireless LAN (5 GHz)

IEEE 802.11a/n (Infrastructure Mode), IEEE 802.11a/n (Wi-Fi Direct)

#### Wireless LAN (2.4 GHz)

IEEE 802.11b/g/n (Infrastructure Mode), IEEE 802.11g/n (Wi-Fi Direct)

#### Protocols (IPv4)

ARP, RARP, BOOTP, DHCP, APIPA (Auto IP), WINS/NetBIOS name resolution, DNS Resolver, mDNS, LLMNR responder, LPR/LPD, Custom Raw Port/Port9100, IPP/IPPS, FTP Server, TELNET Server, HTTP/HTTPS server, TFTP client and server, SMTP Client, SNMPv1/v2c/v3, ICMP, Web Services (Print), CIFS client, SNTP client, LDAP

#### Protocols (IPv6)

NDP, RA, DNS resolver, mDNS, LLMNR responder, LPR/LPD, Custom Raw Port/Port9100, IPP/IPPS, FTP Server, TELNET Server, HTTP/HTTPS server, TFTP client and server, SMTP Client, SNMPv1/v2c/v3, ICMPv6, Web Services (Print), CIFS Client, SNTP Client, LDAP

## **Network Security (Wired)**

SMTP-AUTH, SSL/TLS (IPPS, HTTPS, SMTP), SNMP v3, 802.1x (EAP-MD5, EAP-FAST, PEAP, EAP-TLS, EAP-TTLS), Kerberos, IPsec

#### **Network Security (Wireless)**

SMTP-AUTH, SSL/TLS (IPPS, HTTPS, SMTP), SNMP v3, 802.1x (EAP-FAST, PEAP, EAP-TLS, EAP-TTLS), Kerberos, IPsec

#### **Wireless Network Security**

WEP 64/128 bit, WPA-PSK (TKIP/AES), WPA2-PSK (TKIP/AES) (Wi-Fi Direct supports WPA2-PSK (AES) only)

#### **Wireless Certification**

Wi-Fi Certification Mark License (WPA<sup>™</sup>/WPA2<sup>™</sup> - Enterprise, Personal), Wi-Fi Protected Setup<sup>™</sup> (WPS) Identifier Mark License, Wi-Fi CERTIFIED<sup>™</sup> Wi-Fi Direct

## **Computer Requirements Specifications**

Supported Operating Systems And Software Functions

Computer Platform & Operating System Version		Computer	mputer Interface				Hard Disk Space to Install	
		Parallel (IEEE128 4)	USB <sup>1</sup>	10Base-T/ 100Base- TX/ 1000Base -T (Ethernet) Wireless 2 802.11a/b /g/n		ssor	For Drivers	For Application s (including Drivers)
Windows Operating System	Windows 7 SP1 / 8.1 <sup>1 3</sup>	N/A	Printing			32 bit (x86) or 64 bit	50 MB	1.6 GB
	Windows 10 Home / 10 Pro / 10 Education / 10 Enterprise <sup>1</sup>					(x64) proces sor		
	Windows Server 2008 SP2 <sup>3</sup>		Printing					50 MB

	Windows Server 2008 R2 <sup>3</sup>		64 bit (x64)		
	Windows Server 2012		proces		
	Windows Server 2012 R2				
	Windows Server 2016				
	Windows Server 2019				
Mac	macOS v10.14.x	Printing	64 bit	N/A	500 MB
Operating System <sup>4</sup>	macOS v10.15.x		(x64) proces		
System	macOS v11		sor		

<sup>&</sup>lt;sup>1</sup> Third-party USB ports are not supported.

For the latest driver updates, go to your model's **Downloads** page at <u>support.brother.com</u>. All trademarks, brand and product names are the property of their respective companies.

<sup>&</sup>lt;sup>2</sup> For certain models, the optional Wireless Module is required.

<sup>3</sup> Windows 7 / Server 2008 / Server 2008 R2 supported by Extended Security Updates until Jan 10, 2023.

<sup>4</sup> macOS Disclaimer. AirPrint capable: Printing via Mac requires using AirPrint. Mac printer driver is not provided.

## ▲ Home > Supplies

# **Supplies**

When the time comes to replace supplies, such as the toner cartridge or drum unit, an error message will appear on your machine's control panel or in the Status Monitor. For more information about the supplies for your machine, visit <a href="https://www.brother.com/original">www.brother.com/original</a> or contact your local Brother dealer.



The Supply Order Number (No.) will vary depending on your country and region.

Supply Items	Supply Order No.	Approximate Life (Page Yield)	Applicable Models
Toner Cartridge	Standard Toner: TN810	<ul> <li>Black:         Approximately 9,000 pages <sup>1 2</sup> </li> <li>Cyan / Magenta / Yellow:         Approximately 6,500 pages <sup>1 2</sup> </li> </ul>	HL-L9430CDN/HL-L9470CDN
	High Yield Toner: TN810XL	<ul> <li>Black:         Approximately 12,000 pages <sup>1 2</sup> </li> <li>Cyan / Magenta / Yellow:         Approximately 9,000 pages <sup>1 2</sup> </li> </ul>	HL-L9430CDN/HL-L9470CDN
	Super High Yield Toner: TN815	<ul> <li>Black:         Approximately 15,000 pages <sup>1 2</sup> </li> <li>Cyan / Magenta / Yellow:         Approximately 12,000 pages <sup>1 2</sup> </li> </ul>	HL-L9430CDN/HL-L9470CDN
	Starter Toner: (Supplied with your machine)	<ul> <li>Black:         Approximately 9,000 pages <sup>1 2</sup> </li> <li>Cyan / Magenta / Yellow:         Approximately 6,500 pages <sup>1 2</sup> </li> </ul>	HL-L9430CDN/HL-L9470CDN
Drum Unit	• DR810CL	Approximately     100,000 pages <sup>3</sup>	HL-L9430CDN/HL-L9470CDN
Belt Unit	• BU800CL	Approximately     150,000 pages <sup>4</sup>	HL-L9430CDN/HL-L9470CDN

Supply Items	Supply Order No.	Approximate Life (Page Yield)	Applicable Models
Waste Toner Box	• WT800CL	Approximately     100,000 pages <sup>2 5 6</sup>	HL-L9430CDN/HL-L9470CDN

- 1 The approximate cartridge yield is declared in accordance with ISO/IEC 19798.
- 2 Letter or A4 size single-sided pages
- 3 Approximately 100,000 pages based on three pages per job (A4/Letter single-sided pages). The number of pages may be affected by a variety of factors including but not limited to media type and media size.
- 4 Approximately 150,000 pages based on two pages per job (A4/Letter single-sided pages). The number of pages may be affected due to a variety of factors including but not limited to media type and media size.
- 5 Approximate waste toner box yield is declared in accordance with ISO/IEC 19798.
- 6 The number of pages may be affected due to a variety of factors including but not limited to media type and media size.

Brother International Corporation 200 Crossing Boulevard P.O. Box 6911 Bridgewater, NJ 08807-0911 USA

Brother International Corporation (Canada) Ltd. 1 rue Hôtel de Ville, Dollard-des-Ormeaux, QC, Canada H9B 3H6



These machines are approved for use in the country of purchase only. Local Brother companies or their dealers will support only machines purchased in their own countries.

