

HP Color LaserJet Managed MFP E47528f (3QA75A)



HP's entry-level Enterprise-class Color MFP with speeds up to 27 ppm[10] and strongest security.[1]

HP Managed MFPs and printers are optimized for managed environments. With increased monthly page volumes and fewer interventions, this portfolio of products can help reduce printing and copying costs. See your HP Authorized Reseller for details.



Easy to use, simple to manage

HP FutureSmart firmware can be updated with the latest features[2] to optimize your investment for years to come.

HP's most secure printing[1]

The operating code (BIOS) is automatically checked during startup and repairs itself if compromised.

Enhanced productivity to empower work teams

Give workgroups what they need to succeed with hundreds of HP and third-party solutions and card reader support.

Specifications

Print Resolution Technologies	HP ImageREt 3600, Enhanced (600x600 dpi), Fine Lines (1200x1200 dpi), Quickview (300x300 dpi)
Print quality black (best)	Up to 600 x 600 dpi
Print quality color (best)	Up to 600 x 600 dpi
Print speed black (ISO, A4)	Up to 27 ppm
Print speed black (ISO, letter)	Up to 29 ppm
Print Speed Color (ISO)	Up to 27 ppm
Print speed color (ISO)	Up to 29 ppm
Print speed	Print speed up to 29 ppm (black) and 29 ppm (color)
Functions	Print, copy, scan, fax
Duplex printing	Automatic (default)
Duty cycle (monthly, A4)	Up to 65,000 pages
Duty cycle (monthly, letter)	Up to 65,000 pages
Printer smart software features	Print preview, duplex printing, print multiple pages per sheet (2, 4, 6, 9, 16), collation, watermarks, store print jobs, easy-access USB
Copier smart software features	Auto scale; Reduce/enlarge from scanner glass (25 to 400 percent); Collate; Auto color detection; Two-sided copying; Image adjustments (darkness, background cleanup, sharpness); Job build
Scanner advanced features	Optimize text/picture; Image adjustments; Job build; Output quality setting; Selectable scan resolution 75 to 600 dpi; Auto detect color; Edge Erase; Job notification; Blank page suppression; HP Quick Sets
Fax smart software features	Stored faxes; Fax archiving; Fax forwarding; Scale to fit; Fax address book; LAN/Internet fax; Fax number confirmation; Holiday fax schedule
Energy savings feature technology	HP Auto-On/Auto-Off Technology; Instant-on Technology; Instant-on Copy
Replacement cartridges	HP Black Managed Original LaserJet Toner Cartridge ~8600 pages W9090MC HP Cyan Managed Original LaserJet Toner Cartridge ~6900 pages W9091MC HP Yellow Managed Original LaserJet Toner Cartridge ~6900 pages W9092MC HP Magenta Managed Original LaserJet Toner Cartridge ~6900 pages W9093MC ^[2]
Supplies feature	HP JetIntelligence Cartridge
Connectivity, standard	2 Hi-Speed USB 2.0 Host; 1 Hi-Speed USB 2.0 Device; 1 Gigabit Ethernet 10/100/1000T network; 1 FAX
Connectivity, optional	HP Jetdirect LAN Accessory 8FP31A, HP Jetdirect 3100w BLE/NFC/Wireless Accessory 3JN69A
Modem	33.6 kbps
Network capabilities	Yes, via HP Jetdirect Ethernet embedded print server (standard) which supports: 10Base-T, 100Base-Tx, 1000Base-T; 802.3az (EEE) support on Fast Ethernet and Gig Links; IPsec (standard); 802.11a/b/g/n wireless networking (Optional); second Ethernet port (Optional).
Wireless capability	Optional, enabled with purchase of a wireless hardware accessory. Dual band Wireless Station and Wi-Fi Direct functionality available with HP Jetdirect 3100w BLE/NFC/Wireless Accessory 3JN69A
Mobile printing capability	HP ePrint; Apple AirPrint™; Mopria™ Certified; Wi-Fi® Direct Printing; NFC Touch-to-print (optional); Roam capable for easy printing; PrinterOn Print
Network protocols, supported	Via built-in networking solution: TCP/IP, IPv4, IPv6; Print: TCP-IP port 9100 Direct Mode, LPD, Web Services Printing, IPP 2.0, Apple AirPrint™, HP ePrint; Discovery: SLP, Bonjour, Web Services Discovery; IP Config: IPv4 (BootP, DHCP, AutoIP, Manual), IPv6 (Stateless Link-Local and via Router, Statefull via DHCPv6); Management: SNMPv2/v3, HTTP/HTTPS, Syslog; Security: SNMPv3, SSL Cert Management, IPSec(IKEv1 and IKEv2), Firewall, 802.1x
Software included	No software solutions are included in the Box only on http://hp.com or http://123.hp.com
Compatible Operating Systems	Windows 11; Windows 10; Windows 8; Windows 8.1; Windows 7; Windows Client OS; Android; iOS; Mobile OS; macOS 10.12 Sierra; macOS 10.13 High Sierra; macOS 10.14 Mojave; macOS 10.15 Catalina
Technical features	ADF; AirPrint; Automatic two-sided printing; Compact size; ENERGY STAR®; HP Auto-On/Auto-Off; HP ePrint; JetIntelligence Toners; Walk-up USB (doc, ppt, pdf, jpg)
Sustainable impact specifications	Mercury-free
Energy star certified	Yes
Ecolabels	EPEAT® Silver; CECP; ENERGY STAR® certified
Blue Angel compliant	Yes, Blue Angel DE-UZ 219—only ensured when using Original HP supplies
Copy speed (black, normal quality, A4)	Up to 27 cpm
Copy speed (color, normal quality, A4)	Up to 27 cpm
Copy speed black (normal, letter)	Up to 28 cpm
Copy speed color (normal, letter)	Up to 28 cpm

Copy speed black duplex (A4)	Up to 24 cpm
Copy speed black duplex (Letter)	Up to 25 cpm
Digital sending standard features	Scan to E-mail; Save-to-Network Folder; Save-to-USB drive; Scan-to-Sharepoint; Send to FTP; Send to Internet Fax; Local Address Book; SMTP over SSL; Blank Page Removal; Edge Erase; Auto Color Sense; Auto Crop To Content; Compact PDF
Fax Resolution Black (best)	Up to 300 x 300 dpi
Faxing	Yes
Scan speed (normal, A4)	Up to 29 ppm/46 ipm (b&w), up to 20 ppm/35 ipm (color)
Scan speed (normal, letter)	Up to 31 ppm/49 ipm (b&w), up to 21 ppm/37 ipm (color)
Scan technology	Contact Image Sensor (CIS)
Scanner type	Flatbed, ADF
Display area (imperial)	3.74 x 2.12 in
Display area (metric)	95 x 53.86 mm
Display	4.3" diagonal Color TFT-LCD back-lit 480 RGB (H) x 272 (V)
Minimum dimensions (W x D x H)	415.4 x 472 x 399.8 mm
Minimum dimensions (W x D x H)	16.4 x 18.6 x 15.7 in
Weight	23.2 kg (With Print Cartridges)
Weight	51.2 lbs (With Print Cartridges)
Power consumption	581 watts (active printing), 21.9 watts (ready), 1.0 watts (sleep), 0.08 watts (auto-off/manual-on), 0.08 watts (manual off) (Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty.)
Power supply type	Internal (Built-in) power supply
What's in the box	HP Color LaserJet Managed MFP E47528f printer; HP Black Original LaserJet Toner Cartridge (~2,400 pages); HP Cyan, Magenta, Yellow Original LaserJet Toner Cartridges (~2,100 pages each); Fixed-Size Paper Tray Guides; Getting started Guide; 1 Power cord ^[1]
Manufacturer Warranty	One-Year, On-site Repair 24-hour / 7 day a week phone support

Top Recommended Displays, Accessories and Services

Imaging and Printing Hardware Support Onsite Svc

HP 3 year Next Business Day w/DMR Service for Color LaserJet Managed MFPE47528	U11VKE
HP 3 year 4 hour 9x5 w/DMR Service for Color LaserJet Managed MFP E47528	U11VNE

Imaging and Printing Commercial Care Pack Services

HP Installation Service with network configuration for Workgroup Printer(1 unit)	U9JT2E
--	--------

Messaging Footnotes

[1] HP's most advanced embedded security features are available on HP Enterprise and HP Managed devices with HP FutureSmart firmware 4.5 or above. Claim based on HP review of 2019 published features of competitive in-class printers. Only HP offers a combination of security features to automatically detect, stop, and recover from attacks with a self-healing reboot, in alignment with NIST SP 800-193 guidelines for device cyber resiliency. For a list of compatible products, visit hp.com/go/PrintersThatProtect. For more information, visit hp.com/go/PrinterSecurityClaims

[2] Some features enabled by future HP FutureSmart firmware upgrades may not be available on older devices, if for example, physical product characteristics limit the functionality of the new feature.

[10] Measured using ISO/IEC 24734, excludes first set of test documents. For more information, see <http://www.hp.com/go/printerclaims>. Exact speed varies depending on the system configuration, software application, driver, and document complexity.

Technical Specifications Footnotes

[1] For yield information on the cartridge(s) included with your printer, see <http://www.hp.com/go/toneryield>. Yield values measured in accordance with ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors.

[2] Declared yields based on ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see <http://www.hp.com/go/toneryield>.

Learn more at
<http://www.hp.com/uk>

The product could differ from the images shown. © 2014 Hewlett-Packard Development Company, L.P. The Information contained herein is subject to change without notice. Warranties for HP products and services are set out in the express warranty statements accompanying such products and services. In addition, our products and services come with guarantees that cannot be excluded under the Australian Consumer Law. Subject to the foregoing, nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

