

# Eaton 5E700UIAU

Catalog Number: 5E700UIAU

Eaton 5E Gen2 UPS USB AU, 700 VA, 360 W, Input:cord, Outputs: (2) AU, Tower

## General specifications

Product Name	Catalog Number
Eaton 5E Gen2 UPS	5E700UIAU
Product Length/Depth	Product Height
288 mm	148 mm
Product Width	Product Weight
100 mm	4.28 kg
Warranty	Compliances
2 year	LVD Directive
	EMC Directive
	RoHS Directive
	Packaging Directive
	WEEE Directive
	Batteries Directive
	CB



## Certifications

IEC/EN 62040-3  
IEC/EN 62040-1  
IEC/EN 62040-2  
CE  
EAC  
UKCA  
Cm  
Ukr  
RCM

## Product specifications

## Resources

### Secondary frequency - max

60 Hz

### Wattage

360 W

### Form factor

Tower

### Includes network card

No

### Input connection

AU plug

### Input voltage - min

140 V

### Output voltage - max

257 V

### Secondary frequency - min

50 Hz

### Software compatibility

Eaton UPS Companion (enables safe system shutdown, energy usage metering and configuration of UPS settings)

### Battery type

Sealed, lead-acid

### Efficiency

95

### Special features

Automatic Voltage Regulation (AVR)

Saves space with a compact tower design

HID-compliant USB port, for automatic integration with major operating systems (Windows/Mac OS/Linux)

### Construction type

Free standing model

### Output voltage - min

195 V

### Color

Black

### Extended battery capability

No

Output voltage range

195-257 V

Topology

Line-interactive

Surge protection

Yes

Input nominal voltage

240V

Input frequency range

45-65 Hz

Internal bypass

No

Input voltage - max

300 V

Voltage type

AC

Phase (output)

1

Battery management

Automatic battery test, deep-discharge protection, cold-start capable

Auto shutdown function

Yes

Number of Outputs C13

2

Operating temperature - min

0 °C

VA rating

700 VA

Potential free switch contact

No

Receptacle

(2) AU

Phase (input)

1

Package contents

Quick start

Safety instructions

Noise level

<25 dB at 1 meter

Feed type

1

Runtime graph

[View runtime graph](#)

User interface

LEDs

Battery quantity

1

Operating temperature - max

40 °C

Voltage

240V

Hot swap power

No

Temperature range

0° to 40°C (32° to 104°F)

Ethernet interface

No

Communication

USB port (HID compliant)

Relative humidity

0-85% non-condensing

Output apparent power

700 VA

Rack mounting kit

No

Output frequency

50/60 Hz

Type of interface

USB

Primary frequency - min

45 Hz

Battery rating

12 V / 7 Ah

Type

UPS

Output nominal voltage

240V

Input voltage range

140-300 V

Nominal frequency

50/60 Hz

Primary frequency - max

65 Hz



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All rights reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)