

Eaton 5E2200UIAU

Catalog Number: 5E2200UIAU

Eaton 5E Gen2 UPS USB AU, 2200 VA, 1200 W, Input:cord,
Outputs: (3) AU, Tower

General specifications

| | |
|----------------------|---------------------|
| Product Name | Catalog Number |
| Eaton 5E Gen2 UPS | 5E2200UIAU |
| Product Length/Depth | Product Height |
| 330 mm | 180 mm |
| Product Width | Product Weight |
| 133 mm | 9.8 kg |
| Warranty | Compliances |
| 2 year | RoHS Directive |
| | LVD Directive |
| | Packaging Directive |
| | WEEE Directive |
| | Batteries Directive |
| | EMC Directive |
| | CB |



Certifications

IEC/EN 62040-3
IEC/EN 62040-1
IEC/EN 62040-2
CE
EAC
UKCA
Cm
Ukr

Product specifications

Resources

Secondary frequency - max

60 Hz

Wattage

1200 W

Form factor

Tower

Includes network card

No

Input connection

AU plug

Input voltage - min

140 V

Output voltage - max

257 V

Secondary frequency - min

50 Hz

Software compatibility

Eaton UPS Companion (enables safe system shutdown, energy usage metering and configuration of UPS settings)

Battery type

Sealed, lead-acid

Efficiency

95

Special features

Automatic Voltage Regulation (AVR)

Saves space with a compact tower design

HID-compliant USB port, for automatic integration with major operating systems (Windows/Mac OS/Linux)

Construction type

Free standing model

Output voltage - min

195 V

Color

Black

Extended battery capability

No

Output voltage range

195-257 V

Topology

Line-interactive

Surge protection

Yes

Input nominal voltage

240V

Input frequency range

45-65 Hz

Internal bypass

No

Input voltage - max

300 V

Voltage type

AC

Phase (output)

1

Battery management

Automatic battery test, deep-discharge protection, cold-start capable

Auto shutdown function

Yes

Number of Outputs C13

3

Operating temperature - min

0 °C

VA rating

2200 VA

Potential free switch contact

No

Receptacle

(3) AU

Phase (input)

1

Package contents

Quick start

Safety instructions

Noise level

<40 dB at 1 meter

Feed type

1

Runtime graph

[View runtime graph](#)

User interface

LEDs

Battery quantity

2

Operating temperature - max

40 °C

Voltage

240V

Hot swap power

No

Temperature range

0° to 40°C (32° to 104°F)

Ethernet interface

No

Communication

USB port (HID compliant)

Relative humidity

0-85% non-condensing

Output apparent power

2200 VA

Rack mounting kit

No

Output frequency

50/60 Hz

Type of interface

USB

Primary frequency - min

45 Hz

Battery rating

12 V / 9 Ah

Type

UPS

Output nominal voltage

240V

Input voltage range

140-300 V

Nominal frequency

50/60 Hz

Primary frequency - max

65 Hz



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All rights reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)