



VIEWSONIC 32" 1080P IPS 75HZ MONITOR WITH HDMI, VGA | VA3209M

Key Features


- Versatile Monitor: 32 Inch Full HD (1920x1080p) IPS monitor with thin bezels and 75Hz refresh rate
- Enhanced Viewing Comfort: Flicker-Free technology and Blue Light Filter for reduced eye fatigue
-
- No Image Tearing: Variable Refresh Rate enables smooth frame rates to aid you in battle
- Optimized View Settings: Offers "Game," "Movie," "Web," "Text," and "Mono" presets
- Flexible Connectivity: The VA3209M supports laptops, PCs, Macs and more with HDMI and VGA inputs



32
DISPLAY



IPS
PANEL



1920 x 1080
RESOLUTION



Product Description

Get the bigger picture with the ViewSonic® VA3209m home office monitor.

Featuring an expansive 32" (31.5" viewable) display with SuperClear® IPS panel technology, this immersive monitor delivers stunning brightness and contrast at almost any viewing angle.

With a minimalist edge-to-edge screen and a three-sided frameless bezel, creating a seamless multi-monitor setup has never been easier.

Connect laptops, PCs, gaming consoles and other multimedia devices to this 32" monitor via HDMI or VGA.



And with state-of-the-art features like flicker-free technology and a blue light filter, you can work or play for longer with less eye strain.

Enjoy a three-year limited warranty and an industry-leading pixel performance guarantee with the ViewSonic VA3209M Full HD 1080p monitor.

Specifications

	More Information
UPC	766907022810
Screen Size	32
Viewable Area (in.)	31.5
Panel Type	IPS
Display Resolution	1920 x 1080
Display Resolution	Full HD (1920x1080)
Static Contrast Ratio	1,200:1
Dynamic Contrast Ratio	50,000,000:1
Light Source	LED
Brightness	250 cd/m2
Colors	16.7M
Color Space Support	8 bit true
Aspect Ratio	16:9
Response Time (Typical GTG)	4ms
Viewing Angles	178º horizontal, 178º vertical
Backlight Life (Hours)	30,000
Panel Surface	Anti-Glare (Semi-Glossy) type, Hardness 2H
Refresh Rate	75Hz
PC Resolution (max)	1920 x 1080
Mac® Resolution (max)	1920 x 1080
3.5mm Audio Out	1
VGA	1
HDMI 1.4 In	1
Internal Speakers	2.5W (x2)
Eco Mode (Conserve)	25w
Eco Mode (optimized)	29w
Consumption (typical)	34w
Consumption (max)	39w
Voltage	100-240 VAC, 50-60Hz
Stand-by	0.5w
Power Supply	External
Cable Organization	No
Kensington Lock Slot	1

Physical Controls	Key 1 (favorite), Key 2, Key 3, Key 4, Key 5 (power)
On Screen Display	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu
Temperature	32-104º F (0 - 40º C)
Humidity (non-condensing)	20-90%
VESA Compatible	100 x 100 mm
Frequency Horizontal	24 ~ 86 KHz
Frequency Vertical	48 ~ 75 Hz
Tilt (Forward/Back)	5º / 20º
Regulations	cTUVus, FCC-B, ICES003, CEC
Net (lbs)	16.1
Net Without Stand (lbs)	13.4
Gross (lbs)	20.3
Net (kg)	7.3
Net Without Stand (kg)	6.1
Gross (kg)	9.2
Packaging (in.)	30.3 " (W) x 20.1 " (H) x 4.9 " (D)
Physical (in.)	28.1 " (W) x 20.5 " (H) x 9.1 " (D)
Physical Without Stand (in.)	28.1 " (W) x 16.8 " (H) x 2.3 " (D)
Packaging (mm)	770 mm (W) x 510 mm (H) x 125 mm (D)
Physical (mm)	714 mm (W) x 520 mm (H) x 231 mm (D)
Physical Without Stand (mm)	714 mm (W) x 428 mm (H) x 59 mm (D)
Package Contents	LCD Display, Power Cable, HDMI to HDMI Cable, Quick Start Guide
Recycle/Disposal	Please dispose of in accordance with local, state or federal laws.
Warranty	Three-year limited warranty on parts, labor and backlight
UPC: 766907022810	



Contact Sales

[ViewSonic.com](https://www.viewsonic.com)

888.881.8781 📞

email:

salesinfo@viewsonic.com

