

HP Color LaserJet Pro 4201dn Printer (4RA85F)



Fast color printing and easy set up.

Get a blazing fast color printer and easy set up with LaserJet Pro.



Maximum productivity in full color

Support your business workteam with this compact, high-performing, color printer, ideal for up to 10 users.

Simple set up

Quickly set up your printers so you can focus more on your business

Advance your security with HP Wolf Pro

Get printer fleet security out of the box. Preconfigured settings mean it's ready when you are.

Featuring

Business team solution

Blazing fast speed

Self-healing Wi-Fi® [7] [7]

True-to-life colors [14] [14]

HP Web Jetadmin. [3] [3]

Specifications

Print Resolution Technologies	HP ImageREt 2400, PANTONE® calibrated
Print quality black (best)	Up to 600 x 600 dpi
Print quality color (best)	Up to 600 x 600 dpi
Print speed black (ISO, A4)	Up to 33 ppm
Print speed black (ISO, letter)	Up to 35 ppm
Print Speed Color (ISO)	Up to 33 ppm
Print speed color (ISO)	Up to 35 ppm
Print speed	Print speed up to 35/33 ppm black & color (Letter/A4)
Functions	Print
Duplex printing	Automatic
Duty cycle (monthly, A4)	Up to 50,000 pages
Duty cycle (monthly, letter)	Up to 50,000 pages
Printer smart software features	Automatic duplex, collation, watermarks, printable forms, quiet mode, HP premium print quality mode, accepts a variety of paper sizes and types
Energy savings feature technology	HP Auto-On/Auto-Off Technology; Instant-on Technology
Replacement cartridges	HP 210A Black Original LaserJet Toner Cartridge (~2,000 pages) W2100A; HP 210A Cyan Original LaserJet Toner Cartridge (~1,800 pages) W2101A; HP 210A Yellow Original LaserJet Toner Cartridge (~1,800 pages) W2102A; HP 210A Magenta Original LaserJet Toner Cartridge (~1,800 pages) W2103A; HP 210X Black Original LaserJet Toner Cartridge (~7,500 pages) W2100X; HP 210X Cyan Original LaserJet Toner Cartridge (~5,500 pages) W2101X; HP 210X Yellow Original LaserJet Toner Cartridge (~5,500 pages) W2102X; HP 210X Magenta Original LaserJet Toner Cartridge (~5,500 pages) W2103X ^[2]
Supplies feature	TerraJet Cartridge
Connectivity, standard	1 Hi-Speed USB 2.0 (device); 1 Hi-Speed USB 2.0 (host); 1 Gigabit Ethernet 10/100/1000 Base-TX network
Network capabilities	Yes, via built-in 10/100/1000Base-Tx Ethernet, Gigabit; Auto-crossover Ethernet; Authentication via 802.1x
Mobile printing capability	HP Smart App; Apple AirPrint™; Mobile Apps; Mopria™ Certified
Network protocols, supported	TCP/IP, IPv4, IPv6; Print: TCP-IP port 9100 Direct Mode, LPD (raw queue support only), Web Services Printing, Apple AirPrint™, Mopria, IPP Print; Discovery: SLP, Bonjour, Web Services Discovery; IP Config: IPv4 (DHCP, AutoIP, Manual), IPv6 (Stateless Link-Local and via Router, Stateful via DHCPv6), SSL Security and Certificate management; Management: SNMPv1, SNMPv2, SNMPv3, HTTP/HTTPS, Syslog
Software included	No software solutions are included in the Box only on http://hp.com or http://123.hp.com
Compatible Operating Systems	Windows 11; Windows 10; Windows Client OS; Android; iOS; Mobile OS; macOS 10.15 Catalina; macOS 11 Big Sur; macOS 12 Monterey; Linux; Citrix; Chrome OS (Citrix Ready Kit Certification - Up to Citrix Server 7.18 for more information see http://citrixready.citrix.com ; Citrix Server 6.5; Citrix XenApp & XenDesktop 7.6; Linux- For more information see http://developers.hp.com/hp-linux_imaging-and-printing ; Novell iPrint server; Unix- For more information see http://hp.com/go/unixmodelscripts ; Windows Server 2008 R2 64-bit ; Windows Server 2012 64-bit; Windows Server 2012 R2 64-bit; Windows Server 2016 64-bit; Windows Server 2019 64-bit; Windows Server 2022 64-bit; (All operating systems with the latest updates); Android; iOS; macOS Big Sur v11.0; macOS Catalina v10.15; macOS Monterey v12.0; macOS's-; Mobile OS's-; Win10; Win11; Windows Client OS (32/64 bit)-; (All operating systems with the latest updates))
Technical features	Automatic 2-sided printing; Cloud-based fleet management; Compact size; ENERGY STAR®; Network printing; HP Auto-on/Auto-off; TerraJet Toner; Private Print via PIN; Professional print quality; Made with recycled plastic
Sustainable impact specifications	ENERGY STAR® certified; EPEAT® registered; Contains at least 10% post-consumer recycled plastic
Energy star certified	Yes
Ecolabels	IT ECO Declaration; EPEAT® Silver Australia; EPEAT® Silver Canada; EPEAT® Silver US
Blue Angel compliant	No, please refer to the ECI (Ecolabel Comparison Information) document
Faxing	No
Display area (imperial)	2.0 x 1.3 inch
Display area (metric)	51.6(W) X 30.1(H) mm
Display	4-line back lit LCD
Minimum dimensions (W x D x H)	421 x 427 x 288 mm
Minimum dimensions (W x D x H)	16.6 x 16.8 x 11.3 in
Weight	~16.33 kg
Weight	~36 lb

Power consumption	580 watts (active printing), 17 watts (ready), 0.7 watts (sleep), 0.7watts (HP auto-off/auto-on), 0.07 watts (auto-off/manual-on), 0.07 watts (off) ^[5] <i>([5] Values based on 115V test results based on Energy Star test method.)</i>
Power supply type	Internal (built-in) Power Supply
What's in the box	HP Color LaserJet Pro 4201dn; 4 preinstalled introductory HP LaserJet Toner Cartridges (Black: ~1,200 pages; Cyan, Magenta, Yellow: ~1,000 pages); In-box documentation (Reference guide; Setup Card; Regulatory flyer); HP printer software is available at www.hp.com/support ; Power cord. ^[1]
Manufacturer Warranty	One-year Bench/Depot Repair warranty. Warranty and support options vary by product, country and local legal requirements. Contact your Contractual Vendor or go to hp.com/support to learn about HP award winning service and support options in your region. (wty code 4E; wty ID A033)

Top Recommended Displays, Accessories and Services

Imaging and Printing Commercial Care Pack Services

HP 3 year Next Business Day Advanced Exchange Service for Color LaserJet Pro 420x	U51YDE
HP Installation Service with network configuration for Personal Scanner and Printer (1 unit)	U9JT1E

Imaging and Printing Hardware Support Onsite Svc

HP 3 year Next Business Day Onsite Service for Color LaserJet Pro 420x	U51Y5E
--	--------

Messaging Footnotes

[3] HP Web Jetadmin is available for download at no additional charge at hp.com/go/webjetadmin.

[14] Standard print mode for HP Color LaserJet Pro series with HP TerraJet technology compared to predecessors. See hp.com/TerraJetcolors.

Technical Specifications Footnotes

[1] For yield information on the cartridge(s) included with your printer, see <http://www.hp.com/go/toneryield>. Yield values measured in accordance with ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors.

[2] Declared yields based on ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see <http://www.hp.com/go/toneryield>

[5] Values based on 115V test results based on Energy Star test method.

Learn more at

hp.com

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

