



# Poly Blackwire 3325 3.5mm Top (85R08AA)

## Overview

### Style, comfort and audio quality

Built for style with a sleek design that focuses on comfort and reliability. Poly signature audio quality so you know you will sound great. And intuitive and simple features so every user can connect to their preferred device simply and easily.

### Connect quickly and easily

The Blackwire 3300 Series is completely plug-n-play with USB devices, so users can take calls in the office or on the go. Its robust design delivers reliability you can count on. This is the hassle-free headset you've been looking for.

### Look good, feel good, sound amazing

Boost your on-the-call confidence with professional-quality audio and a customized fit with a headset that can connect to your devices quickly and easily and is ready to go with you wherever you go.

## Features

### High-quality audio

Makes collaboration easy with Poly signature audio quality and reliability.

### Wearing style

Hi-fi stereo wearing style for those who want a richer, more immersive experience.

### Headset flexibility

With professional voice quality and a customized fit, this fully adjustable headset has 180-degree pivoting speakers and a flexible microphone boom.

### Long-lasting comfort

Supports long-wearing comfort with a plush, padded headband and pillow soft ear cushions.

### Connectivity options

Enhanced connectivity for your devices: USB Type-C® cord with tethered USB-A adapter for PC and 3.5 mm for mobile or tablet connectivity.

### Optimized for communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.

## Specifications

<b>Audio</b>	Noise and echo reduction; Dynamic EQ optimized
<b>Minimum dimensions (W x D x H)</b>	15.5 x 3.2 x 17.8 cm
<b>Minimum dimensions (W x D x H)</b>	6.1 x 1.25 x 7.1 in
<b>Weight</b>	96 g
<b>Weight</b>	0.21 lb
<b>Package dimensions (W x D x H)</b>	190 x 210 x 55 mm
<b>Package weight</b>	300 g
<b>Special features</b>	UC certified
<b>Minimum System Requirements</b>	3.5 mm audio
<b>Manufacturer Warranty</b>	Poly standard two-year limited warranty
<b>What's in the box</b>	Headset (top only)

## Additional specifications

<b>Acoustic protection technology</b>	SoundGuard <sup>[1]</sup>
<b>Boom mic length (ft)</b>	0.44 ft
<b>Boom mic length (mm)</b>	135 mm
<b>Boom mic rotation</b>	280°
<b>Cable length</b>	66.5 cm
<b>Cable length (imperial)</b>	3.85 ft
<b>Cartons per layer</b>	10
<b>Cartons per pallet</b>	50
<b>Color</b>	Black
<b>Compatible Operating Systems</b>	Windows 10; macOS
<b>Connection type</b>	3.5 mm audio
<b>Country of origin</b>	Made in China or Mexico
<b>ECCN</b>	EAR99
<b>Ear cushions</b>	Artificial leather (surface material)
<b>HTS code</b>	8518302000
<b>Headphone type</b>	On-ear (stereo)
<b>Impedance</b>	32 ohm
<b>Management Software</b>	Plantronics Hub (desktop)
<b>Microphone bandwidth</b>	100 Hz to 10 kHz
<b>Microphone type</b>	Omnidirectional
<b>Multiple order quantity</b>	10
<b>Nominal sound pressure level</b>	118 dB SPL
<b>Package dimensions (W x D x H)</b>	7.48 x 8.26 x 2.16 in
<b>Package weight</b>	0.66 lb
<b>Pallet (layers)</b>	5
<b>Pallet dimensions</b>	40 x 48 x 58.66 in
<b>Pallet dimensions (W x D x H)</b>	101.6 x 121.9 x 149 cm
<b>Pallet weight</b>	787.05 lb
<b>Pallet weight</b>	357 kg
<b>Products per pallet</b>	500
<b>Products per pallet layer</b>	100
<b>Sensitivity (microphone)</b>	-38 +/-3 dB
<b>Sensitivity (speaker)</b>	116 dB

<b>Signal-to-noise ratio</b>	>118 dB
<b>Speaker bandwidth</b>	80 Hz to 20 kHz
<b>Speaker size</b>	14.2 mm
<b>UNSPSC code</b>	43191638

---

*[1] Protects against Acoustic Shock by limiting sounds to below 118 dBA.*

---

## Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Oct 15, 2024 7:39 AM UTC+0000