



Planar URL136-T

All-in-One LED Display

The Planar® UltraRes™ L Series URL136-T is an all-in-one, 136", Full HD resolution fine pixel pitch LED display. It features best-in-class on-board processing as well as audio, power, native multi-point touch and five video inputs to support up to four sources viewed simultaneously. It has a narrow bezel that facilitates 10-point touch for interactive environments such as meeting rooms and classrooms. Planar UltraRes L Series can be quickly assembled with only two people and is conveniently powered using a single 110v cable.



SPECIFICATION	DETAIL
Planar Model	URL136-T
Planar Part Number	998-3398-00
Display Diagonal	136in
Display Active Area	118.1" x 66.4" (3000mm x 1688mm)
Display Resolution	Full HD (1920 x 1080)
Aspect Ratio	16:9
Pixel Pitch	1.5625 mm
Pixel Density	409,479/m ² 38,042/ft ²
Contrast Ratio	5000:1
Brightness	350 nits (max)
Response Time (typ)	<1 ms
Frame Rate	60Hz
Color Gamut	90% of P3
HDR (High Dynamic Range)	HDR10
Color Temperature,	3,000 - 12,000; 6500, 9300, 12000 presets

Adjustable (k)	
Viewing Angle (typ)	160°
External Connections	DisplayPort 1.2 in x 1, DisplayPort out, HDMI® 2.0 x 2 (HDCP 2.2), HDMI 1.4 x 2, USB-B (for touch controller)
Display Control	IR, RS-232, LAN, HDMI-CEC, Keypad, Web Browser Interface
Multi-Source Views	PiP, Dual, Triple, Quad
Modes	4x 1920x1080 @ 24/25/30/50/60Hz; 480p, 576p, 720p @ 50/60 Hz; 1080p @ 24/25/30/50/60Hz; 1080i @ 50/60 Hz
Audio Input	PC Line In
Audio Output	PC Line Out, S/PDIF
Speakers	10W x 2 built-in
Mounting	Wall mount included. External device mounting: 75 x 75mm. Optional rolling floor stand available.
Fanless	Yes
Power Consumption, Maximum (watts)	1500W (standby: <0.5W)
Line Voltage	120-240V; 50/60Hz
Service Access	Front, Rear
Environment	Indoor
LED Type	2in1 package w/lens
LED Refresh Rate	>3840
LED Lifetime	100K hours Lifetime (Half brightness)
Display Dimensions	119.4" x 70.6" x TBD" (3032.0mm x 1794.0mm x TBDmm)
Bezel Width	0.63" (16.0mm) Left, Right and Top; 3.54" (90.0mm) Bottom
Display Edge to Active Area	0.6" (16.0mm) left and right, 0.6" (16.0mm) top, 3.5" (90.0mm) bottom
Installed Depth (from Wall)	3.5" (87.9mm)
Dimensions including Wall Mount	119.4" x 70.6" x 3.5" (3032.0mm x 1794.0mm x 87.9mm)
Dimensions including Optional Stand	119.4" x 94.6" x 30.7" (3032.0mm x 2404mm x 780mm) or 119.4" x 98.6" x 30.7" (3032.0mm x 2504mm x 780mm)

Display Weight	134kg 294.5lbs
Display Weight with Wall Mount	146.6kg 322.5lbs
Display Weight with Optional Stand	204.3kg 449.4lbs
Operating Temperature	0° to 40° C 32° to 104° F
Operating Humidity	10-80%
Storage Temperature	-20° to 85° C -4° to 185° F
Storage Humidity	10-85%
Touch Technology	IR touch: 10 points
OS Compatibility	Windows 10, 11, Mac OSX and Linux
Enclosure	Metal
Features	MediaPlex Plus Processing, Scheduling, Presets
Solution Includes	URL136-T display, US and EU power cords, HDMI cable, USB A to B cable, IR cable, remote control, vacuum removal tool and charger, gloves, and Quick Start Guide
Spare Modules	Does not include spare modules. Recommend purchasing 5 modules for each URL136-T purchased.
Approvals	FCC Class A, cTUVus, CE, RoHS
Recommended Usage	Up to 24x7 operation
Warranty	5 years
Security	No WiFi, no Android O/S, signed and encrypted firmware
UPC	8 10069 81105 5
HDMI®	Planar utilizes HDMI® standards in this product. The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI Trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 12/23/2023

© Copyright 2023 Planar Systems, Inc. All rights reserved