



XPG VENTO 120 ARGB

XPG VENTO 120 ARGB Fan offers both functional and aesthetic cooling purpose, accessorizes PC desktop with lighting effects, capable of syncing most major motherboard ARGB softwares.



RIFLE BEARING

The XPG VENTO 120 ARGB is designed with Rifle Bearing, allowing the fans to perform quietly and smoothly.



HIGH PERFORMANCE COOLING FAN

Equipped with 9 LEDs, capable of light-syncing with most major motherboard brands, making it an ideal modding fan accessory.

SPECIFICATIONS

Dimensions	120 x 120 x 25mm
Bearing Type	Rifle Bearing
Connector	3-Pin
Fan Speed (RPM)	1200 RPM \pm 10%
Fan Max Airflow	45.3 CFM \pm 10%
Fan Max Static Pressure	0.68mm H ₂ O \pm 10%
Fan Noise Level	21 dBA(avg.)
Fan Rated Voltage	DC 12V
Fan Starting Voltage	DC 5V
Fan Operating Voltage	DC 5V ~ 12.6V
Fan Rated Current	0.16A (Max)
Fan Protection	Auto-Restart
Power Dissipation	1.92W
MTTF	At 40°C 60,000 Hours
Weight	Product : 117g (4.1oz) with Package : 149g (5.3oz)
Warranty	2 Years

* Data may vary due to differences in testing equipment and environment, with \pm 10% tolerance.

ORDERING INFORMATION

Model Name	VENTO120ARGB-WHCWW
Product Number	75261280
Ean & Jancode	4711085943255
Upc Code	842243030044



Model Name	VENTO 120 ARGB-BKCWW
Product Number	75260103
Ean & Jancode	4710273775722
Upc Code	842243020601

