



Monoprice™

## Commercial Series Push-to-Pop-Out TV Video Wall Mount for 50in to 55in LED Screens, Max Weight 154lbs, VESA Patterns Up to 800x400


Quick Access and Precise Panel Alignment in a Heavy-Duty Mount for Video Wall Displays

### Optimize Video Wall Installations with the Monoprice™ Push-to-Pop-Out TV Video Wall Mount

The Monoprice™ Commercial Series Push-to-Pop-Out TV Video Wall Mount is a professional-grade solution designed to simplify multi-screen installations and maintenance. Its multi-axis, pop-out design allows displays to extend up to 10.4 inches from the wall, providing easy access to cables, controls, and behind-screen components. Keyed connection slots and alignment pins ensure precise, consistent positioning across video wall arrays of any size, while micro-adjustable tilt, rotation, swivel, and lateral shift functions make screen alignment effortless.

Engineered with durable steel and reinforced plastic, this mount supports 50"–55" displays weighing up to 154lbs (70kg) and is compatible with VESA patterns ranging from 200x200 to 800x400. Integrated supporting arms provide additional tilt for enhanced cable access during installation or servicing. Whether you're mounting to brick, concrete, or wood studs, this mount delivers strong, secure support—ideal for digital signage, command centers, and commercial AV installations. RoHS-compliant and built to last, it's the perfect choice for creating clean, professional, and flexible video wall layouts.

- Pop-out extension up to 10.4 inches with integrated supporting arms for easy access to cables, controls, and behind-display components
- Supports 50"–55" displays with a maximum weight capacity of 154 pounds (70 kilograms)
- VESA-compatible with mounting patterns ranging from 200x200 to 800x400
- Heavy-duty construction using steel and reinforced plastic ensures long-term durability and strength
- Micro-adjustable tilt (+4°/-2°), rotation (±3°), swivel, and lateral shift provide precise screen alignment across video wall arrays
- Keyed interlocking slots and alignment pins help simulate a seamless panel layout with consistent positioning
- Compatible with brick, concrete, and wood stud wall types for flexible installation options
- RoHS-compliant for safety and environmental responsibility in commercial AV setups




## POP-OUT ACCESS

The push-to-pop design makes it simple to access the back of any display in the array. A light push pops the mount out up to 10.4 inches, and built-in supporting arms provide even more tilt for quick access to wiring, controls, or hidden components.



## SEAMLESS ALIGNMENT WITH KEYED MOUNTING

Interlocking alignment pins and keyed slots ensure precise positioning across multi-display arrays, helping simulate a seamless video wall layout—ideal for 2x2, 3x3, or larger configurations.



## MICRO-ADJUSTABLE TILT AND ROTATION

Fine-tune your video wall with micro-adjustable tilt (+4°/-2°), rotation (±3°), lateral shift, and swivel, ensuring perfect alignment of all display panels with minimal effort.

## Full Specs

P/N	39660
Mount Type	Fixed Push-to-Pop-Out
Minimum Display Size	50"
Maximum Display Size	55"
Maximum Weight Capacity	154 lbs (70 kg)
Minimum VESA	200x200
Maximum VESA	800x400
Tilt Range	+4°/-2°
Rotation Range	±3°
Minimum Extension	3.3" (84 mm)
Maximum Extension	10.4" (265 mm)
Construction	Steel and Plastic
Color	Black
Stud Type	Dual
Wall Type	Brick, Concrete, Wood Stud, etc.
Display Type	Flat Back
Wall Plate Dimensions	48.4" x 19.1" (1230 x 485 mm)
Front Plate Dimensions	48.4" x 17.6" (1230 x 447 mm)