




## ZX10 FULLY RUGGED TABLET

- Qualcomm® Snapdragon™ 660, Octa-core Processor
- 10.1" LumiBond® display with Getac sunlight readable technology and glove-enabled capacitive touchscreen
- Dual hot-swappable batteries for uninterrupted operation
- 6ft drop, MIL-STD-810H and IP66 certified
- Optional 1D/2D imager barcode reader



# ZX10 FULLY RUGGED TABLET

## SPECIFICATIONS

<b>Operating System</b>	Android™ 11.0
<b>Mobile Computing Platform</b>	Qualcomm® Snapdragon™ 660, Octa-core 1.95GHz Max. 2.2GHz
<b>VGA Controller</b>	Qualcomm® Adreno™ 512 GPU
<b>Display</b>	10.1" TFT LCD WUXGA (1920 x 1200) Protection film 800 nits LumiBond® display with Getac sunlight readable technology Capacitive multi-touch screen
<b>Storage &amp; Memory</b>	4GB LPDDR4, 64GB eMMC Optional: 6GB LPDDR4, 128GB eMMC
<b>Device Button</b>	Power button 4 tablet programmable buttons
<b>Pointing Device</b>	Touchscreen - Capacitive multi-touch screen - Optional: Dual mode touchscreen (multi-touch)
<b>Expansion Slot</b>	Optional: 1D/2D imager barcode reader Optional: Smart card reader Optional: HF RFID/NFC combo reader <sup>i</sup>
<b>I/O Interface</b>	8M pixels webcam x 1 16M pixels auto focus rear camera x 1 Audio in/out combo x 1 DC in Jack x 1 USB 3.2 Gen 1 Type-C w/ DP & PD x 1 USB 2.0 (Host) x 1 MicroSD x 1 Docking connector x 1 Optional: RF antenna pass-through for GPS, WLAN and WWAN

# ZX10 FULLY RUGGED TABLET

<b>Communication Interface</b>	Wi-Fi 802.11 a/b/g/n/ac Bluetooth (v5.0) <sup>ii</sup> Dual Micro SIM Dedicated GPS Optional: 4G LTE mobile broadband
<b>Pre-installed software</b>	Getac File Browser Getac Camera Getac Input Method Getac settings and Google applications (Search, Chrome, Gmail, Maps, YouTube, Play, Drive, Play music, Play movies, Duo and photos)
<b>Security Feature</b>	Kensington lock Optional: HF RFID/NFC combo reader <sup>i</sup> Optional: Smart card reader
<b>Power</b>	AC adapter (65W, 100-240VAC, 50/60Hz) Li-Ion smart battery(3.84V, typical 4990mAh; min. 4870mAh) x 2 LifeSupport™ battery swappable technology Optional: High capacity battery (3.84V, typical 9980mAh; min. 9470mAh) x 2
<b>Dimension (W x D x H) &amp; Weigh</b>	275 x 192 x 17.9mm (10.8" x 7.56" x 0.7") 1.04kg (2.29lbs) <sup>iii</sup>
<b>Rugged Feature</b>	MIL-STD-810H certified IP66 certified Vibration & 6 feet (1.8m) drop resistant Optional: ANSI/UL 121201, CSA C22.2 NO. 213 (Class I, Division 2, Groups A, B, C, D)
<b>Environmental Specification</b>	Temperature <sup>iv</sup> : - Operating: -29°C to 63°C / -20°F to 145°F - Storage: -51°C to 71°C / -60°F to 160°F Humidity: - 95% RH, non-condensing

# ZX10 FULLY RUGGED TABLET

## Accessories

Battery (3.84V, typical 4990mAh; min. 4870mAh)  
AC adapter (65W, 100-240VAC, 50/60Hz)  
Capacitive stylus with tether

### Optional:

Carry bag  
High capacity battery (3.84V, typical 9980mAh; min. 9470mAh)  
Multi-Bay charger (Dual-Bay)  
Multi-Bay charger (Eight-Bay)  
100W Type-C AC adapter  
Office dock AC adapter (65W, 100-240VAC)  
DC-DC vehicle adapter (120W, 22-32VDC)  
Protection film  
Hand strap  
Shoulder strap (2-point)  
Shoulder harness (4-point; handsfree)  
Hard handle  
Keyboard dock  
Office dock  
Vehicle Dock

## Bumper-toBumper warranty

Accidents can take your equipment out of service when you least expect it, especially in a rugged environment, which can cause costly equipment downtime.

That is why Getac has introduced accidental damage as standard under our Bumper-to-Bumper warranty, to help minimize your enterprise IT costs.

Bumper-to-Bumper is your hassle-free guarantee.

That means you can depend on us to have your unit back in service within days.

### Standard

3 years Bumper-to-Bumper

- I. 13.56MHz HF RFID/NFC combo reader (ISO 15693, 14443 A/B, Mifare and FeliCa™ compliant).
- II. Bluetooth performance and connectable distance may be subject to interference with the environments and performance on client devices, users may be able to reduce effects of interference by minimizing the number of active Bluetooth wireless devices that is operating in the area.
- III. Weight and dimensions vary from configurations and optional accessories; optional high-capacity batteries add approx. 7.65mm (H), 144g.
- IV. Tested by an independent third-party test lab following MIL-STD-810H.

Information provided herewith is for reference only, available specification shall be subjected to quotation by request.

# ZX10 FULLY RUGGED TABLET

	Office Dock (Pogo)
Serial Port	-
Microphone	1
Audio Output	1
DC in Jack	1
USB	USB 2.0 x 3
LAN	1
HDMI	1
RF Pass-through	-
Kensington Lock	1

## Getac USA

15495 Sand Canyon Ave. Suite 350  
Irvine, CA 92618  
Tel : 949-681-2900

GetacSales\_US@getac.com | [www.getac.com/us/](http://www.getac.com/us/)

Copyright © 2022 Getac Technology Corporation and/or any of its affiliates. All Rights Reserved.

Information provided herewith is for reference only,  
available specification shall be subjected to quotation by request.