



**5 YEAR WARRANTY**



## SAKER SERIES

The Saker Series is an electric projection screen that embodies all the virtues of quality, durability, and aesthetic value. It utilizes our Max-White® Fiberglass (FG) material which has a wide viewing angle to allow the audience to see the image from anywhere in the room. The enameled aluminum casing has a stylish arcuate profile that is best suited to the aesthetics of interior design. To make installation easy, the Saker comes fully assembled with sliding wall mounts to ensure that it will be properly centered in every installation.



### Screen Material & Design

- MaxWhite® Fiberglass (1.1 Gain) matte white fiberglass-backed material
- Wide viewing angle and uniformly diffuses light in all directions
- Active 3D, 4K Ultra HD, and HDR Ready
- Compatible with Standard throw Projectors ONLY
- Standard black masking borders and black screen backing
- Arcuate profile aluminum enamel white case with parallel grooves
- Extra top black masking border for high ceiling installations
- Plug & Play ready, no hardwire installation required
- Available in the following diagonal sizes:
  - 100", 110", 120", 135", 150" and 180" in 16:9 aspect ratio
  - 100" in 16:10 aspect ratio

### Controls & Installation

- Includes handheld Infrared (IR) and Radio Frequency (RF) remote controls, and a wall box controller for manual on-wall operation.
- User-friendly programmable vertical drop position for easy installation
- Wall box controller is detachable for a clean look
- Built-in selectable channels allow one RF remote programming to control multiple screens and prevent interference
- 12v trigger feature allows the screen's UP/DOWN operation to synchronize with the projector's power cycle
- Synchronous motor on diagonal sizes 100", 110", and 120"
- Tubular motor on diagonal sizes 135", 150", and 180"
- 5-year limited manufacturer's warranty

info@eliteproav.com



www.eliteproav.com