

# CyberPower

## CR6U61003 WALL MOUNT ENCLOSURE



### Wall mount enclosure safeguards 6U of 19-inch rack equipment

The CR6U61003 is designed for use in network closets, classrooms, and other locations. This wall mount rack houses network switches and patch panels up to 20.3 inches deep. It includes convenient top panel cable access openings, perforated front door and side panels for efficient airflow, adjustable rack angles, and square and threaded mounting holes. The CR6U61003 ships fully assembled for quick deployment and can be customized with compatible accessories. It is covered by a five-year limited warranty.

### TYPICAL APPLICATIONS

- Network Closets
- Retail Locations

### FEATURES

- Rack Type: EIA-310 Standard 19-inch Rack
- Height: 6U
- Stationary Capacity: 132 lbs
- Max. mounting depth: 20.3 in.
- Color: Black RAL 9005 Powder Coat Paint
- Mounting Hole Type: Square and Threaded
- Reversible Door: Front
- Side Panels: One per Side
- Removable Sections: Door and Side Panels
- Security: Keyed Alike Door and Side Panels
- Assembly: Fully Assembled
- Mounting Hardware: Included
- Warranty: 5-Year

### SPECIFICATIONS

#### CABLE SPECIFICATIONS

Cable Access	Top and Bottom Openings
--------------	-------------------------

#### PHYSICAL SPECIFICATIONS

Cable Access Opening Dimensions	9.8 x 2.2 in (249 x 56 mm)
Color	Black
Door Type	Hex Perforated Metal Door
Factory Default Mounting Depth	17.2 ft (436.9 mm)
Lockable Doors and Side Panels	Yes, keyed alike
Max. Mounting Depth (in)	20.3 in.
Max. Mounting Depth (mm)	516 mm

#### PHYSICAL SPECIFICATIONS - CONT.

Min. Mounting Depth (in.)	1.9 in.
Min. Mounting Depth (mm)	47 mm
Rack Angle Mounting Hole Type	Square Mounting Holes #12-24 Mounting Holes
Rack Height	6U
Removable Doors and Side Panels	Yes
Reversible Front Door	Yes
Weight Capacity - Stationary Load (kg)	60 kg
Weight Capacity - Stationary Load (lbs)	132.3 lbs.

# CR6U61003

## WALL MOUNT ENCLOSURE

### SPECIFICATIONS - CONT.

DIMENSIONS	
Physical Dimensions - Width/Height/Depth (cm)	59.94 x 32.0 x 59.94 cm
Physical Dimensions - Width/Height/Depth (mm)	599 x 320 x 599 mm
Physical Dimensions - Width/Height/Depth (in.)	23.6 x 12.6 x 23.6 in.
Weight (kg)	13.47 kg
Weight (lb)	29.70 lbs.
Country of Origin	China

ENVIRONMENTAL	
Protection Class	IP20
CERTIFICATIONS	
Environmental	RoHS Compliant
Approvals	EIA-310E, IEC-60297-1, 2, ASTM-D610, ASTM-B117
WARRANTY	
Product Warranty	5-Year Limited