



8GB DDR5 PC5-38400 - 4800Mhz SO DIMM Notebook Memory Module - V7384008GBS-U

V7384008GBS-U

SKU: HH3898

V7 DDR5 has been designed to meet increasing needs for high performance and power efficient memory in a wide range of applications from client systems to high performance server platforms. DDR5 is designed to support scaling memory performance without degrading channel efficiency at higher speeds and has double the burst length and 32banks allowing for increased module capacity. Decision feedback equalization enables IO speed scalability for higher bandwidth and improved performance. DDR5 supports double the bandwidth compared to DDR4 and starts at speeds of 4800Mhz which is a considerable increase on the highest DDR4 speeds.

- JEDEC industry standard specification
- Improve System Performance
- Guaranteed Compatibility
- TAA Compliant
- Easy to install

General

Sku: HH3898
Model: V7384008GBS-U
EAN: 5050914227685
Warranty: Lifetime
Compliance: CE, RoHS
Country Of Origin: Taiwan
Package Type: Blister
SAP: 5845378

Technical

Rank: Single
Buffering: Non-ECC, Unbuffered DIMM
Platform: Notebook
RAM Type: DDR5
Clock Rate: 4800 Mhz
Capacity: 8 GB
Memory Form Factor: 262PIN SO-DIMM
Memory Module: PC5-38400 - 4800Mhz CL40

Package Dimensions

Package Dimensions (L/W/H): 170 x 55 x 15 mm
Package Weight: 30g

Product Dimensions

Product Dim (L/W/H): 170 x 55 x 15 mm
Product Weight: 30g