

2-Bay, 3-Bay, & 5-Bay Credenzas

Standard depth, single and dual display cabinets

Avteq credenzas are made to order and perfect for conference rooms, huddle spaces and training centers. Credenzas are fully customizable and designed specifically for commercial AV use. The standard configuration is 22.95 inches deep and includes two, three, or five bays plus storage that supports all your audio visual equipment. The integrated VESA mounting system eliminates wall-mounted displays and supports a single display up to 98", dual displays up to 82", or dual extra large displays up to 86". The back of the credenza is open for maximum ventilation. Optional back covers are available.

Choose from a wide selection of laminates or custom veneers from WilsonArt or Formica. Avteq can also help match existing furniture.

Avteq credenzas come fully assembled to simplify installation which makes these cabinets the perfect choice for standard room solutions across multiple rooms and locations.

Credenza uprights are available as an accessory to bring additional height for larger displays.

FEATURES


- Standard 2-bay, 3-bay or 5-bay configurations
- Custom 4-bay and 6-bay cabinets available
- Universal VESA mount for single or dual displays
- 10RU sliding, rotating rack
- Open back for ventilation
- 9-port rack-mounted surge protector
- Round door pulls
- Leveling feet
- 100% steel frame
- Optional back bay covers
- Optional modesty panel to cover display uprights
- Optional camera shelves
- TAA compliant



3-Bay Credenza



2-Bay Credenza



5-Bay Credenza

CUSTOM SIZES

4-bay and 6-bay configurations are available made-to-order. Contact your Avteq sales rep for pricing, custom sizes and options.

4-Bay Credenza




6-Bay Credenza




DIMENSIONS

2-Bay Credenza




3-Bay Credenza



DIMENSIONS CONT.

5-Bay Credenza



SPECIFICATIONS	
Part Number & Display Sizes: (Single) (Dual) (Dual Xtra Large)	2-Bay: (CRED2L-S, CRED2V-S) (CRED2L-D, CRED2V-D) 3-Bay: (CRED3L-S, CRED3V-S) (CRED3L-D, CRED3V-D) (CRED3L-DX, CRED3V-DX) 5-Bay: (CRED5L-S, CRED5V-S) (CRED5L-D, CRED5V-D) (CRED5L-DX, CRED5V-DX)
Finishes: L = Laminate V = Veneer	
Display Sizes	Single: (45-98 inches) Dual: (45-82 inches) Dual Xtra Large: 86 inch
Dimensions (HxWxD)	
2-Bay	52.6 x 30 x 25.4 Inches (1336 x 762 x 645 mm)
3-Bay	79 x 30 x 25.4 Inches (2007 x 762 x 645 mm)
5-Bay	132 x 30 x 25.4 Inches (3353 x 762 x 645 mm)
Cabinet	22.5 x 24 x 22 Inches (572 x 610 x 559 mm)
Rack (D)	17 Inches
Rack Space	10 RU
UM-1 Single Display (min-max width)	Min: 27.1 Inches (688 mm) Max: 42.2 Inches (1072 mm)
UM-2 Dual Display (min-max width)	Min: 57 Inches (1448 mm) Max: 93.7 Inches (2380 mm)

* Contact your AVTEQ representative for applications larger than 90".



FINISHES

AVTEQ uses quality laminate and veneer finishes from the WilsonArt catalog. To view the entire catalog, visit WilsonArt.com.



DESIGNER WHITE
D354



WHITE CYPRESS
7976



ASIAN SAND
7952



BEIGEWOOD
7850



TUSCAN LIMESTONE
1861



TRUSS MAPLE
7972



NEW AGE OAK
7938



ALOE
7962



TUSCAN WALNUT
7921



NEPAL TEAK
7209



ASIAN SUN
7951



WILD CHERRY
7054



BILTMORE CHERRY
7924



ZANZIBAR
7957



XANADU
7945



5TH AVE. ELM
7966



BOARDWALK OAK
7983



SKYLINE WALNUT
7964



STERLING ASH
7995



EBONY RECON
7997



MADAGASCAR
7944

ACCESSORIES



Poly Studio X Mounts

POLY-X-24 | POLY-X-32
POLY-X-42 | POLY-X-48



Cisco Room Kit Mounts

CRK-ABV-24 | CRK-ABV-32 |
CRK-ABV-42 | CRK-ABV-48
CRK-BLW-24 | CRK-BLW-32 |
CRK-BLW-42 | CRK-BLW-48



Logitech Rally Bar Mount

LRC-MOUNT-24 | LRC-MOUNT-32
LRC-MOUNT-42 | LRC-MOUNT-48



Neat Bar and Bar Pro Mount

NEAT-BRK-24 | NEAT-BRK-32
NEAT-BRK-42 | NEAT-BRK-48



Rotating Rack

SR-12




Extended Uprights

CRED-EXT-UPRIGHTS



Back Bay Covers

CRED2-BC | CRED3-BC



Credenza Cover Panel

CRED2-PP-L | CRED3-PP-L



Call 800.285.8315 or visit AVTEQ.net