



LATITUDE

3330

Collaboration made real with essential productivity and intelligent connectivity.



3330



Collaboration made real with essential productivity and intelligent connectivity.

Built for any business and any budget, and perfectly suited for the mobile professional who works from anywhere. Now available as a laptop or 2-in-1 in a new light design, with Latitude intelligence.

Ideal for professionals in any business, Higher Education students, staff and educators, and K-12 staff and educators driven to produce results and strive for efficiency. They need enterprise-level security and productivity to work anywhere.

The world's lightest new essential 13-inch business laptop¹
Starts at 2.65lbs/1.20kg.

Small, light design
World's smallest and lightest essential business 2-in-1³.

New versatility
2-in-1 option features Active Touch Panel with pen support.

Sustainability
EPEAT Gold, TCO-certified, waterborne paint, recycled plastic, and sustainable packaging.

ALL NEW 2-in-1 option
Offered for the first time ever on a 13-inch 3000 Series device.

Premium feel and look
Large keys with edge-to-edge backlit** keyboard and mylar touchpad with glass-like feel

Increased connectivity
Now with PowerShare added to one of the USB 3.2 ports.

ExpressConnect
Utilize 2 or more networks at once with ExpressConnect, the world's 1st simultaneous multi-network connection for faster data and video downloads.

ExpressResponse
Launch applications faster and improve overall app performance.

Intelligent Audio with Neural Noise Cancellation
Collaborate confidently with AI-based background noise elimination.

New optional FHD IR Camera on 2-in-1
Look your best on every video call on the only essential business 2-in-1 to offer FHD camera².

Added privacy control
New mechanical privacy camera shutter.

WiFi 6 and 6E*
For faster wireless performance, expanded capacity, and more efficient bandwidth.

Powerful performance
11th Generation Intel® Core™ Processors up to i7 4-Core.

*Wi-Fi 6E coming later in 2022.


** Backlit keyboard is optional.

3330

Sustainability on Dell Latitude

Leading the industry in sustainable practices in our products, packaging and supply chain.

OUR MOST SUSTAINABLE LATITUDE PORTFOLIO: WORKING TOWARD OUR GOALS, SO YOU CAN MEET YOURS.



Packaging Innovation

100%

Recycled or renewable packaging across all new Latitude PCs. Easy-to-open and uses less carbon to ship. It's the 1st design that already meets our 2030 moonshot goals.

Design

1st

Dell PCs were the 1st to use reclaimed carbon fiber and tree-based bioplastic⁴.

Recycling e-waste



Securely, responsibly retire your IT equipment with Dell regardless of brand, in support of a circular economy. Learn more at Dell.com/Recycle.

LATITUDE HAS

90+

EPEAT registered products⁵



100%

EPEAT Gold in 2021 products



38

TCO 8 certified configurations



8.0

ENERGY STAR[®] throughout the portfolio




3330

Dell Optimizer

We make it intelligent. You make it yours.

Dell Optimizer revolutionizes the way you work by fueling the world's most intelligent PCs⁶. It is the only business, AI-based optimization software that learns and responds to the way you work and is designed to automatically improve application performance, battery run-time, audio settings, and privacy—all in the background while you're working.

Accomplish anything with built-in intelligence that learns and adapts.



Extended power

ExpressCharge analyzes your power usage habits to improve PC battery utilization, extend run time, and charge your system faster.



Enhanced audio

Intelligent Audio delivers audio and mic enhancements and reduces background noise using Neural noise cancellation.



Simplified manageability

Elevate work experience with an easy-to-manage application that provides a seamless experience for both end-users and IT decision-makers.



Unmatched connectivity


ExpressConnect⁷ provides the world's first simultaneous multi-network connection⁸ that joins the best network⁹ available.



Improved performance

ExpressResponse¹⁰ analyzes how you use your preferred apps¹¹ to boost performance.





RECOMMENDED ACCESSORIES

AT THE DESK



Dell 24 Monitor - P2422H

Stay productive no matter where you work with this sleek 23.5" FHD monitor with ComfortView Plus.



Dell Mobile Wireless Mouse - MS3320W

Pair and connect to almost any PC via 2.4GHz wireless or Bluetooth 5.0 and enjoy a long 36 months¹⁵ battery life.



Dell Pro Stereo Headset - WH3022

Experience exceptional audio clarity with this Teams-certified wired headset that allows you to wear the microphone on either side for a customized fit.



Dell Pro Wireless Keyboard and Mouse - KM5221W

Enhance your everyday productivity with a quiet full-size keyboard and mouse combo that offers programmable shortcuts and 36 months¹⁵ battery life.

ON THE GO



Dell Dock - WD19S

Boost your PC's power with this powerful and modular USB-C dock with a future-ready design.



Dell USB-C Mobile Adapter - DA310

Compact and portable 7-in-1 USB-C mobile adapter provides superb video, data connectivity and up to 90W power pass-through to your PC.



Dell Notebook Power Bank Plus - PW7018LC

With fast high-power delivery of up to 65W, this power bank can charge the widest range of USB-C laptops, and mobile devices.



Dell Pro Slim Briefcase 15 - PO1520CS

Keep your laptop, tablet and other essentials securely protected within the eco-friendly Dell Pro Slim Briefcase 15, a slim-fit briefcase designed for work and beyond.



LATITUDE 3330

FEATURE TECHNICAL SPECIFICATION

MODEL NUMBER	3330
PROCESSOR OPTIONS¹⁴	11th Gen Intel® Core™ processors up to i7, 4-core
OPERATING SYSTEM¹⁴	Windows 11 Home Windows 11 Pro Windows 10 Pro (Windows 11 Pro license included) Ubuntu® 20.04 LTS
MEMORY OPTIONS^{14,15,16}	Up to 16GB LPDDR4x SDRAM 4266MHz (on board)
CHIPSET¹⁴	Integrated with the processor
INTEL RESPONSIVENESS TECHNOLOGIES^{14,18}	Intel® Rapid Storage Technology
GRAPHICS^{14,23}	Intel® UHD Graphics (Integrated) - i3 Intel® Iris® X® Graphics (Integrated) - i5/i7
DISPLAY¹⁴	Laptop: 13.3" 16:9, FHD (1920 x 1080), WVA, non-touch, 250 nits, NTSC 45%, Anti-Glare 2-in-1: 13.3" 16:9, FHD (1920 x 1080), WVA, touch, 300 nits, NTSC 72%, Anti-reflective, Anti-Glare, Corning® Gorilla Glass®, Active Pen Support
STORAGE^{14,16}	Up to 1TB, M.2 2230 PCIe NVMe, SSD, Class 35 Up to 1TB, M.2 2280 PCIe NVMe, SSD, Class 40
SECURITY¹⁴	TPM 2.0 FIPS-140-2 Certified / TCG Certified Optional Windows Hello compliant fingerprint reader in power button Optional Security Hardware Authentication Bundles Optional Face IR camera (Windows Hello compliant) Camera Shutter Dell Client Command Suite: On-Prem Dell Client Command Suite: Cloud Dell Optimizer Dell SafeBIOS Dell SafeID Vmware Carbon Black Endpoint Standard Vmware Carbon Black Endpoint Advanced Vmware Carbon Black Endpoint Enterprise Absolute Visibility Absolute Control Absolute Resilience Dell Encryption Personal Dell Encryption Enterprise Netskope Cloud Access Security Broker (CASB) Netskope Secure Web Gateway Netskope Private Access
DOCKING¹⁴ <i>(SOLD SEPARATELY)</i>	Dell USB-C Dock - WD19S Dell Dual Charge Dock - HD22Q (later in 2022) Dell Universal Dock - UD22 (later in 2022) Dell Universal Dock - D6000/ D6000S Dell Thunderbolt™ Dock - WD22TB4 Dell Thunderbolt™ Dock- WD19TBS Dell Performance Dock - WD19DCS
MULTIMEDIA¹⁴	FHD IR Camera: Experience: Temporal Noise Reduction (TNR) + Camera Shutter HD RGB Camera: Experience: Temporal Noise Reduction (TNR) + Camera Shutter (2) Speakers, Waves MaxxAudio Pro (2) Noise Cancelling Microphones Intelligent Audio with Neural Noise Cancellation Universal Audio Jack
BATTERY OPTIONS¹⁴	3-Cell, 41Whr Polymer, ExpressCharge 1.0™ 4-Cell, 54Whr Polymer, ExpressCharge 1.0™
POWER OPTIONS¹⁴	65W adapter, Type-C 65W adapter, 4.5mm, barrel
CONNECTIVITY OPTIONS^{14,24}	Microsoft Modern Standby compliant Wireless LAN Options¹⁹: Realtek Wi-Fi 5 RTL 8822CE 2x2 + Bluetooth ²⁶ Intel® Wi-Fi 6 (6GHz) AX201 2x2 + Bluetooth ²⁶ USB Type-C 3.2 Gen2x2 USB 3.2 Gen 1

FEATURE TECHNICAL SPECIFICATION

PORTS, SLOTS & CHASSIS¹⁴	USB 3.2 Gen 1 with PowerShare HDMI 1.4 Optional Touch Fingerprint Reader in Power Button Universal Audio jack Wedge Shaped Lock Slot
DIMENSIONS & WEIGHT^{14,25}	Width: 305.96mm / 12.04" Height: 16.42mm / .64" (2-in-1) Height: 15.68mm / .61" (laptop) Depth: 209.78mm / 8.25" Screen to Body: 82.96 % (laptop) Screen to Body: 82.73 % (2-in-1) Laptop Starting weight: 2.6lbs / 1.20kg 2-in-1 Starting weight: 2.8lbs / 1.3kg
REGULATORY AND ENVIRONMENTAL COMPLIANCE¹⁴	Regulatory Model: P158G (Laptop) P159G (2-in-1) Regulatory Type: P158G002 (Laptop) P159G002 (2-in-1) ENERGY STAR EPEAT Registered. For specific country participation and rating, please see www.epeat.net TCO compliant configurations available Halogen-Free/Arsenic-Free BFR/PVC free (not including PSU) ²⁰
INPUT¹⁴ <i>(SOLD SEPARATELY)</i>	10-Finger Touch Display Glass Microsoft® Precision Clickpad Spill Resistant Non-Backlit Keyboard Spill Resistant Backlit Keyboard Dell Active Pen - Model PN5122W (optional, sold separately, 2-in-1 only) Dell Premier Rechargeable Active Pen - Model PN7522W (optional, sold separately, 2-in-1 only)
SENSORS	Gyroscope, eCompass/Magnetometer, Accelerometer, Adaptive Thermal Performance (via Gyroscope/Accelerometer), Wake on with lid open
SYSTEMS MANAGEMENT¹⁴	Dell Client Command Suite available (dell.com/command), Factory Installed Dell Client Command Update, Dell Command Power Manager Dell Optimizer
WARRANTY AND SERVICE¹⁴	Limited Hardware Warranty ¹⁷ Standard 1 year Mail-in Service after Remote Diagnosis ²¹ Optional 3, 4 and 5 year hardware warranty extensions 3-5 year Dell ProSupport contracts available ²²
PERIPHERAL ECOSYSTEM¹⁴	Powerful accessories designed and tested for Latitude 3330 enable seamless productivity to work from anywhere.

- 1 Based on internal Dell analysis, January 2022.
- 2 Based on internal Dell analysis, January 2022.
- 3 Based on internal Dell analysis, January 2022.
- 4 ExpressCharge can recharge system battery from 0% up to 80% within 40 minutes. After charging has reached 80% capacity, charging speed will return to normal speed. Recommended for use with the provided Dell power adapter; not recommended with a smaller capacity power adapter. Charging time may vary +/-10% due to system tolerance. ExpressCharge Boost can recharge system battery from 0% up to 35% within 20 minutes when system is powered-on and battery temperature is between 16-45 degrees C. With ExpressCharge mode enabled, the system battery can then continue charging up to 80% within 40 minutes. After charging has reached 80% capacity, charging speed will return to normal speed. Recommended for use with the provided Dell power adapter; not recommended with a smaller capacity power adapter. Charging time may vary +/-10% due to system tolerance.
- 5 EPEAT registered where applicable. EPEAT registration varies by country. See www.epeat.net for registration status by country.
- 6 Based on internal analysis, April 2021. Dell Optimizer available in 2020 devices, not available in OptiPlex 3000 series, Latitude 3310 2-in-1 and Latitude Chromebook Enterprise. Feature availability and functionality varies by model.
- 7 ExpressConnect available with Dell Optimizer software version 2.0 and onwards. Download the latest at <https://www.dell.com/support/home>.
- 8 Disclaimer: Simultaneous multi-network connection (or Connection based teaming) is a new connectivity feature under ExpressConnect. It simultaneously sends and receives data and video traffic using two wired or wireless connections. Based on Dell internal analysis.
- 9 Best network selection based on signal strength, channel congestion, router type and others. Network suggestions based on user credentials.
- 10 ExpressResponse must be enabled in the Applications feature. DO learns how user uses the selected application(s) over several hours. Based on Dell testing using Sysmark 2018 benchmark on a Latitude system running productivity applications; and using performance evaluation benchmarks on Precision mobile workstations running ISV applications, March 2020. Improvement will vary based on product configuration, use, application and other factors
- 11 User must input preferred apps first in order for them to be analyzed.
- 12 With ExpressConnect's optimized internet bandwidth. Based on testing performed by Dell Labs in June 2020, comparing performance with ExpressConnect enabled and disabled. Actual results may vary; testing results do not guarantee performance under test conditions. Subject to service provider's broadband subscription and coverage area; speeds may vary. Additional charges will apply. Contact your service provider for details.
- 13 Based on Dell internal analysis of battery life usage model calculations, Nov. 2019. Results vary depending on usage and computing conditions.
- 14 Offering may vary by country and by configuration and Operating System.
- 15 A 64-bit operating system is required to support 4GB or more of system memory.
- 16 GB means 1 billion bytes and TB equals 1 trillion bytes; actual capacity varies with preloaded material and operating environment and will be less.
- 17 Limited Hardware Warranty: For copy of Limited Hardware Warranty, write Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see www.dell.com/warranty.
- 18 Intel Rapid Storage Technology requires a HDD, mSATA, or an SSD, as primary storage device. See OS requirements.
- 19 Wireless antenna and module available only at time of system purchase.
- 20 Dell Latitude 3330 are brominated flame retardant free (BFR-free) and polyvinyl chloride free (PVC-free); meeting the definition of BFR-/PVC-free as set forth in the INEMI Position Statement on the 'Definition of Low-Halogen Electronics (BFR-/CFR-/PVC-free)'; Plastic parts contain less than 1,000 ppm (0.1%) of bromine (if the Br source is from BFRs) and less than 1,000 ppm (0.1%) of chlorine (if the Cl source is from CFRs or PVC or PVC copolymers). All printed circuit board (PCB) and substrate laminates contain bromine/chlorine total less than 1,500 ppm (0.15%) with a maximum chlorine of 900 ppm (0.09%) and maximum bromine being 900 ppm (0.09%).
- 21 Onsite Service after Remote Diagnosis: Remote Diagnosis is determination by online/phone technician of cause of issue; may involve customer access to inside of system and multiple or extended sessions. If issue is covered by Limited Hardware Warranty (www.dell.com/warranty) and not resolved remotely, technician and/or part will be dispatched, usually within 1 business day following completion of Remote Diagnosis. Availability varies. Other conditions apply.
- 22 Dell Services: Availability and terms of Dell Services vary by region. For more information, visit www.dell.com/servicesdescriptions.
- 23 GB means 1 billion bytes and TB equals 1 trillion bytes; significant system memory may be used to support graphics, depending on system memory size and other factors.
- 24 Miracast Wireless Technology: Requires a compatible media adapter (sold separately and can be integrated into the display) and an HDMI-enabled display.
- 25 Weights vary depending on configuration and manufacturing variability.
- 26 The Bluetooth wireless card version may vary depending on the operating system that is installed on your computer.