



# Poly Rove 20 DECT Phone Handset (8F3E4AA)

## Overview

### **We've got you covered**

Keep the conversation going whenever, wherever in the office. Built for on-site employees the Poly Rove 20 wireless DECT™ IP phone solution delivers the freedom to move and the flexibility to scale as you grow.

### **Clarity meets function**

Designed for busy professionals, Poly Rove 20 handsets emphasize usability, functionality, and style. Enjoy HD voice for lifelike conversations, customizable line keys, and effortless call parking.

### **You grow, we scale**

You shouldn't have to worry about outgrowing your communication solution or feel held back by its options. Poly Rove 20 wireless DECT™ IP phone solution has the flexibility to scale with handsets, bases, and repeaters as you grow.

# Features

## Privacy is ensured

Conversations are safe and secure with DECT™ wireless security. And it doesn't stop there - maintain DECT™ encryption even when you add a base or repeater to your solution.

## Extended battery life

Enable employees on the move to communicate more effectively, respond faster to requests and alerts, and be more productive with up to 35 hours of talk time (Eco-mode) and up to 300 hours of standby time.

## Grab a Poly headset and go

Communicate hands-free with a Poly wired headset using the dedicated 3.5 mm connection. Perfect for users who feel more comfortable wearing a headset.  
[1]

## Easy-to-clean handsets

Ideal for healthcare environments, these handsets are specifically designed for easy cleaning with smooth surfaces and no gaps between buttons.

## Pro-grade features

Single-cell DECT™ handset with 4-line keys and easy call park functionality. Push-to-talk for inter-handset communication. And with the 2" TFT color LCD with backlight users will see productivity soar.

## HD audio quality

HD voice enables more natural conversations to enhance productivity. Voices stay in the forefront – background noise suppression lets people on both sides of the call focus on the person speaking, not their surroundings.

---

[1] Poly wired headset sold separately.

## Additional specifications

<b>Audio</b>	Full-duplex handsfree speakerphone with acoustic echo cancellation and background noise suppression
<b>Audio codecs</b>	G.165, 168 echo cancellation
<b>Battery life</b>	Up to 35 hours (talk time) using Eco mode; Up to 300 hours (standby time)
<b>Battery type</b>	Rechargeable Li-ion
<b>Certifications and compliances</b>	UL 62368-1
<b>Certified collaboration software</b>	Zoom
<b>Color</b>	Black
<b>Country of origin</b>	Product of China
<b>DECT frequency</b>	1880 to 1900 MHz
<b>Display features</b>	Adjustable font size selection (regular, medium, large)
<b>Display size (diagonal)</b>	5.1 cm (2")
<b>Display size (diagonal)</b>	2"
<b>Energy star certified</b>	ENERGY STAR® certified
<b>Headset and handset compatibility</b>	Compliant with ADA Section 508 Subpart B 1194.23 (all)
<b>Headset ports</b>	1 3.5 mm headset jack
<b>Management Software</b>	Polycom Device Management Service for Service Providers (PDMS-SP) Cloud Management
<b>Manufacturer Warranty</b>	Poly standard one-year limited warranty
<b>Minimum dimensions (W x D x H)</b>	55.2 x 127 x 26.3 mm
<b>Minimum dimensions (W x D x H)</b>	2.2 x 5 x 1 in
<b>Native resolution</b>	128 x 160
<b>Network protocols, supported</b>	Manual or dynamic host configuration protocol (DHCP) network setup; Time and date synchronization using SNTP
<b>Operating humidity range</b>	5 to 95%
<b>Operating temperature range</b>	14 to 131°F
<b>Operating temperature range</b>	-10 to 55°C
<b>Package dimensions (W x D x H)</b>	180 x 92.2 x 61 mm
<b>Package dimensions (W x D x H)</b>	7.1 x 3.6 x 2.4 in
<b>Package weight</b>	0.63 lb
<b>Package weight</b>	287 g
<b>Panel technology</b>	Color TFT LCD
<b>Power</b>	External universal AC adapter: 5V 1A DC

<b>Security management</b>	DECT™ security certified
<b>Storage temperature range</b>	-40 to 70°C
<b>Storage temperature range</b>	-40 to 158°F
<b>Telephony and call handling features</b>	4 line keys
<b>UNSPSC code</b>	43191606
<b>UPC number</b>	(ABA) 197497473193; (ABB) 197497473186; (ABG) 197497473179; (ABJ) 197497776973; (ABU) 197497473162; (UUF) 197497473155
<b>VoIP features</b>	Ten (10) service provider configuration profile assignments (ITSP Profile A – J)
<b>Weight</b>	0.36 lb
<b>Weight</b>	162 g
<b>What's in the box</b>	Safety information sheet; Handset; Quick start guide; AC power adapter; Charging cradle; Spare battery; Base station; Ethernet cable; Belt clip
<b>Wireless range</b>	Up to 50 m indoor
<b>Wireless range (imperial)</b>	Up to 165 ft indoor

---

## Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Nov 01, 2023 9:36 AM UTC+0000