



Poly Blackwire C3215 Monaural Headset +Carry Case (80S05AA)

Overview

Freedom to work your way

The Blackwire 3200 Series provides a quality audio experience in a headset that's built for enterprise needs. With a sleek design and flexible microphone boom for a customizable fit, what's not to love?

Poly signature audio quality

Experience the high-quality audio you expect from Poly with a headset that offers PC wideband, a noise-canceling mic, and hi-fi stereo sound options. Dynamic EQ optimizes call quality and automatically adjusts the settings for listening to multimedia.

Long-lasting comfort and portability

Relax while you talk knowing your headset is secure- lightweight metal headband offers durability plus a custom fit. Leatherette ear cushions fold flat for easy portability.

Advanced connectivity

Ideal for managing calls on your PC, mobile phone, or tablet combined with the comfort and durability of a corded headset for greater flexibility.

Features

Enhanced call quality

Dynamic EQ optimizes the quality of your voice on calls, and automatically adjusts the EQ settings when you want high-quality sound for listening to music or for multimedia playback.

Connectivity options

Select the right option for your device: USB-A or USB Type-C® for PC and 3.5 mm for mobile connectivity with select models.

Wearing style

Monaural wearing style for those who prefer to leave one ear open.

Lightweight design

A lightweight metal headband offers durability and a comfortable custom fit.

Simple call management

Use the intuitive inline controls to answer/end calls, control volume, and mute to simplify call management. Conveniently placed indicator lights provide helpful but unobtrusive user call, mute, and volume status.

Optimized for communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.^[1]

[1] Visit <https://www.poly.com/us/en/products/headsets/blackwire/blackwire-3200> for more detail.

Specifications

Dimensions (W x D x H)	155 x 32 x 178 mm
Dimensions (W x D x H)	6.1 x 1.25 x 7.1 in
Weight	87 g (with cable); 64 g (without cable)
Weight	0.19 lb (with cable); 0.14 lb (without cable)
Package dimensions (W x D x H)	185 x 56 x 207 mm
Package weight	300 g
Manufacturer Warranty	Poly standard two-year limited warranty
What's in the box	USB Type-C® cable; Headset; Travel case

Additional specifications

Acoustic protection technology	SoundGuard ^[1]
Boom mic length (ft)	0.43 ft
Boom mic length (mm)	130 mm
Boom mic rotation	270°
Button user controls	Call answer/ignore/end/hold; Redial; Mute; Volume +/-
Cable length	129.5 cm (inline module to headset); 90 cm (USB to inline module); 227 cm (total USB to headset)
Cable length (imperial)	4.25 ft (inline module to headset); 2.95 ft (USB to inline module); 7.45 ft (total USB to headset)
Cartons per layer	6
Cartons per pallet	36
Certified collaboration software	Skype for Business; Cisco Jabber; Avaya
Color	Black
Compatibility	Compatible with PCs via USB/USB Type-C®, connects to mobile devices and tablets via 3.5 mm and devices that support USB Type-C®
Compatible Operating Systems	Windows 11; Windows 10; macOS
Connection type	Wired: USB Type-C®, 3.5 mm audio
Ear cushions	Foam (surface material)
Ecolabels	TCO Certified
Headphone type	On-ear (monoaural)
Impedance	32 ohms
Management Software	Poly Lens
Microphone bandwidth	100 Hz to 10 kHz
Microphone type	Noise cancelling
Multiple order quantity	12
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in
Package weight	0.66 lb
Pallet (layers)	6
Pallet dimensions	40 x 48 x 58.66 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 149 cm
Pallet weight	404.76 lb
Pallet weight	183.6 kg
Products per pallet	432
Products per pallet layer	72

Sensitivity (microphone)	10 dB SLR
Sensitivity (speaker)	0 dB RLR
Signal-to-noise ratio	>24 dB
Speaker bandwidth	200 Hz to 6.8 kHz (speech mode); 20 Hz to 20 kHz (media mode)
Speaker size	28 mm
UNSPSC code	43191638

[1] Protects against Acoustic Shock by limiting sounds to below 118 dBA.

Services

Communication & Collaboration

★ : Recommended

Poly Support Services

3 year Poly+ Blackwire Service

PBLKWIRE312 ★

3 year Partner Poly+ Blackwire Service

PBLKWIRE362

Hybrid Work Solutions

Audio

★ : Recommended

Audio Accessories

Poly Blackwire 3200 Leatherette Ear Cushions (2 Pieces)	85S24AA
---	---------

Poly Blackwire 3310/3320 Foam Ear Cushions (2 Pieces)	85S23AA
---	---------

Poly Blackwire 3315/3325 Leatherette Ear Cushions (2 Pieces)	85S22AA
--	---------

Poly Blackwire 5000 Leatherette Ear Cushions (2 Pieces)	85S19AA
---	---------

Poly Blackwire 5200 Y Training Cable	85S08AA
--------------------------------------	---------

Poly Blackwire 8225 Leatherette Ear Cushions (2 Pieces)	783Q9AA
---	---------

Poly Blackwire C310/320 Foam Ear Cushions (2 Pieces)	85S15AA
--	---------

Poly USB-A to USB-C Adapter	85Q48AA
-----------------------------	---------

Poly USB-C to USB-A Adapter	85Q49AA
-----------------------------	---------

Disclaimer — Copyright

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – May 21, 2025 11:18 AM UTC+0000