



# Poly Savi 8210 Top and Charging Cradle (85T30AA)

## Overview

### Power through the noise

Hearing every word clearly on a call is not a nice-to-have, it is a must-have. With the Poly Savi 8200 Office series, you can tune out noise and nearby conversations with noise-canceling microphone plus close conversation limiting.

### Freedom to roam

Being able to talk for a long time on a single charge means work gets done. And with the freedom to roam up to 590 ft/180 m means you can keep the calls going, even away from the desk [1].

### Multi-device connectivity

Today's enterprise and contact center professionals work on a range of devices. Savi 8200 Office Series headset systems have 3-way connectivity – computer, desk phone and mobile phone – for convenient conferencing on up to two devices at once.

# Features

## 3-way connectivity

Manage all your calls with a compatible single base that offers 3-way connectivity – computer, desk phone and mobile.

## Take it further

Everyone can move, multitask, and get more done with up to 13 hours of talk time on a single charge. Convenient voice prompts notify of mute status, wireless range limit and more.

## Training made easy

Make training and collaboration easy with the ability to conference up to 4 headsets onto a single base.

## Crystal-clear calls

Reduce background sounds with noise-canceling microphone and close conversation limiting.

## Privacy is ensured

Privacy of your conversation is ensured: DECT™ security-certified headset.

## Communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.<sup>[2]</sup>

---

[1] Line of sight from computer.

[2] Visit [www.poly.com/savi-8200-office](http://www.poly.com/savi-8200-office) for more detail.

## Specifications

<b>Audio</b>	Noise and echo reduction
<b>Package dimensions (W x D x H)</b>	190 x 210 x 55 mm
<b>Package weight</b>	300 g
<b>Battery life</b>	>13 hours (talk time, over-the-head); >50 hours (standby time)
<b>Special features</b>	Adjustable headband
<b>UPC number</b>	(ABA) 197497580006; (ABB) 197497580020; (UUF) 197497580037
<b>Manufacturer Warranty</b>	Poly standard two-year limited warranty
<b>What's in the box</b>	Headset (top only)

## Additional specifications

<b>Acoustic protection technology</b>	SoundGuard Digital <sup>[1,2]</sup>
<b>Battery type</b>	Rechargeable Li-ion polymer
<b>Button user controls</b>	Power on/off; Call answer/end; Mute; Volume +/-
<b>Cartons per layer</b>	6
<b>Cartons per pallet</b>	36
<b>Certified collaboration software</b>	Zoom
<b>Charge time</b>	3 hours
<b>Color</b>	Black
<b>Connection type</b>	USB Type-A
<b>Connection type</b>	Bluetooth® 4.2; DECT™
<b>Connectivity</b>	3-way base
<b>Country of origin</b>	Made in Mexico
<b>ECCN</b>	EAR99
<b>Ear cushions</b>	PC (polycarbonate) (surface material)
<b>Ecolabels</b>	TCO Certified
<b>HTS code</b>	8517620090
<b>Headphone type</b>	On-ear (monoaural)
<b>Impedance</b>	32 ohms
<b>Indicator light</b>	On call
<b>Management Software</b>	Plantronics Hub (desktop)
<b>Microphone bandwidth</b>	35 Hz to 21 kHz
<b>Microphone type</b>	Omnidirectional
<b>Multiple order quantity</b>	12
<b>Package dimensions (W x D x H)</b>	7.48 x 8.26 x 2.16 in
<b>Package weight</b>	0.66 lb
<b>Paired devices</b>	Up to 2
<b>Pallet (layers)</b>	6
<b>Pallet dimensions</b>	40 x 48 x 58.66 in
<b>Pallet dimensions (W x D x H)</b>	101.6 x 121.9 x 149 cm
<b>Pallet weight</b>	357 kg
<b>Pallet weight</b>	787.05 lb
<b>Products per pallet</b>	432
<b>Products per pallet layer</b>	72

<b>Sensitivity (microphone)</b>	-40 +/-3 dB
<b>Signal-to-noise ratio</b>	>53 dB
<b>Speaker bandwidth</b>	20 Hz to 20 kHz (media mode)
<b>Speaker size</b>	32 mm
<b>Supported bluetooth profiles</b>	A2DP; AVRCP; HFP; HSP
<b>UC compatibility</b>	Standard
<b>UNSPSC code</b>	43191638
<b>Voice alerts</b>	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low
<b>Wearing style</b>	Mono
<b>Wireless range</b>	Up to 180 m in open area; Up to 55 m in typical office environment
<b>Wireless range (imperial)</b>	Up to 590 ft in open area; Up to 180 ft in typical office environment

---

*[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).*

*[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.*

---

## Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Dec 09, 2024 10:10 AM UTC+0000