



# Poly Blackwire C3215 Monaural Headset +Carry Case TAA (Bulk) (8M3X9A6)



## Overview

### Freedom to work your way

The Blackwire 3200 Series provides a quality audio experience in a headset that's built for enterprise needs. With a sleek design and flexible microphone boom for a customizable fit, what's not to love?

### Poly signature audio quality

Experience the high-quality audio you expect from Poly with a headset that offers PC wideband, a noise-canceling mic, and hi-fi stereo sound options. Dynamic EQ optimizes call quality and automatically adjusts the settings for listening to multimedia.

### Long-lasting comfort and portability

Relax while you talk knowing your headset is secure- lightweight metal headband offers durability plus a custom fit. Leatherette ear cushions fold flat for easy portability.

### Advanced connectivity

Ideal for managing calls on your PC, mobile phone, or tablet combined with the comfort and durability of a corded headset for greater flexibility.

# Features

## Enhanced call quality

Dynamic EQ optimizes the quality of your voice on calls, and automatically adjusts the EQ settings when you want high-quality sound for listening to music or for multimedia playback.

## Wearing style

Monaural wearing style for those who prefer to leave one ear open.

## Simple call management

Use the intuitive inline controls to answer/end calls, control volume, and mute to simplify call management. Conveniently placed indicator lights provide helpful but unobtrusive user call, mute, and volume status.

## Connectivity options

Select the right option for your device: USB-A or USB Type-C® for PC and 3.5 mm for mobile connectivity with select models.

## Lightweight design

A lightweight metal headband offers durability and a comfortable custom fit.

## Optimized for communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.<sup>[1]</sup>

---

[1] Visit <https://www.poly.com/us/en/products/headsets/blackwire/blackwire-3200> for more detail.

## Additional specifications

<b>Acoustic protection technology</b>	SoundGuard <sup>[1]</sup>
<b>Audio</b>	Dynamic EQ optimized; Digital signal processing (DSP); Noise cancellation (NC)
<b>Boom mic length (ft)</b>	0.43 ft
<b>Boom mic length (mm)</b>	130 mm
<b>Boom mic rotation</b>	270°
<b>Button user controls</b>	Call answer/ignore/end/hold; Redial; Mute; Volume +/-
<b>Cable length</b>	129.5 cm (inline module to headset); 90 cm (USB to inline module); 227 cm (total USB to headset)
<b>Cable length (imperial)</b>	4.25 ft (inline module to headset); 2.95 ft (USB to inline module); 7.45 ft (total USB to headset)
<b>Cartons per layer</b>	4
<b>Cartons per pallet</b>	12
<b>Certified collaboration software</b>	Skype for Business; Cisco Jabber; Avaya
<b>Color</b>	Black
<b>Compatibility</b>	Compatible with PCs via USB/USB Type-C <sup>®</sup> , connects to mobile devices and tablets via 3.5 mm and devices that support USB Type-C <sup>®</sup>
<b>Compatible Operating Systems</b>	Windows 11; Windows 10; macOS
<b>Connection type</b>	Wired USB Type-C <sup>®</sup> ; 3.5 mm audio
<b>Connects to</b>	PC
<b>Country of origin</b>	Made in Mexico
<b>Ear cushions</b>	Artificial leather (surface material)
<b>Headphone type</b>	On-ear (monoaural)
<b>Impedance</b>	32 ohms
<b>Management Software</b>	HP Headset Control Center
<b>Manufacturer Warranty</b>	Poly standard two-year limited warranty
<b>Microphone bandwidth</b>	100 Hz to 10 kHz
<b>Microphone type</b>	Omnidirectional
<b>Minimum System Requirements</b>	USB Type-C <sup>®</sup> port; 3.5 mm audio
<b>Minimum dimensions (W x D x H)</b>	6.1 x 1.25 x 7.1 in
<b>Minimum dimensions (W x D x H)</b>	155 x 32 x 178 mm
<b>Multiple order quantity</b>	50
<b>Package dimensions (W x D x H)</b>	185 x 56 x 207 mm
<b>Package dimensions (W x D x H)</b>	7.48 x 8.26 x 2.16 in
<b>Package weight</b>	300 g

<b>Package weight</b>	0.66 lb
<b>Pallet (layers)</b>	3
<b>Pallet dimensions</b>	40 x 48 x 58.66 in
<b>Pallet dimensions (W x D x H)</b>	101.6 x 121.9 x 149 cm
<b>Pallet weight</b>	357 kg
<b>Pallet weight</b>	787.05 lb
<b>Products per pallet</b>	600
<b>Products per pallet layer</b>	200
<b>Sensitivity (microphone)</b>	-38 dBV/Pa
<b>Sensitivity (speaker)</b>	90 dB
<b>Signal-to-noise ratio</b>	>118 dB
<b>Speaker size</b>	28 mm
<b>Special features</b>	Adjustable headband; Voice alerts
<b>UNSPSC code</b>	43191638
<b>UPC number</b>	197498193847
<b>Weight</b>	87 g (with cable); 64 g (without cable)
<b>Weight</b>	0.19 lb (with cable); 0.14 lb (without cable)
<b>What's in the box</b>	USB Type-C® cable; Headset; Travel case

---

[1] Protects against Acoustic Shock by limiting sounds to below 118 dBA.

---

# Services

## Poly Services

★ : Recommended

### Poly Support Services

3 year Poly+ Blackwire Service	PBLKWIRE312 ★
3 year Next Business Day Hardware Advance Replacement Blackwire Poly DaaS Service	DBLKWIREDS3
3 year Partner Poly+ Blackwire Service	PBLKWIRE362

# Hybrid Work Solutions

## Audio

★ : Recommended

### Audio Accessories

Poly 2.5mm to QD Cable (0.45M)	85Q30AA
Poly 2.5mm to QD Cable (3M)	85Q32AA
Poly 2.5mm to QD Cable with Hookswitch (0.18M)	85Q35AA
Poly 2.5mm to QD Gold Cable (0.45M)	85S11AA
Poly 3.5mm to QD Cable (0.15M)	85Q37AA
Poly 3.5mm to QD Cable (3M)	85Q40AA
Poly 3.5mm to QD Cable for IP Touch (3M)	85Q43AA
Poly 4 Pin QD to 6 Pin QD Cable	85Q45AA
Poly 4 Pin QD to 6 Pin QD Cable (0.13M)	85Q47AA
Poly A10-11 QD to QD Adapter	85S27AA
Poly A10-12 Adapter (S1 Plug)	85S26AA
Poly A10-16 Adapter	85T17AA
Poly A10-16 Adapter (Bagged)	85T18AA
Poly AL10 Inline Audio Limiter	85S25AA
Poly Blackwire 3200 Leatherette Ear Cushions (2 Pieces)	85S24AA
Poly Blackwire 3200 USB-A Inline Controls	85R03AA
Poly Blackwire 3200 USB-C Inline Controls	85R04AA
Poly Blackwire 3215 3.5mm Top	85R05AA
Poly Blackwire 3300 Case	85R06AA
Poly Blackwire 3310/3320 Foam Ear Cushions (2 Pieces)	85S23AA
Poly Blackwire 3315/3325 Leatherette Ear Cushions (2 Pieces)	85S22AA
Poly Blackwire 435 Clothing Clip (1 Piece)	85S21AA
Poly Blackwire 5000 Leatherette Ear Cushions (2 Pieces)	85S19AA
Poly Blackwire 5200 USB-A Inline Controls	85Q62AA
Poly Blackwire 5200 USB-C Inline Controls	85Q64AA
Poly Blackwire 5200 Y Training Cable	85S08AA
Poly Blackwire 600/700 Leatherette Ear Cushions (2 Pieces)	85S18AA
Poly Blackwire 7225 Case	85Q69AA
Poly Blackwire 7225 Espresso Leatherette Ear Cushions (2 Pieces)	85S17AA
Poly Blackwire 7225 Sand Leatherette Ear Cushions (2 Pieces)	85S16AA

Poly Blackwire 8225 Leatherette Ear Cushions (2 Pieces)	783Q9AA
Poly Blackwire C310/320 Foam Ear Cushions (2 Pieces)	85S15AA
Poly CA22CD-DC Dual Channel Remote with Battery	85Q91AA
Poly CA22CD-SC Single Channel Remote with Battery	85Q92AA
Poly DA75 USB to QD Black Adapter TAA	786C6AA
Poly DA90 USB to QD Adapter	85T19AA
Poly HIC-1 Cable	85R30AA
Poly HIC-10 Cable	783S2AA
Poly HIS Cable TAA	783S3AA
Poly M15D Adapter	85Q54AA
Poly M22 Adapter	85T20AA
Poly M22 Adapter (Bilingual)	85Q15AA
Poly M22 High Gain Adapter	85Q17AA
Poly M22 High Gain Adapter (Bilingual)	85Q19AA
Poly M22 Narrowband Adapter	85T21AA
Poly M22 to 2.5mm Cable (0.5M)	85R36AA
Poly M22 to QD Cable	85R38AA
Poly M22 to QD Lightweight Cable	85R40AA
Poly MDA100 RJ9 Cable	85R42AA
Poly MDA500 Cable	85R46AA
Poly MDA500 USB-C to USB-A Cable	85R48AA
Poly MDA500 USB-C to USB-C Cable	85R50AA
Poly MDA524 USB-C	85Q24AA
Poly QD to QD Extension Cable (3M)	85R66AA
Poly QD to QD Lightweight Extension Cable with QD Lock	85R69AA
Poly U10 Lightweight Cable with QD Lock	85R85AA
Poly USB-A to USB-C Adapter	85Q48AA
Poly USB-C to USB-A Adapter	85Q49AA
Poly Y Training Cable	85S07AA
Poly Y Training Cable with QD Lock-Digital Headsets	85S09AA

---

## Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

