

# ThinkPad X1 Yoga Gen 8

Powered by up to 13th Gen Intel U or P Series Core i7 Processor, this laptop combines productivity and lightweight design – ideal for professionals who demand optimal performance while they are on the move. Support of Wi-Fi 6E ensures a high-speed and reliable connected experience helping users to work from anywhere, even in a device-crowded network. With a 57Wh battery that supports rapid charge, the laptop gives the power to keep rolling through your workday.



Professionals will appreciate the bright and immersive 14" screen with up to WQUXGA resolution and up to 500nits brightness that offers greater pixel density. The multi-touch fold enables a productivity mode, transforming the laptop into a tablet for the reader.

Users can work without limits in any location with up to 64GB LPDDR5 memory and up to 2TB SSD, accelerating performance and enabling multitasking productivity without slowing the device down.

Minimal preloaded applications mean maximum battery life and responsiveness for users, and faster deployment for IT admins.

## Lenovo devices that are a class apart

The ultimate device for any mobile worker or executive, ThinkPad X1 Series combines the latest productivity and security technologies with sleek and lightweight designs.

## Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



### Return To Depot Repair Warranty

No-hassle repair process at a Lenovo service center  
Lenovo pays for all shipping between the customer and service facility  
Avoid unplanned operational expense with a simple annual fee

## Accessories

### Lenovo Yoga Mouse with Laser Presenter



High-precision up to 1600 DPI tracking and ergonomic V-shape grip.  
Dual-mode support via Bluetooth 5.0 or 2.4 GHz USB dongle.  
Maximum thickness of 14 mm in flat mode; the ergonomic V-shape form factor provides ample space for your palm and optimal placement for your fingers.

PN: GY50U59626

### Lenovo Essential Wireless Keyboard & Mouse Combo



Simple design that is comfortable for all day use and tough enough to handle spills  
Convenient and easy to use wireless connection  
Quality typing experience with quiet key strokes and a full-size number pad

PN: 4X30M39458 - US English

# ThinkPad X1 Yoga Gen 8

## Key Specifications

<p><b>Processor</b> 13th Gen Intel U or P Series Core i5 / i7</p>
<p><b>Operating System</b> Windows 11 Pro, Windows 11 Home, Windows 11 Home Single Language, Windows 11 DG Windows 10 Pro 64, Linux, Ubuntu Linux</p>
<p><b>Display</b> 14" WUXGA (1920x1200), IPS, Anti-glare, 16:10 - 400nits, 100% sRGB, touch, low power, Eyesafe, ICC Template color calibration</p> <p>14" WUXGA (1920x1200), IPS, Anti-glare, 16:10 - 500nits, 100% sRGB, touch, ThinkPad Privacy Guard</p> <p>14" WUXGA (1920x1200) IPS ARAS 16:10 - 400nits, 100% sRGB, touch, low power, Eyesafe, ICC Template color calibration</p> <p>14" WQUXGA (3840x2400) OLED ARAS 16:10 - 500nits Brightness, 100% DCI-P3, touch, Dolby Vision, DisplayHDR 400, Eyesafe, ICC Template color calibration</p>
<p><b>Touchscreen</b> OGS (One Glass Solution) multi-touch, supports 10-point touch</p>
<p><b>Graphics</b> Intel Iris Xe Graphics eligible (integrated)</p>
<p><b>Memory</b> 16GB LPDDR5/x-6400, soldered 32GB LPDDR5/x-6000, soldered 64GB LPDDR5/x-6000, soldered</p>
<p><b>Storage</b> Up to 1x 2TB M.2 2280 PCIe NVMe SSD</p>
<p><b>Audio</b> High Definition (HD) Audio, Stereo speakers, 2W x2 woofers and 0.8W x2 tweeters, Dolby Atmos Quad-microphone array, 360° far-field, Dolby Voice</p>
<p><b>Battery</b><sup>†</sup> 57Wh (up to 13.2 hr) battery, Rapid Charge</p>
<p><b>Power Adapter</b> <i>One of the following</i> 45W USB-C (2-pin) 45W USB-C (3-pin) 65W USB-C (2-pin) 65W USB-C (3-pin) 65W USB-C Slim (2-pin) 65W USB-C Slim (3-pin)</p>
<p><b>Camera</b> <i>One of the following</i> FHD 1080p + IR Discrete with Privacy Shutter, MIPI, Computer Vision FHD 1080p + IR Hybrid with Privacy Shutter FHD 1080p with Privacy Shutter</p>
<p><b>Keyboard</b> 6-row, spill-resistant, air intake design, backlight, TrackPoint and glass surface touchpad 56 x 110 mm (2.20 x 4.33 inches)</p>
<p><b>Dimensions</b> 314.4 x 222.3 x 15.53 mm (12.38 x 8.75 x 0.61 inches)</p>
<p><b>Weight</b> Starting at 1.38 kg (3.04 lbs)</p>

## Green Certifications

EPEAT Gold, ENERGY STAR 8.0, ErP Lot 6/26, TCO Certified 9.0, RoHS compliant

## Connectivity

**I/O Ports**  
1x USB 3.2 Gen 1, 1x USB 3.2 Gen 1 (Always On), 2x Thunderbolt 4 / USB 4 40 Gbps (data, PD 3.0, DP 1.4a), 1x HDMI (up to 4K/60Hz), 1x Headphone / microphone combo jack (3.5mm), Optional 1x Nano-SIM card slot (WWAN support models)

**WLAN + Bluetooth**  
Intel Wi-Fi 6E AX211, 11ax 2x2 + BT5.1

**WWAN**  
Optional

**NFC**  
Optional

**Docking**  
Docking support via Thunderbolt / USB-C

## Security & Privacy

Fingerprint Reader  
IR Camera with Windows Hello  
ThinkPad PrivacyAlert  
ThinkPad PrivacyGuard screen  
Discrete TPM 2.0, TCG certified  
Kensington Nano Security Slot  
Touch style MOC fingerprint reader  
Camera privacy shutter  
Optional IR camera for Windows Hello  
Optional Privacy Guard with Privacy Alert  
Optional Computer Vision-based User Presence Sensing  
Glance by Mirametrix

## Manageability

Intel vPro Enterprise  
Non-vPro